


Metal Element Current Sense Resistor



ULR Series

- Robust metal strip able to withstand high temperature and high current.
- Low TCR and Inductance
- Resistance Range from 0.5 mΩ to 15 mΩ
- Power ratings from 1W to 3W in 1206, 2010 and 2512 chip size
- Designed for current sense circuits in power electronic systems
- Higher wattage devices feature PCB clearance gap to maximize thermal performance



Electrical Data

IRC Type	Coating ²	Power rating at 80°C (Watts)	Standard Resistance Values (mΩ) ¹	TCR (±ppm/°C)	Tolerance (±%)	Dielectric Withstanding Voltage (Volts)	
1206 Chip Size							
ULRG1	Green	1	1, 2, 3, 5, 7, 10	50	1, 5	100	
2010 Chip Size							
ULRG15	Green	1.5	1, 2, 3, 5, 7, 10	50	1, 5	100	
2512 Chip Size							
ULRG1	Green	1	11, 12, 15	50	1, 5	200	
ULRG2		2	7, 8, 9, 10	50			
ULRG25		2.5	4, 4.5, 5, 6	50			
ULRG3		3	0.5, 0.75	100			
			1, 1.5, 2, 2.5, 3	50			
ULRB1	Black	1	2.5, 3	150			
			4, 5	100			
			6, 7	75			
ULRB2		2	0.5, 0.75, 1, 1.5, 2	50			

Notes:

¹ Non-standard resistance values available (contact factory). For resistance values above 20 mΩ, please refer to our LRC / LRF / LRMA series. ² Black coating = wave or IR reflow soldering; Green coating = IR reflow solder. Wave reflow - solder mask must match the W and D dimensions on page 2 of data sheet. ³ Package sizes 2010 and 1206 with the green coating are uncoated on the top surface and unmarked for resistance value.

Environmental Data

Test	
Short Term Overload (5x rated power for 5 seconds)	ΔR/R ≤ ± 0.5% + 0.5 mΩ (black); ΔR/R ≤ ± 1% (green)
Load at rated power (1000 hours cyclic load @ 70°C)	ΔR/R ≤ ± 1% + 0.5 mΩ (black); ΔR/R ≤ ± 1% (green)
Temperatature Cycling (-55°C to +150°C; 1000 cycles)	ΔR/R ≤ ± 0.5% + 0.5 mΩ (black); ΔR/R ≤ ± 1% (green)
Dry Heat (+170°C, no load; 1000 hours)	ΔR/R ≤ ± 1% + 0.5 mΩ (black); ΔR/R ≤ ± 1% (green)
Resistance to Solder Heat (260°C for 10 seconds)	ΔR/R ≤ ± 0.5% + 0.5 mΩ (black); ΔR/R ≤ ± 1% (green)
Solderability (235°C for 2 seconds)	Minimum 95% coverage
Resistance to Solvents	No deterioration of protective coating or marking
Operating Temperature	-55°C to 170°C


General Note

TT electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT electronics' own data and is considered accurate at time of going to print.



www.bitechnologies.com www.irctt.com www.welwyn-tt.com

Physical Data



Coating	Resistance Value (mΩ)	L	W	T	D
1206 Chip Size (1 Watt)					
Green	1.0, 4.0, 5.0, 6.0	3.20±0.25	1.60±0.10	0.60±0.20	1.10±0.25
	2.0, 3.0, 10				0.60±0.25
	7.0, 8.0, 9.0				0.90±0.25
2010 Chip Size (1.5 Watt)					
Green	1	5.08±0.25	2.54±0.15	0.60±0.20	1.84±0.25
	2.0, 6.0, 7.0, 8.0				1.54±0.25
	3				1.04±0.25
	4.0, 5.0				1.84±0.25
2512 Chip Size (1 Watt, 2 Watt, 2.5 Watt, and 3 Watt)					
Green	0.5	6.35 ± 0.25	3.00 ± 0.2	0.6 ± 0.2	2.68 ± 0.25
	0.75				2.48 ± 0.25
	1				1.93 ± 0.25
	1.5				1.43 ± 0.25
	2 - 3				1.18 ± 0.25
	4				2.18 ± 0.25
	5 - 6.5				1.93 ± 0.25
	7				1.43 ± 0.25
	7.5 - 20				1.18 ± 0.25
	0.5				1.25 ± 0.2 1
Black	0.75	6.35 ± 0.25	3.18 ± 0.25	0.65 ± 0.2 1	0.75 ± 0.2 1
	1				0.65 ± 0.2 1
	1.5				0.45 ± 0.2 1
	2				0.35 ± 0.2 1
	2.5				0.65 ± 0.2 1
	3				0.55 ± 0.2 1
	4				0.45 ± 0.2 1
	5				0.35 ± 0.2 1
	6				0.32 ± 0.2 1
	6.5				0.3 ± 0.2 1
	7				0.27 ± 0.2 1
					1.30 ± 0.38










Note:

¹ Dimensions are for reference only. All units are displayed in mm.

General Note

TT electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT electronics' own data and is considered accurate at time of going to print.

Electrical Connections


4-wire pad layout  unit: mm	2512	2-wire pad layout  unit: mm	2512	4-wire measurement points  unit: mm Probe dia.	2512
4-wire pad layout  unit: mm	2010	2-wire pad layout  unit: mm	2010	4-wire measurement points  unit: mm Probe dia.	2010
4-wire pad layout  unit: mm	1206	2-wire pad layout  unit: mm	1206	4-wire measurement points  unit: mm Probe dia.	1206

Package	Resistance (mΩ)	a	L
2512 - Black	All	1.85	2.9
2512 - Green	0.5	2.78	0.9
	0.75	2.58	1.3
	1 - 1.5	2.03	2.4
	2 - 3	1.28	3.9
	4	2.28	1.9
	5 - 6	2.03	2.4
	7	1.53	3.4
	8 - 20	1.28	3.9

Package	Resistance (mΩ)	a	L
1206 - Green	1.0, 4.0, 5.0, 6.0	1.1	1.00
	2.0, 3.0, 10	0.6	2.00
	7.0, 8.0, 9.0	0.9	1.40
	1	1.84	1.40
2010 - Green	2.0, 6.0, 7.0, 8.0	1.54	2.00
	3	1.04	3.00
	4.0, 5.0	1.84	1.40


General Note

TT electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT electronics' own data and is considered accurate at time of going to print.



Black Type


A low TCR resistance alloy plate with plated connection bands is protectively coated and numerically marked with the resistance value, as described in Product Marking. This version has standard plated connection and is suitable for wave or IR reflow soldering processes.



Green Type

A low TCR alloy plate is grooved to set the final resistance. The lower faces are solder plated for connections, and the top surface is protectively coated and numerically marked with the resistance value, as described in Product Marking. This part is suitable for wave and IR reflow soldering processes. Wave reflow requires the solder mask to be dimensioned according to page 2 using the W and D dimensions of the part.


Power Derating Curve



Note:

The power derating curve is a guidance based on a conservative design model. The ULR is a solid metal alloy construction that can withstand significantly greater operating temperatures than the conservative model permits. The protective coating will operate up to 260°C and the alloy can withstand in excess of 350°C. Therefore, the system thermal design will be a more significant design parameter due to the heat limitations of the solder joint.

Plastic Tape Specification



Size	Resistance (mΩ)	A	B	W	E	F	P ₀	P ₁	P ₂	Φ D ₀	Φ D ₁	T
2512	0.5 - 7	3.4±0.1	6.73±0.1	12±0.1	1.75±0.1	5.5±0.05	4±0.1	4±0.1	2±0.05	1.5±0.1, -0	1.4 min.	0.81±0.1
	0.5 - 20		6.75±0.1							1.5±0.1, -0	1.4 min.	0.80±0.1
2010	1 - 10	2.85±0.1	5.55±0.1	12±0.1	1.75±0.1	5.5±0.05	4±0.1	4±0.1	2±0.05	1.55±0.05	1.4 min.	0.85±0.1
1206	1 - 10	1.9±0.1	3.6±0.1	8±0.2	1.75±0.1	3.5±0.05	4±0.1	4±0.1	2±0.05	1.55±0.05	1.0 min.	0.87±0.1


Note:

1. The cumulative tolerance of 10 sprocket hole pitch is ± 0.2 mm.
2. Carrier camber shall not be more than 1 mm per 100 mm through a length of 250 mm.
3. A & B measured 0.3 mm from the bottom of the packet.
4. T measured at a point on the inside bottom of the packet to the top surface of the carrier.
5. Pocket position relative to sprocket hole is measured as the true position of the pocket and not the pocket hole.

General Note

TT electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT electronics' own data and is considered accurate at time of going to print.

IRC Solder Reflow Recommendations



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Average Ramp-up rate (T_{smax} to T_p)	3°C / second max.	3°C / second max.
Preheat		
- Temperature Min (T_{smin})	100°C	150°C
- Temperature Max (T_{smax})	150°C	200°C
- Time (T_{smin} to T_{smax}) (t_s)	60 -120 seconds	60 -180 seconds
Time maintained above		
- Temperature (T_L)	183°C	217°C
- Time (t_L)	60 - 150 seconds	60 - 150 seconds
Peak Temperature (T_p)	See Table 1	See Table 2
Time within 5°C of actual Peak Temperature (t_p) ²	10 - 30 seconds	20 - 40 seconds
Ramp-down Rate	6°C / second max.	6°C / second max.
Time 25°C to Peak Temperature	6 minutes max.	8 minutes max.

Tabel 1: SnPb Eutectic Process - Package Peak Reflow Temperatures		
Package Thickness	Volume mm ³ < 350	Volume mm ³ ≥ 350
< 2.5 mm	240 +0/-5°C	225 +0/-5°C
≥ 2.5 mm	225 +0/-5°C	225 +0/-5°C

Tabel 2: Pb-free Process - Package Peak Reflow Temperatures			
Package Thickness	Volume mm ³ < 350	Volume mm ³ 350 - 2000	Volume mm ³ > 2000
< 1.6 mm	260°C *	260°C *	260°C *
1.6 mm - 2.5 mm	260°C *	250°C *	245°C *
≥ 2.5 mm	250°C *	245°C *	245°C *

* Tolerance: The device manufacturer/supplier shall assure process compatibility up to and including the stated classification temperature at the rated MSL level.


General Note

TT electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT electronics' own data and is considered accurate at time of going to print.

Packaging Quantity	
Series	Emboss Plastic Tape
2512	2,000
2010	2,000
1206	2,000

Ordering Data

Specify type, resistance, tolerance, ROHS compliance and packaging.
Example: Metal Element Current Sense Resistor, 1-watt, 10 mΩ resistor.



Product Marking

Part resistance is indicated by using two marking notation styles:

- 4-digit: R002 = 2 mΩ; R designates the decimal location in ohms.
- 4-digit: 1M50 = 1.5 mΩ; M designates the decimal location in milli-ohm.
- 3-digit: 1M5 = 1.5 mΩ; M designates the decimal location in milli-ohm.

General Note

TT electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT electronics' own data and is considered accurate at time of going to print.