PIHER

According to E.L.V. (2000/53/EC) / RoHS (2002/95/EC)

PC-16 16 mm Carbon Potentiometer



Bushless version

FEATURES

- Carbon resistive element
- Dust proof enclosure
- Polyester substrate
- Modular gang type (up to 4)
- Self extinguishable material UL 94-V0
- Upon request:
  - Metalic support
  - Stereo matching
  - Switch
  - Nut & washer
  - Bushless option available

MECHANICAL SPECIFICATIONS

– Mechanical rotation angle:	300° ± 5°
– Electrical rotation angle:	280° ± 20°
– Torque:	0.5 to 1.5 Ncm. (0.7 to 2.1 in-oz)
– Stop torque:	> 40 Ncm. (>56 in-oz)
– Max. torque nut (binding out):	< 80 Ncm. (112 in-oz)
– Thrust and pull in the shaft:	> 25 N

ELECTRICAL SPECIFICATIONS

– Range of values (*)
100Ω ≤ Rn ≤ 5 M (Decad. 1.0 - 2.0 - 2.2 - 2.5 - 4.7 - 5.0)

– Tolerance (*): 100Ω ≤ Rn ≤ 1M Ω ------ ± 20%
1MΩ < Rn ≤ 5M Ω ------ ± 30%

– Max. Voltage: 250 VDC (lin) 125 VDC (no lin)

– Nominal Power 50°C (122°F) (see power rating curve)
0.2 W (lin) 0.1 W (no lin)

– Taper (*) (Log. & Alog. only Rn > 1K) Lin ; Log; Alog.

– Residual resistance(*): ≤ 0.5% Rn (5 Ω min.)

– Equivalent Noise Resistance: ≤ 3% Rn (3 Ω min.)

– Operating temperature**: –25°C + 70°C (–13°F + 158°F)

* Others upon request

** Up to 85°C depending on application

HOW TO ORDER

STANDARD | OPTIONAL EXTRAS

PC-16	D	H	10	I	M06	203	A	2020	0				
Serie	Model	Mounting style	Bushing diameter	Terminals	Shafts	Value	Taper	Tolerance	Shafts spec. leng.	Mounting brackets	Stereo matching	Switch	Nuts & Washers
PC-16	S =Single D =Tandem T =Triple C =Quad.	H= Horizontal V = Vertical (See note 1)	07 = M7 10 = M10 SC = Bushless (See note 2)	I = PCB C = Solder Lugs	M04 M06 M07 M11 M17 P01 P22 --- (See note 3)	101 = 100 Ω 203 = 20 K 504 = 500 K 505 = 5M (See note 4)	A = Linear B = Log. C = Alog. (See note 10) Others tapers on request	2020 = +/- 20% 3030 = +/- 30% (See note 5)	XX.X (See notes 6,9)	M1 M2 (See note 7)	3D = 3dB 4D = 4dB 6D = 6dB (See note 8)	I = PCB C = Solder lugs (See note 9)	-TA = loose nut & washer MTA=assembled nut & washer -T- = loose nut MT- = assembled nut (See note 9)

NOTES:

(1) Mounting style: Type "V" is only available in model "S" potentiometer and with printed circuit terminals.
(2) Bushings: Type "10" has two paralell flat surfaces for avoiding rotation. Bushless option only available for single model.
(3) M07 shaft is only available with M10 bushing. --- = no shaft
(4) Value: • Code: 10 1 100 Ω
→ Number of zeros
→ 2 first digits of the value.
• In models "D", "T", "C", with different values, they will be asked by drawings.
(5) Tolerance (non standard), upon request. Example: +7% -5% Code: 07 05
→ negative tolerance
→ positive tolerance
(6) Shaft special length:
• Only for special length and plain shafts (not knurled). Example: Shaft Ø6.35 L= 24.5 M07 ..... 24.5
→ special length shafts
• NOTE: Maximun length recommended: L = 45
(7) Mounting brackets: Only applicable for model "S", mounting "H" and without switch.
(8) Stereo matching: not available for single models. Maximun will be: •3dB for model "D" •4dB for model "T" •6dB for model "C"
(9) Not available for Bushless version.
(10) Switch option not available with antilog taper.

NOTE: The information contained here should be used for reference purposes only.

HOW TO ORDER CUSTOM DRAWING

PC-16 S V + DRAWING NUMBER (Max. 16 digits)

This way of ordering should be used for options which are not included in the "How to order" standard and optional extras.

STANDARD OPTIONS

Shaft length ..... 0 Standard Length
Mounting brackets ..... Without mounting brackets
Stereo matching ..... Only on request (see note 8)
Switch ..... No switch
Nut & washer ..... Without nut and washer

MODELS







A = Initial
S = Wiper
E = Final

PC-16 S/D/T/C..H...



PC-16 SV .....

METALLIC SUPPORT







PC-16 SH.....M1



PC-16 SH....M2

BUSHINGS



07



10

EXAMPLES OF BUSHLESS VERSION







TERMINALS





C





I

TAPERS

Standard

A = Linear
B = Log.
C = Alog.



POWER RATING CURVE



NUTS & WASHERS

Bushing 10



Bushing 07



NOTE = Please note relative terminal positions when ordering non linear tapers.

TESTS

		TYPICAL VARIATIONS
ELECTRICAL LIFE	1.000 h. @ 50°C; 0.2 W	±5 %
MECHANICAL LIFE : POT.* SWITCH	25.000 (10-15 CPM) 10.000 (1 A, 50 VAC)	±3 % (Rn < 1 MΩ)
TEMPERATURE COEFFICIENT	–25°C; +70°C	±300 ppm/°C (Rn < 100 KΩ)
THERMAL CYCLING	16 h. @ 85°C; 2h. @ –25°C	±2.5 %
DAMP HEAT	500 h. @ 40°C @ 95% HR	±5 %
VIBRATION (for each plane X,Y,Z)	2 h. @ 10 Hz. ... 55 Hz.	±2 %

(*) only applicable to values ≥1K. For lower values please consult.

SWITCH





PC-16S . . . H . . . . . . I / C







PC-16SV . . . I

SWITCH SPECIFICATIONS

NOMINAL CURRENT	1A, 50 VAC
CONTACT RESISTANCE (initial)	10 m Ω
OPERATING TORQUE	1 to 3 Ncm (1.4 to 4.2 in oz)
OPERATING ANGLE	30° ± 5°
TEST VOLTAGE	500 V

PACKAGING

Boxes of 100 pieces (single body model): Inner dimensions 250 x 160 x 95 mm

METALIC SHAFTS

STANDARD



A	L	CODE
4	45	M04
6	45	M06
6.35	45	M07



A	B	C	L	CODE
2	5	7	15	M11
2	10	11	20	M12
4	12	14	25	M13
4	12	14	30	M14
4	12	14	35	M15
4	12	14	40	M16
4	12	14	45	M17

SPECIAL



A
4
6
6.35

PLASTIC SHAFTS Ø3.1



P09

PLASTIC SHAFTS Ø4



P01



P02



P03

PLASTIC SHAFTS Ø4



P04





P07





P08



P10



P21

PLASTIC SHAFTS Ø6



P05



P06





P11



P12



P13





P14



P15



P16



P17



P18





P19



P20

NOTE: Shaft position shown full CCW. Any other position for plastic shafts has to be shiftted n times 24°
Other positions upon request.



P22