


**EcoCable® Mini**

Small Just Got Mini



**AlphaWire**

*Cables you trust. Service you deserve.*



## EcoCable® Mini Cable

The Smallest Solution to Your Biggest Cable Problems



**S**mall just got mini. Introducing EcoCable Mini. Our newest, completely recyclable high-performance cable is also our smallest and lightest to date. The latest addition to our EcoGen™ family of recyclable wire and cable, EcoCable Mini is small, but the performance advantages are big!

It has all the benefits of our regular EcoCable line, like low specific gravity, low outgassing, and zero halogens. But it's also up to 32% smaller and 44% lighter than standard 300 V PVC cable.



## Small Just got Mini

EcoCable Mini recyclable cable was developed in response to our customers' need for smaller, lighter 300 V cable.

By combining better performance and minimum environmental impact, EcoCable Mini uses its mPPE insulation and jacketing to provide application advantages in a smaller, lighter cable.

Its size makes routing and installation even easier, saving more time during production and maintenance. Even more convenient, it is available in over 250 standard configurations including four shielding options.

## Smaller Size, Lower Weight

Design smaller, lighter devices with EcoCable Mini. Up to 32% smaller and 44% lighter than standard PVC cable, EcoCable Mini uses finely stranded conductors for remarkable flexibility, giving you more options for fast, easy routing. And the thin-wall insulation and jackets give you the most efficient use of constrained spaces.

## Low Outgassing


In applications like medical devices and semiconductor manufacturing equipment, low outgassing is critical in preventing corrosion, contamination, and premature component failure.

EcoCable Mini cable gives you the advantage of up to 92% lower outgassing than PVC control cable. Low outgassing makes it well suited for cleanrooms, where an extremely low particle count is required to lessen the possibility of failure due to contamination.

## More Application Options

EcoCable Mini is a 300 V cable that's ideal for power and signal transmission applications in medical devices, semiconductor manufacturing equipment, and anywhere you are trying to take size and weight out of your design.

**Size Comparison: 28 AWG, 2 conductor unshielded cable**





It's also available in custom and composite configurations, so finding the right EcoCable Mini cable for your application is easier than ever.

### Take Advantage of all the Advantages

- Up to 32% smaller and 44% lighter than PVC
- 92% lower outgassing than PVC
- 28 to 20 AWG

- 100% recyclable mPPE insulation and jacketing
- Contains no halogens, phthalates, or heavy metals
- Meets RoHS and WEEE requirements

### Superior Availability

- Available from stock in most sizes and constructions
- Put-ups as small as 100'
- Same day shipment, next day delivery



Alpha Wire's next generation of eco-friendly, high-performance wire and cable, designed to provide better performance in a smaller package.

- EcoCable®
- EcoWire®
- EcoFlex® Cable
- EcoWire® Plus
- EcoCable® Mini

Learn more about the new EcoGen family of products at [www.alphawire.com/EcoGen](http://www.alphawire.com/EcoGen)



## Specifications

### Configurations

- Multiconductor or multipair
- Unshielded, foil shielded, individually shielded pairs + overall foil shield, and Supra-Shield Foil + Braid
- Custom and composite configurations available

### Materials

- Conductors: Tinned copper
- Insulation: mPPE
- Shielding: Foil
- Jacket: mPPE

### Temperature Range

- -40°C to +80°C

### Voltage Rating

- 300 V

### Properties

- Zero halogen
- Specific gravity: 1.03
- 100% recyclable
- Low outgassing

### Approvals

- UL AWM 21460
- CE
- CSA I A/B FT1
- RoHS
- REACH
- WEEE
- Suitable for use in NFPA 79 applications
- Meets UL VW-1 Flame Rating

### Availability

- 100 ft (30.5 m) and 1000 ft (305 m) lengths
- Bulk

# EcoCable Mini Cable



## Unshielded Multiconductor

### 28 AWG (0.0925 mm<sup>2</sup>)

Stranding: 19/40 (19 x 0.079 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78002       | 2          | 0.094            | 2.39 |
| 78003       | 3          | 0.099            | 2.51 |
| 78004       | 4          | 0.107            | 2.72 |
| 78006       | 6          | 0.124            | 3.15 |
| 78008       | 8          | 0.134            | 3.40 |

### 26 AWG (0.154 mm<sup>2</sup>)

Stranding: 19/38 (19 x 0.102 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78012       | 2          | 0.102            | 2.59 |
| 78013       | 3          | 0.107            | 2.72 |
| 78014       | 4          | 0.116            | 2.95 |
| 78016       | 6          | 0.136            | 3.45 |
| 78018       | 8          | 0.147            | 3.73 |
| 78020       | 10         | 0.170            | 4.32 |
| 78021       | 15         | 0.190            | 4.83 |

### 24 AWG (0.241 mm<sup>2</sup>)

Stranding: 19/36 (19 x 0.127 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78022       | 2          | 0.112            | 2.84 |
| 78023       | 3          | 0.118            | 3.00 |
| 78024       | 4          | 0.128            | 3.25 |
| 78026       | 6          | 0.152            | 3.86 |
| 78028       | 8          | 0.164            | 4.17 |
| 78030       | 10         | 0.190            | 4.83 |
| 78031       | 15         | 0.213            | 5.41 |
| 78403       | 20         | 0.238            | 6.05 |
| 78433       | 25         | 0.268            | 6.81 |

### 22 AWG (0.382 mm<sup>2</sup>)

Stranding: 19/34 (19 x 0.16 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78032       | 2          | 0.126            | 3.20 |
| 78033       | 3          | 0.133            | 3.38 |
| 78034       | 4          | 0.145            | 3.68 |
| 78036       | 6          | 0.173            | 4.39 |
| 78038       | 8          | 0.187            | 4.75 |
| 78040       | 10         | 0.218            | 5.54 |
| 78041       | 15         | 0.245            | 6.22 |
| 78404       | 20         | 0.275            | 6.98 |
| 78434       | 25         | 0.310            | 7.87 |

### 20 AWG (0.616 mm<sup>2</sup>)

Stranding: 19/32 (19 x 0.203 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78042       | 2          | 0.142            | 3.61 |
| 78043       | 3          | 0.150            | 3.81 |
| 78044       | 4          | 0.165            | 4.19 |
| 78046       | 6          | 0.197            | 5.00 |
| 78048       | 8          | 0.214            | 5.44 |
| 78050       | 10         | 0.250            | 6.35 |
| 78055       | 15         | 0.282            | 7.16 |
| 78405       | 20         | 0.317            | 8.05 |
| 78435       | 25         | 0.358            | 9.09 |

# EcoCable Mini Cable



## Unshielded Pairs

### 28 AWG (0.0925 mm²)

Stranding: 19/40 (19 x 0.079 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78052       | 2     | 0.132            | 3.35 |
| 78053       | 3     | 0.140            | 3.56 |
| 78054       | 4     | 0.153            | 3.89 |
| 78005       | 5     | 0.167            | 4.24 |
| 78056       | 6     | 0.182            | 4.62 |
| 78058       | 8     | 0.198            | 5.03 |
| 78009       | 9     | 0.213            | 5.41 |

### 26 AWG (0.154 mm²)

Stranding: 19/38 (19 x 0.102 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78062       | 2     | 0.146            | 3.71 |
| 78063       | 3     | 0.154            | 3.91 |
| 78064       | 4     | 0.169            | 4.29 |
| 78015       | 5     | 0.185            | 4.70 |
| 78066       | 6     | 0.202            | 5.13 |
| 78068       | 8     | 0.219            | 5.56 |
| 78019       | 9     | 0.237            | 6.02 |

### 24 AWG (0.241 mm²)

Stranding: 19/36 (19 x 0.127 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |       |
|-------------|-------|------------------|-------|
|             |       | Inch             | mm    |
| 78072       | 2     | 0.162            | 4.11  |
| 78073       | 3     | 0.172            | 4.37  |
| 78074       | 4     | 0.189            | 4.80  |
| 78025       | 5     | 0.207            | 5.26  |
| 78076       | 6     | 0.227            | 5.77  |
| 78078       | 8     | 0.247            | 6.27  |
| 78029       | 9     | 0.267            | 6.78  |
| 78408       | 20    | 0.369            | 9.37  |
| 78438       | 25    | 0.418            | 10.62 |

### 22 AWG (0.382 mm²)

Stranding: 19/34 (19 x 0.16 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |       |
|-------------|-------|------------------|-------|
|             |       | Inch             | mm    |
| 78082       | 2     | 0.185            | 4.70  |
| 78083       | 3     | 0.197            | 5.00  |
| 78084       | 4     | 0.217            | 5.51  |
| 78035       | 5     | 0.239            | 6.07  |
| 78086       | 6     | 0.261            | 6.63  |
| 78088       | 8     | 0.285            | 7.24  |
| 78039       | 9     | 0.309            | 7.85  |
| 78409       | 20    | 0.429            | 10.90 |
| 78439       | 25    | 0.487            | 12.37 |

### 20 AWG (0.616 mm²)

Stranding: 19/32 (19 x 0.203 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |       |
|-------------|-------|------------------|-------|
|             |       | Inch             | mm    |
| 78092       | 2     | 0.211            | 5.36  |
| 78093       | 3     | 0.225            | 5.72  |
| 78094       | 4     | 0.248            | 6.30  |
| 78045       | 5     | 0.274            | 6.96  |
| 78096       | 6     | 0.301            | 7.65  |
| 78098       | 8     | 0.328            | 8.33  |
| 78049       | 9     | 0.356            | 9.04  |
| 78410       | 20    | 0.498            | 12.65 |
| 78440       | 25    | 0.565            | 14.35 |

## More Choice!

EcoCable Mini cable is available with up to 25 conductors and a variety of shielding options. Custom and composite configurations are also available. Consult Alpha Wire for the latest product specifications.

## Sample the Performance

Samples of EcoCable Mini cable are available today! Request yours at [www.alphawire.com/ecogen](http://www.alphawire.com/ecogen) or call 1-800-52 ALPHA

# EcoCable Mini Cable



## Foil Shielded Multiconductor

### 28 AWG (0.0925 mm<sup>2</sup>)

Stranding: 19/40 (19 x 0.079 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78102       | 2          | 0.098            | 2.49 |
| 78103       | 3          | 0.103            | 2.62 |
| 78104       | 4          | 0.111            | 2.82 |
| 78106       | 6          | 0.128            | 3.25 |
| 78108       | 8          | 0.138            | 3.51 |

### 26 AWG (0.154 mm<sup>2</sup>)

Stranding: 19/38 (19 x 0.102 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78112       | 2          | 0.106            | 2.69 |
| 78113       | 3          | 0.111            | 2.82 |
| 78114       | 4          | 0.12             | 3.05 |
| 78116       | 6          | 0.14             | 3.56 |
| 78118       | 8          | 0.151            | 3.84 |
| 78120       | 10         | 0.174            | 4.42 |
| 78121       | 15         | 0.194            | 4.93 |

### 24 AWG (0.241 mm<sup>2</sup>)

Stranding: 19/36 (19 x 0.127 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78122       | 2          | 0.116            | 2.95 |
| 78123       | 3          | 0.122            | 3.10 |
| 78124       | 4          | 0.132            | 3.35 |
| 78126       | 6          | 0.156            | 3.96 |
| 78128       | 8          | 0.168            | 4.27 |
| 78130       | 10         | 0.194            | 4.93 |
| 78131       | 15         | 0.217            | 5.51 |
| 78413       | 20         | 0.242            | 6.15 |
| 78443       | 25         | 0.272            | 6.91 |

### 22 AWG (0.382 mm<sup>2</sup>)

Stranding: 19/34 (19 x 0.16 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78132       | 2          | 0.13             | 3.30 |
| 78133       | 3          | 0.137            | 3.48 |
| 78134       | 4          | 0.149            | 3.78 |
| 78136       | 6          | 0.177            | 4.50 |
| 78138       | 8          | 0.191            | 4.85 |
| 78140       | 10         | 0.222            | 5.64 |
| 78141       | 15         | 0.249            | 6.32 |
| 78414       | 20         | 0.279            | 7.09 |
| 78444       | 25         | 0.314            | 7.98 |

### 20 AWG (0.616 mm<sup>2</sup>)

Stranding: 19/32 (19 x 0.203 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Conductors | Nominal Diameter |      |
|-------------|------------|------------------|------|
|             |            | Inch             | mm   |
| 78142       | 2          | 0.146            | 3.71 |
| 78143       | 3          | 0.154            | 3.91 |
| 78144       | 4          | 0.169            | 4.29 |
| 78146       | 6          | 0.201            | 5.11 |
| 78148       | 8          | 0.218            | 5.54 |
| 78150       | 10         | 0.254            | 6.45 |
| 78155       | 15         | 0.286            | 7.26 |
| 78415       | 20         | 0.321            | 8.15 |
| 78445       | 25         | 0.362            | 9.19 |

# EcoCable Mini Cable



## Foil Shielded Pairs

### 28 AWG (0.0925 mm<sup>2</sup>)

Stranding: 19/40 (19 x 0.079 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78152       | 2     | 0.136            | 3.45 |
| 78153       | 3     | 0.144            | 3.66 |
| 78154       | 4     | 0.157            | 3.99 |
| 78105       | 5     | 0.171            | 4.34 |
| 78156       | 6     | 0.186            | 4.72 |
| 78158       | 8     | 0.202            | 5.13 |
| 78109       | 9     | 0.217            | 5.51 |

### 26 AWG (0.154 mm<sup>2</sup>)

Stranding: 19/38 (19 x 0.102 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78162       | 2     | 0.150            | 3.81 |
| 78163       | 3     | 0.158            | 4.01 |
| 78164       | 4     | 0.173            | 4.39 |
| 78115       | 5     | 0.189            | 4.80 |
| 78166       | 6     | 0.206            | 5.23 |
| 78168       | 8     | 0.223            | 5.66 |
| 78119       | 9     | 0.241            | 6.12 |

### 24 AWG (0.241 mm<sup>2</sup>)

Stranding: 19/36 (19 x 0.127 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |       |
|-------------|-------|------------------|-------|
|             |       | Inch             | mm    |
| 78172       | 2     | 0.166            | 4.22  |
| 78173       | 3     | 0.176            | 4.47  |
| 78174       | 4     | 0.193            | 4.90  |
| 78125       | 5     | 0.211            | 5.36  |
| 78176       | 6     | 0.231            | 5.87  |
| 78178       | 8     | 0.251            | 6.38  |
| 78129       | 9     | 0.271            | 6.88  |
| 78418       | 20    | 0.421            | 10.69 |
| 78448       | 25    | 0.478            | 12.14 |

### 22 AWG (0.382 mm<sup>2</sup>)

Stranding: 19/34 (19 x 0.16 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |       |
|-------------|-------|------------------|-------|
|             |       | Inch             | mm    |
| 78182       | 2     | 0.189            | 4.80  |
| 78183       | 3     | 0.201            | 5.11  |
| 78184       | 4     | 0.221            | 5.61  |
| 78135       | 5     | 0.243            | 6.17  |
| 78186       | 6     | 0.265            | 6.73  |
| 78188       | 8     | 0.289            | 7.34  |
| 78139       | 9     | 0.313            | 7.95  |
| 78419       | 20    | 0.486            | 12.34 |
| 78449       | 25    | 0.551            | 14.00 |

### 20 AWG (0.616 mm<sup>2</sup>)

Stranding: 19/32 (19 x 0.203 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |       |
|-------------|-------|------------------|-------|
|             |       | Inch             | mm    |
| 78192       | 2     | 0.215            | 5.46  |
| 78193       | 3     | 0.229            | 5.82  |
| 78194       | 4     | 0.252            | 6.40  |
| 78145       | 5     | 0.278            | 7.06  |
| 78196       | 6     | 0.305            | 7.75  |
| 78198       | 8     | 0.332            | 8.43  |
| 78149       | 9     | 0.360            | 9.14  |
| 78420       | 20    | 0.559            | 14.20 |
| 78450       | 25    | 0.635            | 16.13 |

## More Choice!

EcoCable Mini cable is available with up to 25 conductors and a variety of shielding options. Custom and composite configurations are also available. Consult Alpha Wire for the latest product specifications.

## Sample the Performance

Samples of EcoCable Mini cable are available today! Request yours at [www.alphawire.com/ecogen](http://www.alphawire.com/ecogen) or call 1-800-52 ALPHA



# EcoCable

## Mini Cable

### Individually Foil Shielded Pairs + Overall Foil Shield

#### 28 AWG (0.0925 mm<sup>2</sup>)

Stranding: 19/40 (19 x 0.079 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78202       | 2     | 0.153            | 3.89 |
| 78213       | 3     | 0.162            | 4.11 |
| 78204       | 4     | 0.177            | 4.50 |
| 78205       | 5     | 0.194            | 4.93 |
| 78206       | 6     | 0.211            | 5.36 |
| 78208       | 8     | 0.229            | 5.82 |
| 78209       | 9     | 0.247            | 6.27 |

#### 26 AWG (0.154 mm<sup>2</sup>)

Stranding: 19/38 (19 x 0.102 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78212       | 2     | 0.167            | 4.24 |
| 78223       | 3     | 0.177            | 4.50 |
| 78214       | 4     | 0.194            | 4.93 |
| 78215       | 5     | 0.213            | 5.41 |
| 78216       | 6     | 0.232            | 5.89 |
| 78218       | 8     | 0.252            | 6.40 |
| 78219       | 9     | 0.273            | 6.93 |

#### 24 AWG (0.241 mm<sup>2</sup>)

Stranding: 19/36 (19 x 0.127 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78222       | 2     | 0.185            | 4.70 |
| 78233       | 3     | 0.196            | 4.98 |
| 78224       | 4     | 0.215            | 5.46 |
| 78225       | 5     | 0.237            | 6.02 |
| 78226       | 6     | 0.259            | 6.58 |
| 78228       | 8     | 0.282            | 7.16 |
| 78229       | 9     | 0.305            | 7.75 |

#### 22 AWG (0.382 mm<sup>2</sup>)

Stranding: 19/34 (19 x 0.16 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78232       | 2     | 0.209            | 5.31 |
| 78243       | 3     | 0.222            | 5.64 |
| 78234       | 4     | 0.245            | 6.22 |
| 78235       | 5     | 0.270            | 6.86 |
| 78236       | 6     | 0.296            | 7.52 |
| 78238       | 8     | 0.322            | 8.18 |
| 78239       | 9     | 0.349            | 8.86 |

#### 20 AWG (0.616 mm<sup>2</sup>)

Stranding: 19/32 (19 x 0.203 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |       |
|-------------|-------|------------------|-------|
|             |       | Inch             | mm    |
| 78242       | 2     | 0.237            | 6.02  |
| 78253       | 3     | 0.253            | 6.43  |
| 78244       | 4     | 0.279            | 7.09  |
| 78245       | 5     | 0.308            | 7.82  |
| 78246       | 6     | 0.338            | 8.59  |
| 78248       | 8     | 0.369            | 9.37  |
| 78249       | 9     | 0.400            | 10.16 |

# EcoCable Mini Cable

## Supra-Shield Foil + Braid Multiconductor

### 28 AWG (0.0925 mm<sup>2</sup>)

Stranding: 19/40 (19 x 0.079 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number  | Conductors | Nominal Diameter |      |
|--------------|------------|------------------|------|
|              |            | Inch             | mm   |
| <b>78302</b> | 2          | 0.125            | 3.18 |
| <b>78303</b> | 3          | 0.130            | 3.30 |
| <b>78304</b> | 4          | 0.138            | 3.51 |
| <b>78306</b> | 6          | 0.155            | 3.94 |
| <b>78308</b> | 8          | 0.165            | 4.19 |

### 26 AWG (0.154 mm<sup>2</sup>)

Stranding: 19/38 (19 x 0.102 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number  | Conductors | Nominal Diameter |      |
|--------------|------------|------------------|------|
|              |            | Inch             | mm   |
| <b>78312</b> | 2          | 0.133            | 3.38 |
| <b>78313</b> | 3          | 0.138            | 3.51 |
| <b>78314</b> | 4          | 0.147            | 3.73 |
| <b>78316</b> | 6          | 0.167            | 4.24 |
| <b>78318</b> | 8          | 0.178            | 4.52 |
| <b>78320</b> | 10         | 0.201            | 5.11 |
| <b>78321</b> | 15         | 0.221            | 5.61 |

### 24 AWG (0.241 mm<sup>2</sup>)

Stranding: 19/36 (19 x 0.127 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number  | Conductors | Nominal Diameter |      |
|--------------|------------|------------------|------|
|              |            | Inch             | mm   |
| <b>78322</b> | 2          | 0.143            | 3.63 |
| <b>78323</b> | 3          | 0.149            | 3.78 |
| <b>78324</b> | 4          | 0.159            | 4.04 |
| <b>78326</b> | 6          | 0.183            | 4.65 |
| <b>78328</b> | 8          | 0.195            | 4.95 |
| <b>78330</b> | 10         | 0.221            | 5.61 |
| <b>78331</b> | 15         | 0.244            | 6.20 |
| <b>78423</b> | 20         | 0.269            | 6.83 |
| <b>78453</b> | 25         | 0.299            | 7.59 |

### 22 AWG (0.382 mm<sup>2</sup>)

Stranding: 19/34 (19 x 0.16 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number  | Conductors | Nominal Diameter |      |
|--------------|------------|------------------|------|
|              |            | Inch             | mm   |
| <b>78332</b> | 2          | 0.157            | 3.99 |
| <b>78333</b> | 3          | 0.164            | 4.17 |
| <b>78334</b> | 4          | 0.176            | 4.47 |
| <b>78336</b> | 6          | 0.204            | 5.18 |
| <b>78338</b> | 8          | 0.218            | 5.54 |
| <b>78340</b> | 10         | 0.249            | 6.32 |
| <b>78341</b> | 15         | 0.276            | 7.01 |
| <b>78424</b> | 20         | 0.306            | 7.77 |
| <b>78454</b> | 25         | 0.341            | 8.66 |

### 20 AWG (0.616 mm<sup>2</sup>)

Stranding: 19/32 (19 x 0.203 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number  | Conductors | Nominal Diameter |      |
|--------------|------------|------------------|------|
|              |            | Inch             | mm   |
| <b>78342</b> | 2          | 0.173            | 4.39 |
| <b>78343</b> | 3          | 0.181            | 4.60 |
| <b>78344</b> | 4          | 0.196            | 4.98 |
| <b>78346</b> | 6          | 0.228            | 5.79 |
| <b>78348</b> | 8          | 0.245            | 6.22 |
| <b>78350</b> | 10         | 0.281            | 7.14 |
| <b>78355</b> | 15         | 0.313            | 7.95 |
| <b>78425</b> | 20         | 0.348            | 8.84 |
| <b>78455</b> | 25         | 0.389            | 9.88 |

## More Choice!

EcoCable Mini cable is available with up to 25 conductors and a variety of shielding options. Custom and composite configurations are also available. Consult Alpha Wire for the latest product specifications.

## Sample the Performance

Samples of EcoCable Mini cable are available today!  
Request yours at [www.alphawire.com/ecogen](http://www.alphawire.com/ecogen)  
or call 1-800-52 ALPHA

# EcoCable Mini Cable

## Supra-Shield Foil + Braid Pairs

### 28 AWG (0.0925 mm<sup>2</sup>)

Stranding: 19/40 (19 x 0.079 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78352       | 2     | 0.163            | 4.14 |
| 78353       | 3     | 0.171            | 4.34 |
| 78354       | 4     | 0.184            | 4.67 |
| 78305       | 5     | 0.198            | 5.03 |
| 78356       | 6     | 0.213            | 5.41 |
| 78358       | 8     | 0.229            | 5.82 |
| 78309       | 9     | 0.244            | 6.20 |

### 26 AWG (0.154 mm<sup>2</sup>)

Stranding: 19/38 (19 x 0.102 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78362       | 2     | 0.177            | 4.50 |
| 78363       | 3     | 0.185            | 4.70 |
| 78364       | 4     | 0.200            | 5.08 |
| 78315       | 5     | 0.216            | 5.49 |
| 78366       | 6     | 0.233            | 5.92 |
| 78368       | 8     | 0.250            | 6.35 |
| 78319       | 9     | 0.268            | 6.81 |

### 24 AWG (0.241 mm<sup>2</sup>)

Stranding: 19/36 (19 x 0.127 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |       |
|-------------|-------|------------------|-------|
|             |       | Inch             | mm    |
| 78372       | 2     | 0.193            | 4.90  |
| 78373       | 3     | 0.203            | 5.16  |
| 78374       | 4     | 0.220            | 5.59  |
| 78325       | 5     | 0.238            | 6.05  |
| 78376       | 6     | 0.258            | 6.55  |
| 78378       | 8     | 0.278            | 7.06  |
| 78329       | 9     | 0.298            | 7.57  |
| 78428       | 20    | 0.400            | 10.16 |
| 78458       | 25    | 0.449            | 11.40 |

### 22 AWG (0.382 mm<sup>2</sup>)

Stranding: 19/34 (19 x 0.16 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78382       | 2     | 0.216            | 5.49 |
| 78383       | 3     | 0.228            | 5.79 |
| 78384       | 4     | 0.248            | 6.30 |
| 78335       | 5     | 0.270            | 6.86 |
| 78386       | 6     | 0.292            | 7.42 |
| 78388       | 8     | 0.316            | 8.03 |
| 78339       | 9     | 0.340            | 8.64 |

### 20 AWG (0.616 mm<sup>2</sup>)

Stranding: 19/32 (19 x 0.203 mm)  
Insulation thickness: 0.007 (0.18 mm)  
Jacket thickness: 0.015 (0.38 mm)

| Part Number | Pairs | Nominal Diameter |      |
|-------------|-------|------------------|------|
|             |       | Inch             | mm   |
| 78392       | 2     | 0.242            | 6.15 |
| 78393       | 3     | 0.256            | 6.50 |
| 78394       | 4     | 0.279            | 7.09 |
| 78345       | 5     | 0.305            | 7.75 |
| 78396       | 6     | 0.332            | 8.43 |
| 78398       | 8     | 0.359            | 9.12 |
| 78349       | 9     | 0.387            | 9.83 |

## Cables you trust. Service you deserve.

Every application is critical and cable failure is not an option when the safety of your equipment and personnel is paramount. Specify Alpha products since the integrity of your system is only as robust as the products you use.

## Superior availability

Alpha offers wire and cable from stock in most sizes and constructions, in both small and large put-ups, so you can order it when you need it. Our products are available for same-day shipment, eliminating long lead times.

## Service and support, second-to-none

Selecting the correct cable for your critical application is essential to overall system reliability, performance, and safety. So we make it easy for you to select the right Alpha product for your specific application. Our online resources include a wire and cable selection guide, technical information, full product catalog, and a distributor locator to make it easy to select and get the wire or cable you need. Can't find what you're looking for? Design the cable to your specification. It's easy, just visit **[www.alphawire.com](http://www.alphawire.com)**!

GLOBAL HEADQUARTERS  
711 Lidgerwood Avenue  
Elizabeth, NJ 07207-0711 USA  
Toll Free: 1-800-52 ALPHA  
Tel: 1-908-925-8000  
Fax: 1-908-925-5411  
E-mail: [info@alphawire.com](mailto:info@alphawire.com)

EUROPE  
Alpha Wire International  
Saxon House  
1 Downside | Sunbury-on-Thames  
Middlesex | United Kingdom  
TW16 6RT  
Tel: +44-(0)-800-288-8809  
Fax: +44-(0)-800-288-8810  
E-mail: [europa@alphawire.com](mailto:europa@alphawire.com)

ASIA PACIFIC  
Alpha Wire  
Silver Center | Room 1708  
North Shanxi Road 1388  
Shanghai | China | 200060  
Tel: +86-21-61498201/61498205  
Fax: +86-21-61498001  
E-mail: [apac@alphawire.com](mailto:apac@alphawire.com)



Alpha Wire's next generation of eco-friendly, high-performance wire and cable, designed to provide better performance in a smaller package.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Alpha Wire:

|                                    |                                    |                                    |                                    |                                    |                                    |                                    |                                    |
|------------------------------------|------------------------------------|------------------------------------|------------------------------------|------------------------------------|------------------------------------|------------------------------------|------------------------------------|
| <a href="#"><u>78355 SL001</u></a> | <a href="#"><u>78196 SL001</u></a> | <a href="#"><u>78198 SL001</u></a> | <a href="#"><u>78388 SL001</u></a> | <a href="#"><u>78050 SL001</u></a> | <a href="#"><u>78088 SL001</u></a> | <a href="#"><u>78155 SL001</u></a> | <a href="#"><u>78188 SL001</u></a> |
| <a href="#"><u>78145 SL001</u></a> | <a href="#"><u>78098 SL001</u></a> | <a href="#"><u>78350 SL001</u></a> | <a href="#"><u>78039 SL001</u></a> | <a href="#"><u>78245 SL001</u></a> | <a href="#"><u>78049 SL001</u></a> | <a href="#"><u>78239 SL001</u></a> | <a href="#"><u>78248 SL001</u></a> |
| <a href="#"><u>78149 SL001</u></a> | <a href="#"><u>78345 SL001</u></a> | <a href="#"><u>78141 SL001</u></a> | <a href="#"><u>78041 SL001</u></a> | <a href="#"><u>78341 SL001</u></a> | <a href="#"><u>78139 SL001</u></a> | <a href="#"><u>78349 SL001</u></a> | <a href="#"><u>78398 SL001</u></a> |
| <a href="#"><u>78045 SL001</u></a> | <a href="#"><u>78096 SL001</u></a> | <a href="#"><u>78396 SL001</u></a> | <a href="#"><u>78246 SL001</u></a> | <a href="#"><u>78055 SL001</u></a> | <a href="#"><u>78238 SL001</u></a> | <a href="#"><u>78339 SL001</u></a> | <a href="#"><u>78249 SL001</u></a> |
| <a href="#"><u>78150 SL001</u></a> | <a href="#"><u>78309 SL199</u></a> |                                    |                                    |                                    |                                    |                                    |                                    |