

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19070-0120

Status:

Active

Overview:

Ring Tongue - Spade Terminals

Description:

InsulKrimp™ Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 6 (M3.5), Length 27.33mm, Mylar Tape Carrier

Documents:


Drawing (PDF)

Product Specification PS-19902-009 (PDF)

Product Specification PS-19902-011 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19070
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Ring Tongue - Spade Terminals
Product Name	InsulKrimp™
Type	Ring
Physical	
Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	6 (M3.5)
Wire Insulation Diameter	6.40mm max.
Wire Size AWG	10, 12
Wire Size mm²	0.40 - 0.60
Material Info	
Old Part Number	C-228-06XT
Reference - Drawing Numbers	
Product Specification	PS-19902-009, PS-19902-011
Sales Drawing	SD-19070-007



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19070Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Mini-Mac™ Applicator	0638851500
Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals	0192880179

This document was generated on 06/07/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION