


UAQWide Temperature Range, Permissible
Abnormal Voltage


- Improved safety feature for abnormally excessive voltage.
- High ripple current product.
- Compliant to the RoHS directive (2011/65/EU,(EU)2015/863).

UAQ**UAS**


■ Specifications

Item	Performance Characteristics				
Category Temperature Range	-40 to +105°C				
Rated Voltage Range	200 · 400V				
Rated Capacitance Range	10 to 220μF				
Capacitance Tolerance	± 20% at 120Hz, 20°C				
Leakage Current	After 1 minute's application of rated voltage at 20°C, leakage current is 0.04CV+100 (μA) or less.				
Tangent of loss angle (tan δ)	Rated voltage (V)	200	400	Measurement frequency:120Hz at 20°C	
	tan δ (MAX.)	0.15	0.15		
Stability at Low Temperature	Rated voltage (V)		200	400	Measurement frequency : 120Hz
	Impedance ratio (MAX.)	Z-25°C / Z+20°C	3	8	
		Z-40°C / Z+20°C	6	10	
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after D.C. bias plus rated ripple current is applied for 2000 hours at 105°C, the peak voltage shall not exceed the rated voltage.			Capacitance change	Within ±20% of the initial capacitance value
				tan δ	200% or less than the initial specified value
				Leakage current	Less than or equal to the initial specified value
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.				
Safety Performance	The pressure relief vent will operate in normal conditions, with no dangerous conditons such as flames, ignitions or dispersion of pieces of the capacitor and / or case.				
	voltage (V)	Test conditions			
		Limited DC current		Test Voltage	
		200	4A		300VDC and 375VDC
	400	2A		500VDC and 600VDC	
Marking	Printed with white color letter on dark brown sleeve.				

■ Radial Lead Type



- Please refer to page 20 about the end seal configuration.



	φD	10	12.5	16	18	22
P	5.0	5.0	7.5	7.5	10	
φd	0.6	0.6*	0.8	0.8	1.0	
β	0.5	0.5	0.5	0.5	1.0	

※ In case L>25 for φ12.5 (D) case sizes, lead diameter φ0.8 (d) will be applied.

α	(φD≤18) 2.0
	(φD>18) 3.0

Type numbering system (Example : 200V 100µF)

1	2	3	4	5	6	7	8	9	10	11	12
U	A	Q	2	D	1	0	1	M	H	D	
Size code											
Configuration ※											
Capacitance tolerance (±20%)											
Rated capacitance (100µF)											
Rated voltage (200V)											
Series name											
Type											

※ Configuration

φ D	Pb-free leadwire Pb-free PET sleeve
10	PD
12.5 to 18	HD
22	RD

■ Dimensions

V(Code)		200 (2D)					400 (2G)				
Cap.(µF)	Code	φD	φ10	φ12.5	φ16	φ18	φ22	φ12.5	φ16	φ18	φ22
10	100							12.5 × 20 100			
22	220		10 × 20 120					12.5 × 31.5 145	φ16 × 20 145		
33	330		10 × 25 160	φ12.5 × 20 160				12.5 × 40 195	φ16 × 25 195	φ18 × 20 195	
47	470		10 × 31.5 195	φ12.5 × 20 195					16 × 35.5 280	φ18 × 25 280	φ22 × 20 280
56	560			12.5 × 25 210					16 × 35.5 320	φ18 × 31.5 320	φ22 × 25 320
68	680			12.5 × 25 250					16 × 40 350	φ18 × 35.5 350	
82	820			12.5 × 31.5 285	φ16 × 20 285					18 × 40 420	
100	101			12.5 × 35.5 335	φ16 × 25 335	φ18 × 20 335					
150	151				16 × 31.5 435	φ18 × 25 435	φ22 × 20 435				
180	181				16 × 35.5 495	φ18 × 31.5 495	φ22 × 25 495				
220	221					18 × 35.5 575					
Case size φD×L (mm)											
Rated ripple											

Rated ripple current (mA rms) at 105°C 120Hz

● Frequency coefficient of rated ripple current

Frequency	50, 60Hz	120Hz	300Hz	1kHz	10kHz or more
Coefficient	0.80	1.00	1.25	1.40	1.60

○ : In case of low profile type, [6] will be put at 12th digit of type numbering system.

※ : For further low profile product, [3] will be put at 12th digit.

Please refer to page 20, 21, 22 about the formed or taped product spec.

Please refer to page 4 for the minimum order quantity.

CAT.8100I

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

<u>UAQ2D151MRD3</u>	<u>UAQ2D220MPD10</u>	<u>UAQ2D330MPD10</u>	<u>UAQ2D330MHD12</u>	<u>UAQ2D470MPD</u>	<u>UAQ2D470MHD12</u>
<u>UAQ2D560MHD12</u>	<u>UAQ2D680MHD12</u>	<u>UAQ2D820MHD12</u>	<u>UAQ2D820MHD16</u>	<u>UAQ2D101MHD12</u>	
<u>UAQ2D101MHD16</u>	<u>UAQ2D101MHD18</u>	<u>UAQ2D151MHD16</u>	<u>UAQ2D151MHD18</u>	<u>UAQ2D181MHD18</u>	
<u>UAQ2D181MRD22</u>	<u>UAQ2D221MHD18</u>	<u>UAQ2G100MHD12</u>	<u>UAQ2G220MHD12</u>	<u>UAQ2G220MHD16</u>	
<u>UAQ2G330MHD12</u>	<u>UAQ2G330MHD16</u>	<u>UAQ2G330MHD18</u>	<u>UAQ2G470MHD16</u>	<u>UAQ2G470MHD18</u>	
<u>UAQ2G560MRD22</u>	<u>UAQ2G680MHD16</u>	<u>UAQ2G680MHD18</u>	<u>UAQ2G820MHD18</u>	<u>UAQ2G100MHD</u>	<u>UAQ2G820MHD</u>