





SMA type
connector



TNC type
connector

Electrical Properties:

Frequency Range:	902~928 MHz
Impedance:	50Ω nominal
VSWR:	<2.0:1
Gain:	2.0 dBi
Radiation:	Omni
Polarization:	Vertical
Wave:	Half Wave Dipole







Mechanical Properties:

Material:	
Whip:	Polyurethane(Black)
Connector:	Brass with black chrome plating
Operation Temp.:	-20°C to +65°C
Storage Temp.:	-30°C to +75°C

This is a RoHS compliant product.

TITLE	900 MHz ISM Band Straight Antenna - 467 model		Rev. Date	SHEET
			04/23/13	1 of 2
UNIT	DWG. NO.	S467XX - 915		
in.(mm)				
SCALE				
none				

NEARSON



Series Part Numbers

Connector Code -XX-	Description	P / N
AM	SMA Plug	S467AM-915
AH	SMA Plug Reverse Polarity	S467AH-915
TC	TNC	S467TC-915
TR	TNC Plug Reverse Polarity	S467TR-915
BC	BNC	S467BC-915
BR	BNC Plug Reverse Polarity	S467BR-915

Connector Interface



SMA Plug
(AM)



SMA Plug Reverse Polarity
(AH)



TNC Plug
(TC)



TNC Plug Reverse Polarity
(TR)



BNC Plug
(BC)



BNC Plug Reverse Polarity
(BR)

TITLE		900 MHz ISM Band Straight Antenna - 467 model		Rev. Date	SHEET
				04/23/13	2 of 2
UNIT	DWG. NO.	S467XX - 915			
in.(mm)					
SCALE					
none					