



Notes:

1. Electrical:

- Meets EIA/TIA-568-B.2 Cat.5e Specification

① - RJ45 Plug Operating Temperature: -40°C to +85°C

2. Materials and Finish:

- RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
- RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-0
- RJ45 Plug Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
- RJ45 Modular Boot: PVC, Color: Blue
- Cable: Cat. 5e UTP (Unshielded Twisted Pair) AWG24 Solid, Color: Blue

3. RoHS compliant

Directive 2002/95/EC
"RoHS"
Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION DO NOT ALTER CAD DRAWING BY HAND	Customer:			Tolerance Unless otherwise specified			Scale: 1.5:1	Dim. in Inch	
	Name	Title	Approval Date	Dimensional: Angles			Autodesk Inventor	Material: See Notes	
				2008	Date	Name	Title: RJ45 Cat. 5e Ethernet Patch Cord Standard to Standard RoHS Compliant		
				Draw.	Aug. 11	Vincent Ke			
				Appd.	Aug. 11	J. Chaudry			
				Norm					
				D-old					
	b		Feb/18/2009	Vincent ke			Drawing No.: 17K1A007		DIN A3
	a	original					Part No.: 17-100904		Sheet 1/1
	Rev.	Changes	Date	Name					