


Messleitungen / measuring leads

MLB 200/1 V



Produktbeschreibung	Product description		
Beschreibung	Description	Berührungsgeschützte Messleitung, beidseitig 4 mm Durchmesser Stecker, isoliert durch rastende und gefederte Isolierhülse, die nur durch Druck auf die seitliche Verriegelungsfeder freigegeben wird, sowie 4 mm Buchse für Turmsteckbauweise. Hochflexible, doppelt isolierte Litzenleitung. Eingearbeiteter Farbindikator zur Erkennung von Schäden an der Isolierung.	Contact-protected measuring lead, at either end: 4 mm diameter plug, insulated by latching and sprung insulated sleeve which is only released by pressure on the side mounted locking spring. 4 mm diameter nickel-plated. Highly flexible, double insulated stranded conductor. Color indicator for the recognition of damage to the insulation. 4 mm diameter socket for tower construction.
Typ	Type	MLB 200/1 V	MLB 200/1 V
Leitungslänge	Cable length	200 cm	200 cm
Leitungsquerschnitt	Conductor size	1 mm ²	1 mm ²
Gehäusefarbe / Artikel-Nr.	Housing color / article-no.	● 973 647-100 ● 973 647-101 ● 973 647-102 ● 973 647-103 ● 973 647-104	
Zeichnung	Drawing		
Technische Daten	Technical data		
Stiftdurchmesser	Pin dimensions	4 mm	4 mm
Kontaktart	Type of contact	gefedert Stift	spring-loaded pin
Leitungstyp	Cable type	LEH-XY	LEH-XY
Leitungsspezifikation	Cable specification	hochflexible Schlauchleitung	highly flexible lead
Litzenaufbau	Wire stranding	259 x 0,07 mm	259 x 0,07 mm
Bemessungsspannung	Rated voltage	30 VAC / 60 VDC	30 VAC / 60 VDC
Messkategorie lt. IEC61010	Measurement cat. acc. to IEC61010	CAT I	CAT I
Bemessungsstrom (Derating Kurve beachten)	Rated current (consider derating curve)	16 A	16 A
Durchgangswiderstand	Contact resistance	40 mOhm	40 mOhm
Werkstoff	Material		
Kontaktmaterial	Contact material	Kontaktstift: Messing Kontaktfeder: Kupfer-Beryllium	contact pin: brass contact spring: copper-beryllium
Kontaktflächenmaterial	Contact surface material	Nickel	nickel
Gehäusematerial	Housing material	PA	PA
Leitungsmaterial	Cable material	PVC	PVC
Umgebungsbedingungen	Environmental conditions		
Temperaturbereich	Temperature range	-15°C bis +70°C	-15°C to +70°C
Brennbarkeitsklassen	Inflammability class		
Gehäuse (Grundmaterial)	Housing (basic material)	UL 94 V-2	UL 94 V-2