

Shock-Safe Fuseholder, 5 x 20 mm, Fingergrip, NF



250 VAC · 3.4 W/6.3 A (NF)

GAM
T1 NNO**Description**

- IP 68 from front-side
- Screw type fuse carrier

Standards

- NF C 93-436 - Model HB13
- Contrôle de Conformité de Qualité (CCQ)



References
[General Product Information](#)
Weblinks
[Approvals](#), [RoHS](#), [CHINA-RoHS](#), [e-Store](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#)
Technical Data

Fuse-Link	5 x 20 mm
Mounting	Panel Mount, Front-Side
Fastening	Fixing Nut
Terminal	Solder
Rated Voltage	250 VAC
Rated Current	6.3 A (NF)
Rated Power Acceptance IEC	3.4 W / 6.3 A @ Ta 23 °C
Degree of Protection	IP 68
Admissible Ambient Air Temp.	-40 °C to 125 °C
Climatic Category	40/125/56 acc. to IEC 60068-1
Material: Socket	Thermoset, black
Unit Weight (Socket/Cap)	25 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	Type, Voltage Rating, Current Rating

Soldering Methods	Iron
Resistance to Vibration	acc. to NF C 20-706 / IEC 60068-2-6, test Fc
Shocks	acc. to NF C 20-706 / IEC 60068-2-27
Bumps	acc. to NF C 20-729 / IEC 60068-2-29
Salt Mist	acc. to NF C 20-711 / IEC 60068-2-11
Dump Heat	acc. to NF C 20-604
Climatic Composite	acc. to NF C 20-619 Phase D
Admissible Torque on Fixing Nut	max 1.0 Nm
Panel Thickness s	max 4 mm

Dimensions

Length | 41 mm



Mounting holes

Variants
[Distributor-Stock-Check](#) | [SCHURTER-Stock-Check](#) | [e-Store](#)

Holder	Cap	Degree of Protection	Order Number
●	Fingergrip	IP 68	7091.6110

Packaging Unit Bulk (10 pcs.)