


Glass Passivated Junction Fast Switching Rectifier

Reverse Voltage 50 to 1000V
Forward Current 2.5A

Features

- Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- High temperature metallurgically bonded construction
- Cavity-free glass passivated junction
- 2.5 Ampere operation at $T_A=55^\circ\text{C}$ with no thermal runaway
- Typical I_R less than $0.2\mu\text{A}$
- Capable of meeting environmental standards of MIL-S-19500
- High temperature soldering guaranteed: $350^\circ\text{C}/10$ seconds, $0.375"$ (9.5mm) lead length, 5 lbs. (2.3kg) tension

Mechanical Data

Case: JEDEC DO-201AD, molded plastic over glass body**Terminals:** Plated axial leads, solderable per MIL-STD-750, Method 2026**Polarity:** Color band denotes cathode end**Mounting Position:** Any**Weight:** 0.04 oz., 1.12 g**Packaging codes/options:**1/Bulk - 1.5K per container, 15K per box
4/1.4K per 13" reel, 5.6K per box
23/1K per Ammo. mag., 9K per box

Dimensions in inches and (millimeters)

*Glass-plastic encapsulation technique is covered by
Patent No. 3,996,602 and brazed-lead assembly by Patent No. 3,930,306

Maximum Ratings & Thermal Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	RGP 25A	RGP 25B	RGP 25D	RGP 25G	RGP 25J	RGP 25K	RGP 25M	Unit
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current $0.375"$ (9.5mm) lead length at $T_A=55^\circ\text{C}$	$I_{F(AV)}$	2.5							A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	100							A
Maximum full load reverse current, full cycle average $0.375"$ (9.5mm) lead length at $T_A=55^\circ\text{C}$	$I_{R(AV)}$	100							μA
Typical thermal resistance ⁽¹⁾	$R_{\theta JA}$	20							$^\circ\text{C}/\text{W}$
Operating junction and storage temperature range	T_J, T_{STG}	-65 to +175							$^\circ\text{C}$





Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Maximum instantaneous forward voltage at 2.5A	V _F	1.3			V
Maximum DC reverse current at rated DC blocking voltage T _A =25°C T _A =125°C	I _R	5.0 200			μA
Maximum reverse recovery time I _F =0.5A, I _R =1.0A, I _{rr} =0.25A	t _{rr}	150	250	500	ns
Typical junction capacitance at 4.0V, 1MHz	C _J	60			pF

Notes: (1) Thermal resistance from junction to ambient at $0.375"$ (9.5mm) lead length, P.C.B. mounted

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig. 1 - Forward Derating Curve**Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current****Fig. 3 - Typical Instantaneous Forward Characteristics****Fig. 4 - Typical Reverse Characteristics****Fig. 5 - Typical Junction Capacitance**