





1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
2. MATES WITH PLUG P/N 770587-1.
3. COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
4. RECOMMENDED FOR EDGE MOUNTING.
5. 0.00381 MIN MATTE TIN LEAD OVER 0.00127 MIN NICKEL.
6. 0.00076 MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
7. 0.00381 MIN MATTE TIN OVER 0.00127 MIN NICKEL.
8. 0.00076 MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA, 0.00381 MIN MATTE TIN IN THE LOCALIZED TIN PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

BRASS	GOLD		NYLON, UL94V-0	WHITE	1-794108-1
BRASS	TIN		NYLON, UL94V-0	WHITE	1-794108-0
BRASS	GOLD		NYLON, UL94V-0	WHITE	794108-2
BRASS	TIN-LEAD		NYLON, UL94V-0	WHITE	794108-1
MATERIAL	FINISH		MATERIAL	COLOR	PART NO.
PIN		HOUSING			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN S. CARPENTER 24JUL03 CHK C. JONES 24JUL03		HOUSING  TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: PRODUCT SPEC — APPLICATION SPEC — ANGLES — ±		NAME HEADER ASSEMBLY, RIGHT ANGLE, W/SHORT PEG.24 CIRCUIT, MINI UNIVERSAL MATE-N-LOK(TM)	
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT —	
		CUSTOMER DRAWING		SIZE A1	
				CAGE CODE 00779	
				DRAWING NO C-794108	
				RESTRICTED TO —	
				SCALE 5:1	
				SHEET 1 of 1	
				REV D	