

Technical drawing of a rectangular metal plate, showing multiple views and dimensions in millimeters (mm) and inches (in).

Top View:

- Overall width: 260 (10.236)
- Overall height: 160 (6.299)
- Inner width: 240 (9.449)
- Inner height: 140 (5.512)
- Four (4) M4 X 32 Flat Head Screws
- Section A-A is indicated.

Bottom View:

- Overall width: 260 (10.236)
- Overall height: 160 (6.299)
- Inner width: 240 (9.449)
- Inner height: 140 (5.512)
- Section B-B is indicated.

Section A-A (Scale 1:3):

- Overall width: 260 (10.236)
- Overall height: 160 (6.299)
- Inner width: 240 (9.449)
- Inner height: 140 (5.512)
- Section A-A is indicated.

Section B-B (Scale 1:3):

- Overall width: 260 (10.236)
- Overall height: 160 (6.299)
- Inner width: 240 (9.449)
- Inner height: 140 (5.512)
- Section B-B is indicated.

Section C-C (Scale 1:3):

- Overall width: 260 (10.236)
- Overall height: 160 (6.299)
- Inner width: 240 (9.449)
- Inner height: 140 (5.512)
- Section C-C is indicated.

Dimensions:

- Overall width: 260 (10.236)
- Overall height: 160 (6.299)
- Inner width: 240 (9.449)
- Inner height: 140 (5.512)
- Section A-A: 260 (10.236) x 160 (6.299)
- Section B-B: 260 (10.236) x 160 (6.299)
- Section C-C: 260 (10.236) x 160 (6.299)


Tolerances: ± 0.30 (± 0.012)

Dimensions : Millimetres

Box Diecast



G105




Tolerances : ± 0.30 (± 0.012)

Dimensions : Millimetres

Box Diecast



G110




Tolerances : $\pm 0.30 (\pm 0.012)$

Dimensions : Millimetres


Box Diecast



G118



G112



Tolerances : ± 0.30 (± 0.012)

Dimensions : Millimetres

Part Number Table

Description	Part Number
Box, Diecast, 31 × 55.5 × 41mm	G105
Box, Diecast, 52 × 79.6 × 74.6mm	G110
Box, Diecast, 25.5 × 102.5 × 52.5mm	G112
Box, Diecast, 60 × 175 × 80mm	G118
Box, Diecast, 75 × 200 × 120mm	G123
Box, Diecast, 90.5 × 260 × 160mm	G155

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.