




- | | | | | | | | | |
|----------|-------|---------|-------|---------|-------|---------|-----------------|-------------|
| TIN | 91.14 | [3.588] | 95.20 | [3.748] | 99.06 | [3.900] | 24 | 5-641436-4 |
| | 55.47 | [2.184] | 59.54 | [2.344] | 63.40 | [2.496] | 15 | 4-641436-5 |
| | 43.59 | [1.716] | 47.65 | [1.876] | 51.51 | [2.028] | 12 | 4-641436-2 |
| | 31.70 | [1.248] | 35.76 | [1.408] | 39.62 | [1.560] | 9 | 3-641436-9 |
| | 19.81 | [.780] | 23.88 | [.940] | 27.74 | [1.092] | 6 | 3-641436-6 |
| | 11.89 | [.468] | 15.95 | [.628] | 19.81 | [.780] | 4 | 3-641436-4 |
| | 7.92 | [.312] | 11.99 | [.472] | 15.85 | [.624] | 3 | 3-641436-3 |
| | 3.96 | [.156] | 8.03 | [.316] | 11.89 | [.468] | 2 | 3-641436-2 |
| TIN-LEAD | 91.14 | [3.588] | 95.20 | [3.748] | 99.06 | [3.900] | 24 | 2-641436-4 |
| | 55.47 | [2.184] | 59.54 | [2.344] | 63.40 | [2.496] | 15 | 1-641436-5 |
| | 43.59 | [1.716] | 47.65 | [1.876] | 51.51 | [2.028] | 12 | 1-641436-2 |
| | 31.70 | [1.248] | 35.76 | [1.408] | 39.62 | [1.560] | 9 | 641436-9 |
| | 19.81 | [.780] | 23.88 | [.940] | 27.74 | [1.092] | 6 | 641436-6 |
| | 11.89 | [.468] | 15.95 | [.628] | 19.81 | [.780] | 4 | 641436-4 |
| | 7.92 | [.312] | 11.99 | [.472] | 15.85 | [.624] | 3 | 641436-3 |
| | 3.96 | [.156] | 8.03 | [.316] | 11.89 | [.468] | 2 | 641436-2 |
| FINISH | C | | B | | A | | NO. OF CIRCUITS | PART NUMBER |



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN. 10-22-91 K. SALMON CHK. 10-22-91 R. SWING		TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± . 1 PLC ± .013 [.005] 2 PLC ± . 3 PLC ± . 4 PLC ± . ANGLES ± . FINISH		PRODUCT SPEC POSTED CONNECTOR ASSEMBLY, 20 AWG	
MATERIAL SEE NOTE 1		APPLICATION SPEC WEIGHT —		SIZE CAGE CODE DRAWING NO A1 00779 C-641436	
SEE NOTE 1		CUSTOMER DRAWING		RESTRICTED TO — SCALE 5:1 SHEET 1 OF 1 REV H	