




NOTES:

- 1 - BLACK PLASTIC HOUSING AND PLUNGER
- 2 - HOUSING HAS BOSS AROUND PLUNGER TO MEET BSI AND VDE AGENCY
8,00/.315 CLEARANCE REQUIREMENT

③ OPERATING POSITIONS:

CIRCUIT 11-12 - - - 8,26±0,99/.325±.039


CIRCUIT 31-32 - - - 8,99±0,99/.354±.039

④ SEQUENCE ACTION: CIRCUIT 11-12 OPENS BEFORE CIRCUIT
31-32 ON RELEASE OF PLUNGER FROM FULL OVERTRAVEL.

CIRCUIT 21-22 OPENS AT 11,91±0,99/.469±.039

⑤ QUICK CONNECT TERMINALS CONFORM TO 4,78/.188 WIDE X
0.81/.032 THICK NEMA DC-2 SPECIFICATION

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		
MICRO SWITCH a Honeywell Division FED. REG. CODE 81929	SWITCH - BASIC	CATALOG LISTING WW4K01C-D7

THIRD ANGLE PROJECTION			
			
SCALE 2:1			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE :			
	DIM. mm	TOL. mm ±	
NO. PLACE	X	1 / 0.04	X
ONE PLACE	X.X	0.4 / 0.016	X.XX
TWO PLACES	X.XX	0.15 / 0.006	X.XXX
THREE PLACES			
ANGLES			5°
SI METRIC		US CUSTOMARY	
			
WEIGHT			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[WW4K01C-D7](#)