

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 35.20 USD



## Main

Device short name	FHG
Enclosure type	Standard environment enclosure indoor
Factory modification	2-way pressure release valve
Product specific application	Control small electrically driven air compressors
Range of product	Square D Pumptrol

## Complementary

Adjustable range on rising pressure	40...100 psi (275.79...689.48 kPa)
Approximate fixed differential	20 psi (137.90 kPa)
Contact code designation	A600
Maximum Depth	2.78 in (70.61 mm)
Electrical connection	Screw clamp terminal
Fixing mode	By brackets
Fluid connection type	0.375 inch NPSF internal
Height	2.8 in (71.12 mm)
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	220 psig
Maximum Horse Power Rating	7.5 hp 115 V AC, 1 phase 2 hp 115 V AC, 3 phase 2 hp 230 V AC, 1 phase 3 hp 230 V AC, 3 phase 1 hp 460/575 V AC, 3 phase
Number of poles	2
Permissible voltage	575 V AC
Pressure actuator	Diaphragm
Pressure setting range	100 psi (689.48 kPa) off
Net weight	1.13 lb(US) (0.51 kg)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Aug 16, 2020

Scale type	Fixed differential
Switch function	DPST
Width	3.76 in (95.50 mm)

## Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed file E12158 CCN NKPZ CSA LR25490 class 3211 06

## Ordering and shipping details

Category	21533 - 9013 FHG (INDIVIDUAL-DISCOUNT CP7I)
Discount Schedule	CP7I
GTIN	00785901320388
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	MX

## Packing Units

Package 1 Height	10.16 in (25.806 cm)
Package 1 width	4.00 in (10.160 cm)
Package 1 Length	25.81 in (65.548 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------