


MATERIAL NO.	ENGINEERING NO.	LENGTH
1300140078	2R8006A20A120	12' +.75-0 [305mm +19.0-0]
1300140084	2R8006A20F060	6'0" +2.19 [1.8M +55.6-0]


ø .88
22.4



REF. KNOCK-OUT HOLE

1/2-14 NPT

1"-16 THREAD




LENGTH
(SEE CHART)

8.00
203.2


REF

1.52
38.5

REF



Section 1-1



1	ORANGE
2	BLUE
3	WHITE/BLACK
4	BLACK
5	WHITE
6	RED
7	GREEN/YELLOW-GND
8	RED/BLACK

- NOTES:
1. MATERIAL: SEE TABLE
 2. FINISHES: SEE TABLE
 3. MATES WITH: 8/C MINI-CHANGE CORD ASSY.
 4. ELECTRICAL SPECIFICATIONS:
VOLTAGE RATING: 600V AC/DC
CURRENT RATING: 7 AMPS
 5. RoHS COMPLIANT

6	1	LABEL	PLASTIC FILM	BLACK/YELLOW
5	1	POTTING	EPOXY	
4	8	WIRE, 16 AWG (UL 1015)	PVC INSULATED	SEE WIRE DIAGRAM
3	8	CONTACT PIN	BRASS	GOLD PLATED
2	1	INSERT	PVC	YELLOW
1	1	RECEPTACLE SHELL	ZINC ALLOY	E-COAT, BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

RELEASED
EC NO: WNA2009-0813
2009/06/09
DRWN:BRUPERT
CHKD:BRUPERT
APPR:JFMURPHY
2009/06/10

QUALITY
SYMBOLS
=0
=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .0005
1 PLACE	± .005	± .0005

ANGULAR ±1/2°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY
R.STONE

DATE
2009/04/03

CHECKED BY
B.WOODMAN

DATE
2009/04/03

APPROVED BY
J.MURPHY

DATE
2009/04/07

MATERIAL NO.
SEE CHART

SIZE
C

SCALE
1:1

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

TITLE
MINI-CHANGE RECEPTACLE
MALE, 8 POLE
1/2 IN NPT

MOLEX INCORPORATED

DOCUMENT NO.
SD-130014-005

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION