





1. WILL ACCEPT (12) MULTIMATE AND (4) TYPE XII PIN CONTACTS.
2. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
3. NO. 4 FASTENERS RECOMMENDED FOR MOUNTING.
4. THIS CONNECTOR WILL ACCEPT INSULATION DIAMETERS UP TO 3.81 [.150].
5. HOUSING: NYLON, BLACK.
6. PERIPHERAL SEAL: ELASTOMER, GRAY.
7. PERMANENT WHITE MARKED OR WHITE INK STAMPED CAVITY IDENTIFICATION.
8. HOUSING: NYLON, RED.
9. PERIPHERAL SEAL: ELASTOMER, GRAY.
10. WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.

OBSOLETE	8	—	YES	A	1-207486-1
OBSOLETE	7	—	YES	A	207486-9
PRELIMINARY	6	—	YES	A	207486-7
	5	4	YES	A	207486-6
	4	—	YES	A	207486-5
	3	—	NO	B	207486-2
	2	—	NO	A	207486-1
NOTES	THREADED INSERTS	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

5 7

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN M. BINNER 05/26/94
CHK R. STONE 6-23-94
APVD -
PRODUCT SPEC 108-10024
APPLICATION SPEC -
WEIGHT -
CUSTOMER DRAWING

TE Connectivity
RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC
-
SIZE CAGE CODE DRAWING NO
A1 00779 207486
RESTRICTED TO -
SCALE 2:1 SHEET 1 OF 1 REV R