






SECTION C-C SHOWING STRAIGHT PINS

NOTES

- CONTACT-PLATED PHOSPHOR BRONZE.
(SEE SHEET 2)
- HOUSING
POLYESTER (PBT), 15% GLASS FILL, UL94-V0.
COLOR: BLACK.
ALSO
POLYAMIDE (PA4/6), 30% GLASS FILL, UL94-V0.
COLOR: NATURAL.
- FOR (0.635) ± .025 SQ. MALE PINS THE LENGTH MUST BE (5.65) ± .222 MIN & (7.00) ± .276 MAX. TO ENSURE GOOD CONNECTION WITH CONTACT.
- PRODUCT SPECIFICATION: PS-99020-0001
- PCB THICKNESS 1.6MM

UPDATE TOL. SYMMETRY		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO:	DATE	DRWN:	DATE	mm	INCH	MM ONLY	DATE	NTS	METRIC	METRIC			
S2010-0968	2010/05/26	SKANG	2010/06/04	4 PLACES	± ---	± ---	DB	1987/07/14					
CHKD:	2010/06/04	ATSEE		3 PLACES	± ---	± ---	CHECKED BY	DATE					
APPR:	2010/06/05	MLONG		2 PLACES	± 0.15	± ---	D. MORIARTY	2005/03/02					
REV				1 PLACE	± ---	± ---	APPROVED BY	DATE					
				ANGULAR ± 2 °			J. DENNEHY	2010/06/04					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.						
							SEE TABLE						
							SIZE A3						
							THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

F

E

D

C

B

A

PART NO's - STRAIGHT PINS		PART NO.	NO OF CKTS.	DIM. A	DIM. B ^(+0.30) _{-0.02}	NO. PER TUBE
STANDARD	CUSTOMER SPECIFIC					
90148-1X02		90148-4X02	2	(2.54) .100	(5.08) .200	105
↑	↑ 03	↑	↑ 03	3 (5.08) .200	(7.62) .300	72
	04		04	4 (7.62) .300	(10.16) .400	52
	05		05	5 (10.16) .400	(12.70) .500	44
	06 90148-9X06		06	6 (12.70) .500	(15.24) .600	36
	07		07	7 (15.24) .600	(17.78) .700	30
	08		08	8 (17.78) .700	(20.32) .800	26
	09		09	9 (20.32) .800	(22.86) .900	24
	10		10	10 (22.86) .900	(25.40) 1.000	22
	11		11	11 (25.40) 1.000	(27.94) 1.100	18
	12		12	12 (27.94) 1.100	(30.48) 1.200	18
	13		13	13		16
	14		14	14 (33.02) 1.300	(35.56) 1.400	14
	15		15	15 (35.56) 1.400	(38.10) 1.500	14
	16		16	16		13
	17		17	17		12
	18		18	18 (43.18) 1.700	(45.72) 1.800	12
	19		19	19 (45.72) 1.800	(48.26) 1.900	12
	20		20	20 (48.26) 1.900	(50.80) 2.000	11
	21		21	21		10
	22		22	22		10
	23		23	23		10
	24		24	24		9
	25		25	25 (60.96) 2.400	(63.50) 2.500	8
	26		26	26 (63.50) 2.500	(66.04) 2.600	8
	27		27	27		8
	28		28	28		7
	29		29	29		7
	30		30	30 (73.66) 2.900	(76.20) 3.000	7
	↓ 31		↓ 31	31		7
90148-1X32		90148-4X32	32	(78.74) 3.100	(81.28) 3.200	6

PLATING VERSION A

PRE-PLATED HOT DIP TIN
1.0 TO 2.5 microns (.00004" TO .00010").

PLATING VERSION E

1.27 TO 1.78 microns (.00005" TO .00007") NICKEL
OVERALL, 0.38 TO 0.64 microns (.000015" TO .000025")
GOLD ON CONTACT AREA (OVER NICKEL).
3 TO 5 microns (.00012" TO .00020") TIN
ON SOLDER TAILS (OVER NICKEL).

PLATING VERSION F.

1.27 TO 1.78 microns (.00005" TO .00007") NICKEL
OVERALL, 0.76 TO 1.0 microns (.00003" TO .00004")
GOLD ON CONTACT AREA (OVER NICKEL).
3 TO 5 microns (.00012" TO .00020") TIN
ON SOLDER TAILS (OVER NICKEL).

90148-XXYY

INDICATES NO. OF CIRCUITS

PLATING CODE
1 = VERSION A
2 = VERSION E
3 = VERSION F

1 = STRAIGHT PINS POLYESTER
9 = STRAIGHT PINS POLYESTER
4 = STRAIGHT PINS NYLON 46

UPDATE TOL.SYMMETRY EC NO: S2010-0968 2010/05/26 DRWN:SKANG CHKD:ATSEE 2010/06/04 APPR:MLONG 2010/06/05	DESCRIPTION	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY DB	DATE 1987/07/14	TITLE C-GRID III SINGLE ROW HORIZONTAL P.C BOARD CONN.	
			4 PLACES	± ---	± ---	CHECKED BY	DATE		
			3 PLACES	± ---	± ---	D.MORIARTY	2005/03/02	 MOLEX INCORPORATED	
			2 PLACES	± 0.15	± ---	APPROVED BY	DATE		
1 PLACE	± ---	± ---	J.DENNEHY	2010/06/04	MATERIAL NO.	DOCUMENT NO. SDA-90148	SHEET NO. 2 OF 3		
AK	REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE				
					SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

PART NO.	POLARISED CCT NO.	NO.OF CKTS.	DIM. A	DIM. B	(± 0.30) (± 0.12)	NO. PER TUBE
90148-3X01	2	3	(5.08) .200	(7.62) .300		72


NON-STANDARD PRODUCTS

90148-XXXX


OPTION NUMBER
(NOT RELATING TO CCT SIZE OR OTHERWISE)

PLATING CODE (SEE SHEET 2)

3 = STRAIGHT PINS POLYESTER, POLARISED



SECTION C-C SHOWING POLARISED CCT



- NOTES
- 1) SEE SHEET 1 FOR ALL UNSPECIFIED DIMENSIONS AND NOTES.
- 2) PARTS NOT STACKABLE.

UPDATE TOL.SYMMETRY	EC NO: S2010-0968	2010/05/26	2010/06/04	2010/06/05	DESCRIPTION	REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
										MM ONLY		NTS	METRIC			
										DRAWN BY		DATE	TITLE			
										DB		1987/07/14	C-GRID III SINGLE ROW			
										CHECKED BY		DATE	HORIZONTAL			
										D.MORIARTY		2005/03/02	P.C BOARD CONN.			
										APPROVED BY		DATE	MOLEX MOLEX INCORPORATED			
										J.DENNEHY		2010/06/04	SDA-90148			
										MATERIAL NO.		DOCUMENT NO.	SHEET NO.			
										SEE TABLE		3 OF 3				
		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
		A3														

PART NO's - STRAIGHT PINS		PART NO.	NO OF CKTS.	DIM. A	DIM. B $(\pm \frac{0.30}{32})$	NO. PER TUBE
STANDARD	CUSTOMER SPECIFIC					
90148-1X02		90148-4X02	2	(2.54) .100	(5.08) .200	105
↑ 03	↑	↑ 03	3	(5.08) .200	(7.62) .300	72
04	↓	04	4	(7.62) .300	(10.16) .400	52
05		05	5	(10.16) .400	(12.70) .500	44
06	90148-9X06	06	6	(12.70) .500	(15.24) .600	36
07	↑	07	7	(15.24) .600	(17.78) .700	30
08		08	8	(17.78) .700	(20.32) .800	26
09		09	9	(20.32) .800	(22.86) .900	24
10		10	10	(22.86) .900	(25.40) 1.000	22
11		11	11	(25.40) 1.000	(27.94) 1.100	18
12		12	12	(27.94) 1.100	(30.48) 1.200	18
13		13	13			16
14		14	14	(33.02) 1.300	(35.56) 1.400	14
15		15	15	(35.56) 1.400	(38.10) 1.500	14
16		16	16			13
17		17	17			12
18		18	18	(43.18) 1.700	(45.72) 1.800	12
19		19	19	(45.72) 1.800	(48.26) 1.900	12
20		20	20	(48.26) 1.900	(50.80) 2.000	11
21		21	21			10
22		22	22			10
23		23	23			10
24		24	24			9
25		25	25	(60.96) 2.400	(63.50) 2.500	8
26		26	26	(63.50) 2.500	(66.04) 2.600	8
27		27	27			8
28		28	28			7
29		29	29			7
30		30	30	(73.66) 2.900	(76.20) 3.000	7
↓ 31	↓	↓ 31	31			7
90148-1X32		90148-4X32	32	(78.74) 3.100	(81.28) 3.200	6

PLATING VERSION A

PRE-PLATED HOT DIP TIN
1.0 TO 2.5 microns (.00004" TO .00010").

PLATING VERSION E

1.27 TO 1.78 microns (.00005" TO .00007") NICKEL
OVERALL, 0.38 TO 0.64 microns (.000015" TO .000025")
GOLD ON CONTACT AREA (OVER NICKEL).
3 TO 5 microns (.00012" TO .00020") TIN
ON SOLDER TAILS (OVER NICKEL).

PLATING VERSION F.

1.27 TO 1.78 microns (.00005" TO .00007") NICKEL
OVERALL, 0.76 TO 1.0 microns (.00003" TO .00004")
GOLD ON CONTACT AREA (OVER NICKEL).
3 TO 5 microns (.00012" TO .00020") TIN
ON SOLDER TAILS (OVER NICKEL).

90148-XXXX

INDICATES NO. OF CIRCUITS

PLATING CODE

1 = VERSION A

2 = VERSION E

3 = VERSION F

1 = STRAIGHT PINS POLYESTER
9 = STRAIGHT PINS POLYESTER

4 = STRAIGHT PINS NYLON 46

ADD NEW P/N EC NO: E2007-0823 DRWN:DBYRNES CHKD: APPR:EOMAHONY 2007/03/29 2007/03/29 2007/04/04	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		4 PLACES	± ---	INCH	± ---	DRAWN BY DB	DATE 1987/07/14	C-GRID III SINGLE ROW HORIZONTAL P.C. BOARD CONNECTOR			
		3 PLACES	± ---	± ---	± ---	CHECKED BY D.MORIARTY	DATE				
		2 PLACES	± ---	± ---	± ---	APPROVED BY J.DENNEHY	DATE	MOLEX INCORPORATED			
		1 PLACE	± ---	± ---	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
		ANGULAR ± ---°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SDA-90148		2 OF 3	
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					