


|                                                       |     |               |               |                          |           |  |                    |
|-------------------------------------------------------|-----|---------------|---------------|--------------------------|-----------|--|--------------------|
| 8                                                     |     |               |               | 7                        |           |  |                    |
| THIS DRAWING IS UNPUBLISHED.                          |     |               |               | RELEASED FOR PUBLICATION |           |  |                    |
| COPYRIGHT 20                                          |     |               |               | 20                       |           |  |                    |
| BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED. |     |               |               |                          |           |  |                    |
| PART<br>NUMBER                                        | REV | FIRST<br>USED | POWER UNIT    |                          | FEED TYPE |  | DESCRIPTION        |
| 1852710-1                                             | A   | 122500-1      | LEADMAKER     |                          | POST FEED |  | CUTS CARRIER       |
| 1852710-2                                             | A   | 565435-5      | BENCH MODEL K |                          | PRE FEED  |  | CUTS CARRIER       |
| 1852710-3                                             | A   | 354500-1      | BENCH MODEL G |                          | PRE FEED  |  | CUTS CARRIER       |
| 1852710-6                                             | A   | 122500-1      | LEADMAKER     |                          | POST FEED |  | CONTINUOUS CARRIER |
| 7-1852710-7                                           | A   | -             | -             |                          | -         |  | SPARE PARTS        |

- △ RECOMMENDED SPARE PARTS
- △ GREASE LIGHTLY
- △ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE



|                                   |                        |                                        |                                     |      |                         |
|-----------------------------------|------------------------|----------------------------------------|-------------------------------------|------|-------------------------|
| TERMINAL NAME: NH FEMALE TERMINAL |                        |                                        |                                     |      |                         |
| SOCKET                            |                        | SUMITOMO TERMINAL-SUMITOMO CRIMP SPECS |                                     |      |                         |
| TE PN                             | SUMITOMO               | PAD LTR                                | CRIMP HEIGHT                        |      | WIRE SIZE               |
| 1949694                           | 8240-0180              | A                                      | .90mm+.05/- .05 [.035+.002/- .002]  |      | 0.5mm2                  |
| -                                 | -                      | B                                      | .80mm+.05/- .05 [.032+.002/- .002]  |      | 0.3mm2                  |
| -                                 | -                      | C                                      |                                     |      | -                       |
| PIN                               |                        | D                                      |                                     |      | -                       |
| TE PN                             | SUMITOMO               | CRIMP                                  | SIZE                                | TYPE | RANGE                   |
| 1949923-1                         | 8230-4877              |                                        |                                     |      |                         |
| -                                 | -                      | WIRE                                   | 1.40mm [.055]                       | F    | 0.30-0.50               |
| -                                 | -                      | INSUL                                  | 1.42mm [.056]                       | F    | Ø 1.524 MAX             |
| WIRE STRIP LENGTH<br>3.64-4.03    | TERM APPL SPEC<br>NONE | FEED<br>6.99                           | APPLICATOR INSTRUCTIONS<br>408-8040 |      | SET UP GAGE<br>458637-1 |

