






7LS1  
PAGE 1 OF 1  
M  
DRAWING NUMBER  
16  
ISSUE  
REVISIONS  
A CO-195463-B  
D L  
7 SEP 99  
FORMTEK  
FO-50378-003  
DRAWN  
L D 12 JUN 64  
CHECK  
P A W 24 JUNE 64  
CHECK  
P A W 24 JUNE 64  
CHECK  
REPLACES  
RELEASE NO.



CAM TRACKING VIEW

- NOTES
- 1-SWITCH IS ASSEMBLED FOR ACTUATION IN BOTH DIRECTIONS BUT MAY BE ADJUSTED TO ACTUATE IN EITHER THE CLOCKWISE DIRECTION ONLY OR THE COUNTERCLOCKWISE DIRECTION ONLY
  - 2- TO CONVERT SWITCH FOR ACTUATION IN EITHER THE CLOCKWISE OR COUNTERCLOCKWISE DIRECTION ONLY, REMOVE ACTUATOR HEAD AND ROTATE THE NOTCHED PLUNGER 90° TO THE RIGHT FOR CLOCKWISE ACTUATION OR 90° TO THE LEFT FOR COUNTER-CLOCKWISE ACTUATION
  - 3- ROLLER LEVER MAY BE LOCKED IN ANY POSITION THRU 360°
  - 4- LEVER FURNISHED UNASSEMBLED IN UNIT PACKING BOX

| THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH. |                                                                                                                                            |                          |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|
| CHARACTERISTICS                                                                                                                                                                                              | ELECTRICAL DATA                                                                                                                            | SCALE 1/2 TO 1           |
| OPERATING TORQUE ----- 4.5 IN-LB                                                                                                                                                                             | CONTACT ARRANGEMENT<br>(SEE CIRCUIT DIAGRAM)                                                                                               | DO NOT SCALE PRINT       |
| FULL OVERTRAVEL TORQUE----- 6 IN-LB                                                                                                                                                                          |                                                                                                                                            | UNLESS OTHERWISE NOTED   |
| RELEASE TORQUE----- .75 IN-LB                                                                                                                                                                                | 10A-120, 240, OR 480 VAC, 1/3 HP - 120 VAC<br>3/4 HP - 240 VAC; 0.8A - 115 VDC; 0.4A - 230 VDC<br>.1A - 550 VDC<br>PILOT DUTY: 600 VAC MAX | DIMENSIONS ARE IN INCHES |
| PRETRAVEL----- 20° MAX                                                                                                                                                                                       |                                                                                                                                            | TOLERANCES ARE:          |
| DIFFERENTIAL TRAVEL----- 12° MAX                                                                                                                                                                             |                                                                                                                                            | ONE PLACE (.0) ±.030     |
| OVERTRAVEL----- 30° MIN                                                                                                                                                                                      |                                                                                                                                            | TWO PLACE (.00) ±.015    |
| RELEASE TRAVEL----- 5° MIN                                                                                                                                                                                   |                                                                                                                                            | THREE PLACE (.000) ±.005 |
| SWITCH-BASIC REPLACEMENT ----- 2MNI                                                                                                                                                                          |                                                                                                                                            | ANGLES ±                 |
|                                                                                                                                                                                                              |                                                                                                                                            | WEIGHT                   |