


TRANSIENT VOLTAGE SUPPRESSORS

1500 Watts		BREAKDOWN VOLTAGE		at I_L (ma)	WORKING PEAK REVERSE VOLTAGE V_{RWM} (Volts)	MAXIMUM REVERSE LEAKAGE I_{R} (μ A)	PEAK PULSE CURRENT I_{PP} (Amps)	MAXIMUM CLAMPING VOLTAGE at I_{PP} V_C (Volts)	MAX VOLTAGE TEMP. VARIATION of V_{BR} (mv/°C)	PACKAGE QUANT. Bulk/Reel	OUTLINE Inches/Millimeters
JEDEC PART NUMBER	ISI PART NUMBER	V_{BR} (Volts) Min	Max								
1N6267	1.5KE6.8	6.12	7.48	10	5.50	1000	139.0	10.8	5	500/ 1400	
1N6267A	1.5KE6.8A	6.46	7.14	10	5.80	1000	143.0	10.5	5		
1N6268	1.5KE7.5	6.75	8.25	10	6.05	500	128.0	11.7	5		
1N6268A	1.5KE7.5A	7.13	7.88	10	6.40	500	132.0	11.3	5		
1N6269	1.5KE8.2	7.38	9.02	10	6.63	200	120.0	12.5	6		
1N6269A	1.5KE8.2A	7.79	8.61	10	7.02	200	124.0	12.1	6		
1N6270	1.5KE9.1	8.19	10.0	1.0	7.37	50	109.0	13.8	7		
1N6270A	1.5KE9.1A	8.65	9.55	1.0	7.78	50	112.0	13.4	7		
1N6271	1.5KE10	9.00	11.0	1.0	8.10	10	100.0	15.0	8		
1N6271A	1.5KE10A	9.50	10.5	1.0	8.55	10	103.0	14.5	8		
1N6272	1.5KE11	9.90	12.1	1.0	8.92	5.0	93.0	16.2	9		
1N6272A	1.5KE11A	10.5	11.6	1.0	9.40	5.0	96.0	15.6	9		
1N6273	1.5KE12	10.8	13.2	1.0	9.72	5.0	87.0	17.3	10		
1N6273A	1.5KE12A	11.4	12.6	1.0	10.2	5.0	90.0	16.7	10		
1N6274	1.5KE13	11.7	14.3	1.0	10.5	5.0	79.0	19.0	11		
1N6274A	1.5KE13A	12.4	13.7	1.0	11.1	5.0	82.0	18.2	11		
1N6275	1.5KE15	13.5	16.5	1.0	12.1	5.0	68.0	22.0	13		
1N6275A	1.5KE15A	14.3	15.8	1.0	12.8	5.0	71.0	21.2	12		
1N6276	1.5KE16	14.4	17.6	1.0	12.9	5.0	64.0	23.5	16		
1N6276A	1.5KE16A	15.2	16.8	1.0	13.6	5.0	67.0	22.5	14		
1N6277	1.5KE18	16.2	19.8	1.0	14.5	5.0	56.5	26.5	17		
1N6277A	1.5KE18A	17.1	18.9	1.0	15.3	5.0	59.5	25.2	19		
1N6278	1.5KE20	18.0	22.0	1.0	16.2	5.0	51.5	29.1	20		
1N6278A	1.5KE20A	19.0	21.0	1.0	17.1	5.0	54.0	27.7	19		
1N6279	1.5KE22	19.8	24.2	1.0	17.8	5.0	47.0	31.9	21		
1N6279A	1.5KE22A	20.9	23.1	1.0	18.8	5.0	49.0	30.6	19		
1N6280	1.5KE24	21.6	26.4	1.0	19.4	5.0	43.0	34.7	15		
1N6280A	1.5KE24A	22.8	25.2	1.0	20.5	5.0	45.0	33.2	23		
1N6281	1.5KE27	24.3	29.7	1.0	21.8	5.0	38.5	39.1	28		
1N6281A	1.5KE27A	25.7	28.4	1.0	23.1	5.0	40.0	37.5	25		
1N6282	1.5KE30	27.0	33.0	1.0	24.3	5.0	34.5	43.5	31		
1N6282A	1.5KE30A	28.5	31.5	1.0	25.6	5.0	36.0	41.4	28		
1N6283	1.5KE31	29.7	35.3	1.0	26.8	5.0	31.5	47.7	31		
1N6283A	1.5KE31A	31.4	34.7	1.0	28.2	5.0	33.0	45.7	30		
1N6284	1.5KE36	32.4	39.6	1.0	29.1	5.0	29.0	52.0	35		
1N6284A	1.5KE36A	34.2	37.8	1.0	30.8	5.0	30.0	49.9	31		
1N6285	1.5KE39	35.1	42.9	1.0	31.6	5.0	26.5	56.4	39		
1N6285A	1.5KE39A	37.1	41.0	1.0	33.3	5.0	28.0	53.9	36		
1N6286	1.5KE43	38.7	47.3	1.0	34.8	5.0	24.0	61.9	46		
1N6286A	1.5KE43A	40.9	45.2	1.0	36.8	5.0	25.3	59.3	44		
1N6287	1.5KE47	42.3	51.7	1.0	38.1	5.0	22.2	67.8	50		
1N6287A	1.5KE47A	44.7	49.4	1.0	40.2	5.0	23.2	64.8	48		
1N6288	1.5KE51	45.9	56.1	1.0	41.3	5.0	20.4	73.5	55		
1N6288A	1.5KE51A	48.5	53.6	1.0	43.6	5.0	21.4	70.1	51		
1N6289	1.5KE58	50.4	61.8	1.0	45.4	5.0	18.6	80.5	58		
1N6289A	1.5KE58A	53.2	58.8	1.0	47.8	5.0	19.5	77.0	56		
1N6290	1.5KE62	55.8	68.2	1.0	50.2	5.0	16.9	89.0	65		
1N6290A	1.5KE62A	58.9	65.1	1.0	53.0	5.0	17.7	85.0	62		
1N6291	1.5KE68	61.2	74.8	1.0	55.1	5.0	15.3	98.0	71		
1N6291A	1.5KE68A	64.6	71.4	1.0	58.1	5.0	16.3	92.0	69		
1N6292	1.5KE75	67.5	82.5	1.0	60.7	5.0	13.9	108.0	80		
1N6292A	1.5KE75A	71.3	78.8	1.0	64.1	5.0	14.6	103.0	76		
1N6293	1.5KE82	73.8	90.2	1.0	66.4	5.0	12.7	118.0	90		
1N6293A	1.5KE82A	77.9	86.1	1.0	70.1	5.0	13.3	113.0	86		
1N6294	1.5KE91	81.9	100.0	1.0	73.7	5.0	11.4	131.8	99		
1N6294A	1.5KE91A	86.5	95.5	1.0	77.8	5.0	12.0	125.0	94		
1N6295	1.5KE100	90.0	110.0	1.0	81.0	5.0	10.4	144.0	109		
1N6295A	1.5KE100A	95.0	105.0	1.0	85.5	5.0	11.0	137.0	104		
1N6296	1.5KE110	99.0	121.0	1.0	89.2	5.0	9.5	158.0	120		
1N6296A	1.5KE110A	105.0	116.0	1.0	94.0	5.0	9.9	152.0	115		
1N6297	1.5KE120	108.0	132.0	1.0	97.2	5.0	8.7	173.0	131		
1N6297A	1.5KE120A	114.0	126.0	1.0	102.0	5.0	9.1	165.0	125		
1N6298	1.5KE130	117.0	143.0	1.0	105.0	5.0	8.0	187.0	142		
1N6298A	1.5KE130A	124.0	137.0	1.0	111.0	5.0	8.4	179.0	136		
1N6299	1.5KE150	135.0	165.0	1.0	121.0	5.0	7.0	215.0	164		
1N6299A	1.5KE150A	143.0	158.0	1.0	128.0	5.0	7.2	207.0	157		
1N6300	1.5KE180	144.0	176.0	1.0	130.0	5.0	6.5	230.0	175		
1N6300A	1.5KE180A	152.0	168.0	1.0	136.0	5.0	6.8	219.9	167		
1N6301	1.5KE170	153.0	187.0	1.0	138.0	5.0	6.2	244.0	186		
1N6301A	1.5KE170A	162.0	179.0	1.0	145.0	5.0	6.4	234.0	188		
1N6302	1.5KE180	162.0	198.0	1.0	146.0	5.0	5.8	258.0	197		
1N6302A	1.5KE180A	171.0	189.0	1.0	154.0	5.0	6.1	246.0	188		
1N6303	1.5KE200	180.0	220.0	1.0	162.0	5.0	5.2	287.0	219		
1N6303A	1.5KE200A	190.0	210.0	1.0	171.0	5.0	5.5	274.0	209		
	1.5KE220	198.0	242.0	1.0	175.0	5.0	4.3	344.0	240		
	1.5KE220A	209.0	231.0	1.0	185.0	5.0	4.6	328.0	230		
	1.5KE250	225.0	275.0	1.0	202.0	5.0	5.0	360.0	270		
	1.5KE250A	237.0	263.0	1.0	214.0	5.0	5.0	344.0	260		
	1.5KE300	270.0	330.0	1.0	243.0	5.0	5.0	430.0	330		
	1.5KE300A	285.0	315.0	1.0	256.0	5.0	5.0	414.0	315		
	1.5KE350	315.0	385.0	1.0	284.0	5.0	4.0	504.0	385		
	1.5KE350A	332.0	368.0	1.0	300.0	5.0	4.0	482.0	368		
	1.5KE400	360.0	440.0	1.0	324.0	5.0	4.0	574.0	440		
	1.5KE400A	380.0	420.0	1.0	342.0	5.0	4.0	548.0	420		
	1.5KE440	396.0	484.0	1.0	356.0	5.0	4.0	631.0	460		
	1.5KE440A	418.0	462.0	1.0	376.0	5.0	4.0	603.0	440		