



ISORATE®
ISOLATED EDGE RATE CONTACT

(4.00 mm) .1575"

IJ5H-02-0600-S-2-02SP2

IJ5H-08-0300-S-2-03SP2

IJ5H SERIES

50 Ω HYBRID RF CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?IJ5H

Insulator Material:

Black LCP

Contact Material:

Copper Alloy

Pin Material:

Copper Alloy

Dielectric Material:

Black LCP

Plating:

Au over 50 μ" (1.27 μm) Ni

Operating Temp Range:

-40 °C to +90 °C

RoHS Compliant:

Yes

Cable (-2):

Conductor Size:

26 AWG,

(0.51 mm) .020" dia.

Conductor Material:

Silver and Copper

Plated Steel Wire

Insulator Diameter:

(1.52 mm) .060"

Insulator Material:

PTFE

Shield Material:

Silver Plated Copper Wire

Jacket Material:

FEP

Jacket Diameter:

(2.54 mm) .100"

Bend Radius:

12.7 mm

Impedance:

50 Ω

Current Rating:

5A DC

RoHS Compliant:

Yes

Mates with:

IP5, SMA, MCX, MMCX,
SMB5

Low-cost isolated
transmission line
system

RG 316 Cable

Positive
latching

1, 2, 4, 6 or 8
Positions

Choice of traditional
RF end options

**EDGE
RATE®**
CONTACT

IJ5H

**NO. OF
POSITIONS**

**ASSEMBLED
LENGTH**

**END 1
PLATING**

**CABLE
TYPE**

**END 2
OPTION**

**-01, -02,
-04, -06, -08**

- "XXXX"
= Assembled Length
in millimeters
-0300 to -1000
(1000 mm) 39.40"
maximum

-S
= 30 μ" (0.76 μm)
Gold on contact

-2
= RG 316
cable


**Specify
END 2
OPTION
from
chart.**

NO. OF POSITIONS	A
-01	(20.87) .822
-02	(24.87) .979
-04	(32.87) 1.294
-06	(40.87) 1.609
-08	(48.87) 1.924

END 2 OPTION
All Gold
-01SP1 = SMA Straight Plug
-01RP1 = SMA Right-angle plug
-01BJ1 = SMA Bulkhead Jack
-01SR1 = SMA Straight Bulkhead Jack, Sealed, Reversed Polarity

END 2 OPTION
All Gold
-02SP1 = MCX Straight Plug
-02RP1 = MCX Right-angle Plug
-03SP1 = MMCX Straight Plug
-03RP1 = MMCX Right-angle Plug
-07SP1 = SMB Straight Plug

END 2 OPTION
Gold/Nikel Combination
-02SP2 = MCX Straight Plug
-03SP2 = MMCX Straight Plug
-07SP2 = SMB Straight Plug



Note:
This Series is non-standard,
non-returnable.

WWW.SAMTEC.COM

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.