


Surface Mount Ceramic Chip Capacitors – C0201 Series - X5R Dielectric

Outline Drawing



Dimensions – Millimeters (Inches)

EIA Size Code	Metric Size Code	L Length	W Width	B Bandwidth	S Separation
0201	0603	0.6 (.024) ± 0.03 (.001)	0.3 (.012) ± 0.03 (.001)	0.15 (.006) ± 0.05 (.002)	-

See Capacitance Value Table below for thickness dimension.

Capacitance Value

Capacitance Value (uF)	KEMET Part Number	Voltage	Capacitance Tolerance	Thickness	Qty 7" Reel
0.01	C0201C103K4PAC	16	K,M	0.3 (.012) ± 0.03 (.001)	15,000
0.10	C0201C104K9PAC	6.3	K,M	0.3 (.012) ± 0.03 (.001)	15,000

Capacitor Ordering Information

Style _____	C	0201	C	104	K	9	P	A	C	End Metallization C = Standard (Tin-plate nickel barrier)
Size Code _____ See dimension table										Failure Rate Level A = Not Applicable
Specification _____ C - Standard										Temperature Characteristic Designated by Capacitance Change Over Temperature Range P = X5R (±15%) (-55°C +85°C)
Capacitance Code, pF _____ First two digits represent significant figures. Third digit specifies number of zeros. 100 pF = 101. (Use "9" for 1.0 through 9.9 pF) (Use "8" for 0.1 through .99 pF)										Voltage 9 = 6.3V 4 = 16V
Capacitance Tolerance _____ K = ± 10% M = ± 20%										

RoHS Compliant

Electrical Parameters

As detailed in the KEMET Surface Mount Catalog F3102 for X5R, with following specific requirements based on room temperature (25°C) parameters:

- Operating Range: -55°C to +85°C, with no-bias capacitance shift limited to $\pm 15\%$ over that range.
- Insulation Resistance (IR) measured after 2 minutes at rated voltage @ 25°C: Limit is 500 megohm microfarads or 10000M Ω , whichever of the two is smaller.
- Capacitance and Dissipation Factor (DF) measured at 1 kHz and 1 Vrms. DF Limit is 10% max.**

**** Please refer to individual specifications.**

Soldering Process

These components are suitable for reflow only. All parts incorporate the standard KEMET barrier layer of pure nickel, with an overplate of pure tin to provide excellent solderability as well as resistance to leaching.

Marking

These chips will be supplied unmarked.

In general, the information in the KEMET Surface Mount catalog F3102 applies to these capacitors. The information in this bulletin supplements that in the catalog.



F-9078C 08/06