







REV.	DATE	ECR NO.	DESCRIPTION
A	01/30/04	-	UPDATE DRAWING FORMAT
B	10/05/04	-	MODIFY BODY HEX ORIENTATION
C	08/29/08	-	REVISE BARREL O.D./ REVISE FERRULE I.D. AND O.D.



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .128" [3.25]
2. CONTACT PIN TO SOLDER

DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	APPROVALS	DATE	PART DESCRIPTION			
8								<h1 style="text-align: center; color: blue;">Amphenol Connex</h1> <p style="text-align: center;">SMA BULKHEAD CRIMP JACK O-RING SEAL (FOR RG-174/U, 188A/U, 316/U CABLE)</p>			
7	FERRULE	COPPER	GOLD	1		DRAWN	GRS				08/29/08
6	HEX NUT	BRASS	GOLD	1		CHECKED					
5	LOCK WASHER	BRASS	GOLD	1		ISSUED					
4	GASKET	SILICONE	RED	1		SHEET	1 OF 1				
3	CONTACT PIN	BER. COPPER	GOLD	1					PART NO.	132284	
2	INSULATOR	PTFE	NATURAL	1					DWG. NO.	132284.DWG	
1	BODY	BRASS	GOLD	1					REV.	C	
									SIZE	A	
									SCALE	NA	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.40mm
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = ± 0.007"
.315 - 1.180 = ± 0.015"
1.180 - 4.724 = ± 0.020"

APPROVALS	DATE
DRAWN GRS	08/29/08
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE	C:/132/132284.DWG