


## V23105-A5 D2 Neutral Small Relays



## Features

- 2 Form C Contacts
- Switching Capacity Ranges from Low Signal Up to 2 A
- 16 Pin DIP Socket Mountable
- For Printed Circuit Boards
- Plastic Casing
- Immersion Cleanable


## Applications

- Communications Technology
- Office Automation
- Security Devices
- Entertainment Electronics
- Measurement and Control Equipment

Contact Material: Silver palladium, gold-plated, against silver palladium, gold-plated. Maximum Switching Capacity: 60 W at DC voltage, 120 VA at AC voltage. Maximum Coil Temperature: 120°C. Ambient Temperature According to IEC 255-1-00 or VDE 0435 Part 201: -25°C to +70°C. Insulation Resistance at 500 V: 1000 M. Operate Time Including Bounce: Less than 10 ms. Release Time Including Bounce: Less than 10 ms. Weight: Approximately 6 g.

Stock No.	Mfr.'s Type	Nominal Coil Voltage	Nominal Power Consumption	Ohms	Each
886-3104	V23105A5001A201	5 V	150 mW	36	1.41
886-3105	V23105A5003A201	12 V	150 mW	280	1.37
886-3107	V23105A5005A201	24 V	150 mW	1050	1.83
886-3136	V23105A5403A201	12 V	400 mW	280	1.52
886-3134	V23105A5401A201	5 V	400 mW	36	1.33
886-0554	V23105A5405A201	24 V	400 mW	1050	1.21
886-3138	V23105A5407A201	48 V	400 mW	4000	2.00

## RM 2/3/7 Power Relays




- 10/16 A Rating
- Mechanical Indicator
- Push-to-Test Button Option
- Variety of Mounting Options

Weight: 2.85 oz. Contacts: 2 Form C; 3 Form C. Material: AgCdO. Maximum Contact Rating: RM2 — 16 A, 380 VAC, 30 VDC; RM3 — 10 A, 380 VAC, 30 VDC. Nominal Coil Power: RM2/RM3 — 1.2 W, 2.3 V A; RM7 — 1.6 W, 2.8 V A.

4


## PM17 4DPT 25-Amp Power Relays



4PDT for polyphase and heavy-duty switching. Contacts are silver-cadmium-oxide. Rated at 25 amps, 240 V, 50-60 Hz, non-inductive. 1 HP per moveable arm at 120 or 240 V single-phase. Mount by keyhole and 2 channels for 8-32 screws on 2 x 2 1/2" triangular centers. Screw term: 2 5/16" x 2 1/2" x 3 3/16". Weight: 1 lb. UL, CSA listed.

Stock No.	Mfr.'s Type	Coil Volts	EACH			
			1-24	25-49	50-99	100-249
886-0951	PM-17AY-24	24 AC	73.82	69.10	66.03	62.19
886-0952	PM-17AY-120	120 AC	93.02	88.39	83.71	77.82
886-0953	PM-17AY-240	240 AC	73.39	69.73	66.06	63.10
886-0956	PM-17DY-12	12 DC	89.90	81.73	74.92	69.15
886-0957	PM-17DY-24	24 DC	89.90	81.73	74.92	69.15
886-0958	PM-17DY-110	110 DC	93.71	89.04	84.37	80.00

## RM 5/6 Power Relays



- 10/16 A Rating


- 3 mm Contact Gap

Weight: 2.85 oz. Contacts: 2 Form A; 3 Form C. Material: AgCdO. Maximum Contact Rating: RM5 — 16 A, 380 VAC, 30 VDC; RM6 — 10 A, 380 VAC, 30 VDC. Nominal Coil Power: DC — 1.6 W; AC — 2.8 V A.

Stock No.	Mfr.'s Type*	Volts	Amps	Contact Arrangement	EACH		
					1-24	25-49	100-499
886-2022	RM502024	24 VDC	16	DPST-NO	11.62	10.36	9.53
886-2023	RM502524	24 VAC	16	DPST-NO	11.62	10.36	9.53
886-2024	RM502615	115 VAC	16	DPST-NO	12.12	10.82	9.94
886-2025	RM602024	24 VDC	10	3PST-NO	11.50	10.25	9.43
886-2026	RM602524	24 VAC	10	3PST-NO	11.62	10.36	9.53
886-2027	RM602615	115 VAC	10	3PST-NO	12.12	10.82	9.94

\*Third Digit in Mfr.'s Type: 2 — Denotes plain case 0.187" (4.75 mm) quick-connect.

## RM8 Power Relays



- 25 A Rating


- AC or DC Versions

Weight: 2.85 oz. Contacts: 2 Form C. Material: AgCdO. Maximum Contact Rating: 25 A at 250 VAC, 30 VDC. Nominal Coil Power: DC — 1.2 W; AC — 2.8 V A.

Stock No.	Mfr.'s Type*	Volts	Amps	Contact Arrangement	EACH		
					1-24	25-49	100-499
886-2028	RM805012	12 VDC	DPDT	13.07	11.67	10.72	
886-2029	RM805024	24 VDC	DPDT	11.67	10.42	9.58	
886-2030	RM805524	24 VAC	DPDT	13.64	12.17	11.19	
886-2031	RM805615	115 VAC	DPDT	12.12	10.81	9.95	

\*Third Digit in Mfr.'s Type: 5 — Denotes case with mounting slots on 2.52 (64.0) centers and 0.250 quick connect terminals.

## PRD Type Heavy Duty Power Relays



PRD relays are interchangeable with PR relays; same size and mounting holes. Improved design allows use of power screwdrivers on terminals. All models are UL and CSA listed and have silver contacts. Model PRD-3AYO is rated 40 amps, all other rated 25 amps. Mounting: Two 0.188" dia. holes on 1.875" centers. Weight: 11 oz.

Stock No.	Mfr.'s Type	Coil		Contacts	EACH			
		Volts	Resistance in Ohms		1-24	25-49	50-99	100-249
886-0973	PRD-3AYO-120	120 AC	290.0	SPST	15.68	14.25	12.94	11.94
886-0982	PRD-5AYO-120	120 AC	290.0	SPDT	20.15	18.12	16.14	
886-0985	PRD-5DYO-12	12 DC	71.0	SPDT	23.82	21.66	19.85	18.33
886-0986	PRD-5DYO-24	24 DC	288.0	SPDT	19.93	18.92	17.93	16.18
886-0990	PRD-7AYO-24	24 AC	12.0	DPST	25.29	24.04	22.76	21.06
886-0991	PRD-7AYO-120	120 AC	290.0	DPST	24.21	22.01	20.18	18.62
886-0992	PRD-7AYO-240	240 AC	1.2 K	DPST	28.55	25.96	23.80	21.94
886-0994	PRD-7DYO-12	12 DC	71.0	DPST	26.05	23.68	21.48	19.83
886-0995	PRD-7DYO-24	24 DC	288.0	DPST	24.62	22.56	20.82	19.34
886-1004	PRD-11AYO-24	24 AC	12.0	DPST	34.67	31.52	28.90	26.68
886-1005	PRD-11AYO-120	120 AC	290.0	DPDT	30.07	27.33	25.06	23.13
886-1006	PRD-11AYO-240	240 AC	1.2 K	DPDT	35.27	32.06	29.39	27.14
886-1009	PRD-11DYO-12	12 DC	71.0	DPDT	33.88	30.79	28.23	26.06
886-1010	PRD-11DYO-24	24 DC	288.					