





LEAD FINISH:	GOLD
CASING FINISH:	GOLD
CAPACITANCE	1200pF +100%-0%
TEMP. RANGE	-55°C TO 125°C
CURRENT	5 AMP MAX.
WORKING VOLTAGE	125°C 200VDC MAX.
D.C. RESISTANCE	.01ohms MAX.

SCHEMATIC



MARKING:

NONE


PACKING:

BAG: SCI-9925-122
DATE CODE
LOT NO.
QTY./BAG (200 MAX.)



NOTES:

1. SUGGESTED MOUNTING HOLE $\phi .132 \pm .002$
2. MAX. SOLDERING TEMP 260°C FOR 20 SEC MAX

	2	1	0	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	
	CN 22042-CPD	CN 205907	CN 186828	CHANGE NOTICE	Fractions $\pm 1/64$		
					Dec. .xx±	Dwn. SLAGLE	Description
					Dec. .xxx±.005	Ckd. 2/14/02	FEEDTHRU FILTER
					Angles $\pm 0^{\circ} 30'$	Apvd.	SCI-9925-122
					CODE IDENT. NO. DLSP2	© THIRD ANGLE PROJECTION	

