

# SN54LVT16646, SN74LVT16646 3.3-V ABT 16-BIT BUS TRANSCEIVERS AND REGISTERS WITH 3-STATE OUTPUTS

SCBS149D – JULY 1994 – REVISED MARCH 2004

- Members of the Texas Instruments Widebus™ Family
- State-of-the-Art Advanced BiCMOS Technology (ABT) Design for 3.3-V Operation and Low-Static Power Dissipation
- Support Mixed-Mode Signal Operation (5-V Input and Output Voltages With 3.3-V  $V_{CC}$ )
- Support Unregulated Battery Operation Down to 2.7 V
- Typical  $V_{OLP}$  (Output Ground Bounce)  $<0.8$  V at  $V_{CC} = 3.3$  V,  $T_A = 25^\circ\text{C}$
- Bus-Hold Data Inputs Eliminate the Need for External Pullup Resistors
- $I_{off}$  and Power-Up 3-State Support Hot Insertion
- Distributed  $V_{CC}$  and GND Pin Configuration Minimizes High-Speed Switching Noise
- Flowthrough Architecture Optimizes PCB Layout
- Latch-Up Performance Exceeds 500 mA Per JEDEC Standard JESD-17
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)

## description/ordering information

The 'LVT16646 devices are 16-bit bus transceivers and registers designed for low-voltage (3.3-V)  $V_{CC}$  operation, but with the capability to provide a TTL interface to a 5-V system environment.

These devices can be used as two 8-bit transceivers or one 16-bit transceiver. Data on the A or B bus is clocked into the registers on the low-to-high transition of the appropriate clock (CLKAB or CLKBA) input. Figure 1 illustrates the four fundamental bus-management functions that can be performed with the 'LVT16646 devices.

SN54LVT16646 . . . WD PACKAGE  
SN74LVT16646 . . . DGG OR DL PACKAGE  
(TOP VIEW)

|          |    |    |          |
|----------|----|----|----------|
| 1DIR     | 1  | 56 | 1OE      |
| 1CLKAB   | 2  | 55 | 1CLKBA   |
| 1SAB     | 3  | 54 | 1SBA     |
| GND      | 4  | 53 | GND      |
| 1A1      | 5  | 52 | 1B1      |
| 1A2      | 6  | 51 | 1B2      |
| $V_{CC}$ | 7  | 50 | $V_{CC}$ |
| 1A3      | 8  | 49 | 1B3      |
| 1A4      | 9  | 48 | 1B4      |
| 1A5      | 10 | 47 | 1B5      |
| GND      | 11 | 46 | GND      |
| 1A6      | 12 | 45 | 1B6      |
| 1A7      | 13 | 44 | 1B7      |
| 1A8      | 14 | 43 | 1B8      |
| 2A1      | 15 | 42 | 2B1      |
| 2A2      | 16 | 41 | 2B2      |
| 2A3      | 17 | 40 | 2B3      |
| GND      | 18 | 39 | GND      |
| 2A4      | 19 | 38 | 2B4      |
| 2A5      | 20 | 37 | 2B5      |
| 2A6      | 21 | 36 | 2B6      |
| $V_{CC}$ | 22 | 35 | $V_{CC}$ |
| 2A7      | 23 | 34 | 2B7      |
| 2A8      | 24 | 33 | 2B8      |
| GND      | 25 | 32 | GND      |
| 2SAB     | 26 | 31 | 2SBA     |
| 2CLKAB   | 27 | 30 | 2CLKBA   |
| 2DIR     | 28 | 29 | 2OE      |

## ORDERING INFORMATION

| $T_A$          | PACKAGE†    |               | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|----------------|-------------|---------------|-----------------------|------------------|
| –40°C to 85°C  | SSOP – DL   | Tube          | SN74LVT16646DL        | LVT16646         |
|                |             | Tape and reel | SN74LVT16646DLR       |                  |
|                | TSSOP – DGG | Tape and reel | SN74LVT16646DGGR      | LVT16646         |
| –55°C to 125°C | CFP – WD    | Tube          | SNJ54LVT16646WD       | SNJ54LVT16646WD  |

† Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Widebus is a trademark of Texas Instruments.

UNLESS OTHERWISE NOTED this document contains PRODUCTION DATA information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2004, Texas Instruments Incorporated

# SN54LVT16646, SN74LVT16646

## 3.3-V ABT 16-BIT BUS TRANSCEIVERS AND REGISTERS WITH 3-STATE OUTPUTS

SCBS149D – JULY 1994 – REVISED MARCH 2004

### description/ordering information (continued)

Output-enable ( $\overline{OE}$ ) and direction-control (DIR) inputs are provided to control the transceiver functions. In the transceiver mode, data present at the high-impedance port may be stored in either register or in both. The select-control (SAB and SBA) inputs can multiplex stored and real-time (transparent mode) data. The circuitry used for select control eliminates the typical decoding glitch that occurs in a multiplexer during the transition between stored and real-time data. The direction control (DIR) determines which bus receives data when  $\overline{OE}$  is low. In the isolation mode ( $\overline{OE}$  high), A data may be stored in one register and/or B data may be stored in the other register.

When an output function is disabled, the input function is still enabled and may be used to store and transmit data. Only one of the two buses, A or B, may be driven at a time.

Active bus-hold circuitry holds unused or undriven inputs at a valid logic state. Use of pullup or pulldown resistors with the bus-hold circuitry is not recommended.

These devices are fully specified for hot-insertion applications using  $I_{off}$  and power-up 3-state. The  $I_{off}$  circuitry disables the outputs, preventing damaging current backflow through the devices when they are powered down. The power-up 3-state circuitry places the outputs in the high-impedance state during power up and power down, which prevents driver conflict.

To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

FUNCTION TABLE

| INPUTS          |     |        |        |     |     | DATA I/Os                |                          | OPERATION OR FUNCTION               |
|-----------------|-----|--------|--------|-----|-----|--------------------------|--------------------------|-------------------------------------|
| $\overline{OE}$ | DIR | CLKAB  | CLKBA  | SAB | SBA | A1 THRU A8               | B1 THRU B8               |                                     |
| X               | X   | ↑      | X      | X   | X   | Input                    | Unspecified <sup>†</sup> | Store A, B unspecified <sup>†</sup> |
| X               | X   | X      | ↑      | X   | X   | Unspecified <sup>†</sup> | Input                    | Store B, A unspecified <sup>†</sup> |
| H               | X   | ↑      | ↑      | X   | X   | Input                    | Input                    | Store A and B data                  |
| H               | X   | H or L | H or L | X   | X   | Input disabled           | Input disabled           | Isolation, hold storage             |
| L               | L   | X      | X      | X   | L   | Output                   | Input                    | Real-time B data to A bus           |
| L               | L   | X      | H or L | X   | H   | Output                   | Input                    | Stored B data to A bus              |
| L               | H   | X      | X      | L   | X   | Input                    | Output                   | Real-time A data to B bus           |
| L               | H   | H or L | X      | H   | X   | Input                    | Output                   | Stored A data to B bus              |

<sup>†</sup> The data output functions may be enabled or disabled by various signals at  $\overline{OE}$  and DIR. Data input functions always are enabled; i.e., data at the bus pins are stored on every low-to-high transition of the clock inputs.

**SN54LVT16646, SN74LVT16646**  
**3.3-V ABT 16-BIT BUS TRANSCEIVERS AND REGISTERS**  
**WITH 3-STATE OUTPUTS**

SCBS149D – JULY 1994 – REVISED MARCH 2004




Figure 1. Bus-Management Functions


# SN54LVT16646, SN74LVT16646

## 3.3-V ABT 16-BIT BUS TRANSCEIVERS AND REGISTERS

### WITH 3-STATE OUTPUTS

SCBS149D – JULY 1994 – REVISED MARCH 2004

#### logic diagram (positive logic)



# SN54LVT16646, SN74LVT16646

## 3.3-V ABT 16-BIT BUS TRANSCEIVERS AND REGISTERS WITH 3-STATE OUTPUTS

SCBS149D – JULY 1994 – REVISED MARCH 2004

### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

|                                                                                              |                 |
|----------------------------------------------------------------------------------------------|-----------------|
| Supply voltage range, $V_{CC}$                                                               | –0.5 V to 4.6 V |
| Input voltage range, $V_I$ (see Note 1)                                                      | –0.5 V to 7 V   |
| Voltage range applied to any output in the high state or power-off state, $V_O$ (see Note 1) | –0.5 V to 7 V   |
| Current into any output in the low state, $I_O$ : SN54LVT16646                               | 96 mA           |
| SN74LVT16646                                                                                 | 128 mA          |
| Current into any output in the high state, $I_O$ (see Note 2): SN54LVT16646                  | 48 mA           |
| SN74LVT16646                                                                                 | 64 mA           |
| Input clamp current, $I_{IK}$ ( $V_I < 0$ )                                                  | –50 mA          |
| Output clamp current, $I_{OK}$ ( $V_O < 0$ )                                                 | –50 mA          |
| Package thermal impedance, $\theta_{JA}$ (see Note 3): DGG package                           | 64°C/W          |
| DL package                                                                                   | 56°C/W          |
| Storage temperature range, $T_{stg}$                                                         | –65°C to 150°C  |

<sup>†</sup> Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.  
2. This current flows only when the output is in the high state and  $V_O > V_{CC}$ .  
3. The package thermal impedance is calculated in accordance with JESD 51–7.

### recommended operating conditions (see Note 4)

|                     |                                    |                 | SN54LVT16646 |     | SN74LVT16646 |     | UNIT |
|---------------------|------------------------------------|-----------------|--------------|-----|--------------|-----|------|
|                     |                                    |                 | MIN          | MAX | MIN          | MAX |      |
| $V_{CC}$            | Supply voltage                     |                 | 2.7          | 3.6 | 2.7          | 3.6 | V    |
| $V_{IH}$            | High-level input voltage           |                 | 2            |     | 2            |     | V    |
| $V_{IL}$            | Low-level input voltage            |                 |              | 0.8 |              | 0.8 | V    |
| $V_I$               | Input voltage                      |                 |              | 5.5 |              | 5.5 | V    |
| $I_{OH}$            | High-level output current          |                 |              | –24 |              | –32 | mA   |
| $I_{OL}$            | Low-level output current           |                 |              | 48  |              | 64  | mA   |
| $\Delta t/\Delta v$ | Input transition rise or fall rate | Outputs enabled |              | 10  |              | 10  | ns/V |
| $T_A$               | Operating free-air temperature     |                 | –55          | 125 | –40          | 85  | °C   |

NOTE 4: All unused control inputs of the device must be held at  $V_{CC}$  or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

# SN54LVT16646, SN74LVT16646

## 3.3-V ABT 16-BIT BUS TRANSCEIVERS AND REGISTERS WITH 3-STATE OUTPUTS

SCBS149D – JULY 1994 – REVISED MARCH 2004

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER            | TEST CONDITIONS                                                                                                             |                                   | SN54LVT16646 |      |         | SN74LVT16646 |      |           | UNIT          |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------|-----------------------------------|--------------|------|---------|--------------|------|-----------|---------------|
|                      |                                                                                                                             |                                   | MIN          | TYP† | MAX     | MIN          | TYP† | MAX       |               |
| $V_{IK}$             | $V_{CC} = 2.7\text{ V}$ ,<br>$I_I = -18\text{ mA}$                                                                          |                                   |              |      | -1.2    |              |      | -1.2      | V             |
| $V_{OH}$             | $V_{CC} = \text{MIN to MAX}^\ddagger$ ,<br>$I_{OH} = -100\text{ }\mu\text{A}$                                               |                                   | $V_{CC}-0.2$ |      |         | $V_{CC}-0.2$ |      |           | V             |
|                      | $V_{CC} = 2.7\text{ V}$ ,<br>$I_{OH} = -8\text{ mA}$                                                                        |                                   | 2.4          |      |         | 2.4          |      |           |               |
|                      | $V_{CC} = 3\text{ V}$                                                                                                       | $I_{OH} = -24\text{ mA}$          | 2            |      |         |              |      |           |               |
|                      |                                                                                                                             | $I_{OH} = -32\text{ mA}$          |              |      |         | 2            |      |           |               |
| $V_{OL}$             | $V_{CC} = 2.7\text{ V}$                                                                                                     | $I_{OL} = 100\text{ }\mu\text{A}$ |              |      | 0.2     |              |      | 0.2       | V             |
|                      |                                                                                                                             | $I_{OL} = 24\text{ mA}$           |              |      | 0.5     |              |      | 0.5       |               |
|                      | $V_{CC} = 3\text{ V}$                                                                                                       | $I_{OL} = 16\text{ mA}$           |              |      | 0.4     |              |      | 0.4       |               |
|                      |                                                                                                                             | $I_{OL} = 32\text{ mA}$           |              |      | 0.5     |              |      | 0.5       |               |
|                      |                                                                                                                             | $I_{OL} = 48\text{ mA}$           |              |      | 0.55    |              |      |           |               |
|                      |                                                                                                                             | $I_{OL} = 64\text{ mA}$           |              |      |         |              |      | 0.55      |               |
| $I_I$                | $V_{CC} = 3.6\text{ V}$ ,<br>$V_I = V_{CC}\text{ or GND}$                                                                   | Control inputs                    |              |      | $\pm 1$ |              |      | $\pm 1$   | $\mu\text{A}$ |
|                      | $V_{CC} = 0\text{ or MAX}^\ddagger$ ,<br>$V_I = 5.5\text{ V}$                                                               |                                   |              |      | 10      |              |      | 10        |               |
|                      | $V_{CC} = 3.6\text{ V}$                                                                                                     | $V_I = 5.5\text{ V}$              |              |      | 20      |              |      | 20        |               |
|                      |                                                                                                                             | $V_I = V_{CC}$                    |              |      | 5       |              |      | 5         |               |
|                      |                                                                                                                             | $V_I = 0$                         |              |      | -10     |              |      | -10       |               |
| $I_{off}$            | $V_{CC} = 0$ ,<br>$V_I\text{ or }V_O = 0\text{ to }4.5\text{ V}$                                                            |                                   |              |      |         |              |      | $\pm 100$ | $\mu\text{A}$ |
| $I_{I(\text{hold})}$ | $V_{CC} = 3\text{ V}$                                                                                                       | $V_I = 0.8\text{ V}$              | A or B ports |      | 75      |              |      | 75        | $\mu\text{A}$ |
|                      |                                                                                                                             | $V_I = 2\text{ V}$                |              |      | -75     |              |      | -75       |               |
| $I_{OZH}$            | $V_{CC} = 3.6\text{ V}$ ,<br>$V_O = 3\text{ V}$                                                                             |                                   |              |      | 1       |              |      | 1         | $\mu\text{A}$ |
| $I_{OZL}$            | $V_{CC} = 3.6\text{ V}$ ,<br>$V_O = 0.5\text{ V}$                                                                           |                                   |              |      | -1      |              |      | -1        | $\mu\text{A}$ |
| $I_{CC}$             | $V_{CC} = 3.6\text{ V}$ ,<br>$V_I = V_{CC}\text{ or GND}$                                                                   | $I_O = 0$ ,<br>Outputs high       |              |      | 0.12    |              |      | 0.12      | mA            |
|                      |                                                                                                                             | Outputs low                       |              |      | 5       |              |      | 5         |               |
|                      |                                                                                                                             | Outputs disabled                  |              |      | 0.12    |              |      | 0.12      |               |
| $\Delta I_{CC}^\S$   | $V_{CC} = 3\text{ V to }3.6\text{ V}$ ,<br>One input at $V_{CC} - 0.6\text{ V}$ ,<br>Other inputs at $V_{CC}\text{ or GND}$ |                                   |              |      | 0.2     |              |      | 0.2       | mA            |
| $C_i$                | $V_I = 3\text{ V or }0$                                                                                                     |                                   |              |      | 3.5     |              |      | 3.5       | pF            |
| $C_{io}$             | $V_O = 3\text{ V or }0$                                                                                                     |                                   |              |      | 12      |              |      | 12        | pF            |

† All typical values are at  $V_{CC} = 3.3\text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

‡ For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

§ Unused pins at  $V_{CC}\text{ or GND}$

¶ This is the increase in supply current for each input that is at the specified TTL voltage level, rather than  $V_{CC}\text{ or GND}$ .

# SN54LVT16646, SN74LVT16646

## 3.3-V ABT 16-BIT BUS TRANSCEIVERS AND REGISTERS WITH 3-STATE OUTPUTS

SCBS149D – JULY 1994 – REVISED MARCH 2004

timing requirements over recommended operating free-air temperature range (unless otherwise noted) (see Figure 2)

|                    |                                               |           | SN54LVT16646                             |     |                         |     | SN74LVT16646                             |     |                         |     | UNIT |
|--------------------|-----------------------------------------------|-----------|------------------------------------------|-----|-------------------------|-----|------------------------------------------|-----|-------------------------|-----|------|
|                    |                                               |           | $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ |     | $V_{CC} = 2.7\text{ V}$ |     | $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ |     | $V_{CC} = 2.7\text{ V}$ |     |      |
|                    |                                               |           | MIN                                      | MAX | MIN                     | MAX | MIN                                      | MAX | MIN                     | MAX |      |
| f <sub>clock</sub> | Clock frequency                               |           | 150                                      |     | 150                     |     | 150                                      |     | 150                     |     | MHz  |
| t <sub>w</sub>     | Pulse duration, CLK high or low               |           | 3.3                                      |     | 3.3                     |     | 3.3                                      |     | 3.3                     |     | ns   |
| t <sub>su</sub>    | Setup time,<br>A or B before CLKAB↑ or CLKBA↑ | Data high | 1.3                                      |     | 1.4                     |     | 1.3                                      |     | 1.4                     |     | ns   |
|                    |                                               | Data low  | 2.4                                      |     | 3                       |     | 2.4                                      |     | 3                       |     |      |
| t <sub>h</sub>     | Hold time,<br>A or B after CLKAB↑ or CLKBA↑   | Data high | 0.5                                      |     | 0                       |     | 0.5                                      |     | 0                       |     | ns   |
|                    |                                               | Data low  | 0.6                                      |     | 0.5                     |     | 0.5                                      |     | 0.5                     |     |      |

switching characteristics over recommended operating free-air temperature range,  $C_L = 50\text{ pF}$  (unless otherwise noted) (see Figure 2)

| PARAMETER        | FROM<br>(INPUT)         | TO<br>(OUTPUT) | SN54LVT16646                       |     |                         |     | SN74LVT16646                       |                  |     |                         | UNIT |     |
|------------------|-------------------------|----------------|------------------------------------|-----|-------------------------|-----|------------------------------------|------------------|-----|-------------------------|------|-----|
|                  |                         |                | V <sub>CC</sub> = 3.3 V<br>± 0.3 V |     | V <sub>CC</sub> = 2.7 V |     | V <sub>CC</sub> = 3.3 V<br>± 0.3 V |                  |     | V <sub>CC</sub> = 2.7 V |      |     |
|                  |                         |                | MIN                                | MAX | MIN                     | MAX | MIN                                | TYP <sup>†</sup> | MAX | MIN                     |      | MAX |
| f <sub>max</sub> |                         |                | 150                                |     |                         |     | 150                                |                  |     |                         |      | MHz |
| t <sub>PLH</sub> | CLKBA or<br>CLKAB       | A or B         | 1.8                                | 6   | 6.9                     |     | 1.8                                | 3.8              | 5.7 | 6.7                     |      | ns  |
| t <sub>PHL</sub> |                         |                | 2.1                                | 5.9 | 6.6                     |     | 2.1                                | 3.9              | 5.7 | 6.5                     |      |     |
| t <sub>PLH</sub> | A or B                  | B or A         | 1.3                                | 4.9 | 5.6                     |     | 1.3                                | 3                | 4.7 | 5.4                     |      | ns  |
| t <sub>PHL</sub> |                         |                | 1                                  | 4.8 | 5.8                     |     | 1                                  | 3.1              | 4.7 | 5.6                     |      |     |
| t <sub>PLH</sub> | SBA or SAB <sup>‡</sup> | A or B         | 1.4                                | 6.4 | 7.4                     |     | 1.4                                | 4                | 6.2 | 7.2                     |      | ns  |
| t <sub>PHL</sub> |                         |                | 1.4                                | 6.4 | 7.4                     |     | 1.4                                | 4.3              | 6.2 | 7.2                     |      |     |
| t <sub>PZH</sub> | $\overline{\text{OE}}$  | A or B         | 1                                  | 5.7 | 7.4                     |     | 1                                  | 3                | 5.4 | 6.4                     |      | ns  |
| t <sub>PZL</sub> |                         |                | 1                                  | 6.5 | 7.5                     |     | 1                                  | 3.1              | 5.6 | 6.5                     |      |     |
| t <sub>PHZ</sub> | $\overline{\text{OE}}$  | A or B         | 2.3                                | 6.7 | 7.1                     |     | 2.3                                | 4.6              | 6.5 | 6.9                     |      | ns  |
| t <sub>PLZ</sub> |                         |                | 2.2                                | 6   | 6.5                     |     | 2.2                                | 4.5              | 5.8 | 5.9                     |      |     |
| t <sub>PZH</sub> | DIR                     | A or B         | 1                                  | 5.9 | 7.7                     |     | 1                                  | 3.3              | 5.7 | 6.7                     |      | ns  |
| t <sub>PZL</sub> |                         |                | 1.2                                | 5.9 | 7.3                     |     | 1.2                                | 3.5              | 5.8 | 6.7                     |      |     |
| t <sub>PHZ</sub> | DIR                     | A or B         | 1.7                                | 7.3 | 8.5                     |     | 1.7                                | 4.7              | 7.2 | 8.3                     |      | ns  |
| t <sub>PLZ</sub> |                         |                | 1.5                                | 7.8 | 7.4                     |     | 1.5                                | 4.9              | 6.6 | 7.2                     |      |     |

<sup>†</sup> All typical values are at  $V_{CC} = 3.3\text{ V}$ ,  $T_A = 25^\circ\text{C}$ .


<sup>‡</sup> These parameters are measured with the internal output state of the storage register opposite to that of the bus input.

# SN54LVT16646, SN74LVT16646

## 3.3-V ABT 16-BIT BUS TRANSCEIVERS AND REGISTERS WITH 3-STATE OUTPUTS


SCBS149D – JULY 1994 – REVISED MARCH 2004

### PARAMETER MEASUREMENT INFORMATION




LOAD CIRCUIT FOR OUTPUTS


| TEST              | S1   |
|-------------------|------|
| $t_{PLH}/t_{PHL}$ | Open |
| $t_{PLZ}/t_{PZL}$ | 6 V  |
| $t_{PHZ}/t_{PZH}$ | GND  |




VOLTAGE WAVEFORMS  
PULSE DURATION



VOLTAGE WAVEFORMS  
SETUP AND HOLD TIMES



VOLTAGE WAVEFORMS  
PROPAGATION DELAY TIMES  
INVERTING AND NONINVERTING OUTPUTS



VOLTAGE WAVEFORMS  
ENABLE AND DISABLE TIMES  
LOW- AND HIGH-LEVEL ENABLING

- NOTES:
- A.  $C_L$  includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - C. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10$  MHz,  $Z_O = 50 \Omega$ ,  $t_r \leq 2.5$  ns,  $t_f \leq 2.5$  ns.
  - D. The outputs are measured one at a time, with one transition per measurement.
  - E. All parameters and waveforms are not applicable to all devices.

Figure 2. Load Circuit and Voltage Waveforms

## PACKAGING INFORMATION

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish | MSL Peak Temp<br>(3) | Op Temp (°C) | Top-Side Markings<br>(4) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|------------------|----------------------|--------------|--------------------------|-------------------------|
| 74LVT16646DGGRE4 | ACTIVE        | TSSOP        | DGG                | 56   |                | TBD                        | Call TI          | Call TI              | -40 to 85    |                          | <a href="#">Samples</a> |
| 74LVT16646DGGRG4 | NRND          | TSSOP        | DGG                | 56   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM   | -40 to 85    | LVT16646                 |                         |
| SN74LVT16646DGGR | NRND          | TSSOP        | DGG                | 56   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM   | -40 to 85    | LVT16646                 |                         |
| SN74LVT16646DL   | NRND          | SSOP         | DL                 | 56   | 20             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM   | -40 to 85    | LVT16646                 |                         |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) Multiple Top-Side Markings will be inside parentheses. Only one Top-Side Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Top-Side Marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



## TAPE AND REEL INFORMATION

### REEL DIMENSIONS



### TAPE DIMENSIONS



|    |                                                           |
|----|-----------------------------------------------------------|
| A0 | Dimension designed to accommodate the component width     |
| B0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

### TAPE AND REEL INFORMATION

\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74LVT16646DGGR | TSSOP        | DGG             | 56   | 2000 | 330.0              | 24.4               | 8.6     | 15.6    | 1.8     | 12.0    | 24.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS




\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74LVT16646DGGR | TSSOP        | DGG             | 56   | 2000 | 367.0       | 367.0      | 45.0        |

DL (R-PDSO-G56)

PLASTIC SMALL-OUTLINE PACKAGE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion not to exceed  $0.006$  (0,15).
  - D. Falls within JEDEC MO-118

## DGG (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE PACKAGE

48 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold protrusion not to exceed 0,15.  
 D. Falls within JEDEC MO-153

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

|                              |                                                                                      |
|------------------------------|--------------------------------------------------------------------------------------|
| Audio                        | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                               |
| Amplifiers                   | <a href="http://amplifier.ti.com">amplifier.ti.com</a>                               |
| Data Converters              | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>                       |
| DLP® Products                | <a href="http://www.dlp.com">www.dlp.com</a>                                         |
| DSP                          | <a href="http://dsp.ti.com">dsp.ti.com</a>                                           |
| Clocks and Timers            | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>                             |
| Interface                    | <a href="http://interface.ti.com">interface.ti.com</a>                               |
| Logic                        | <a href="http://logic.ti.com">logic.ti.com</a>                                       |
| Power Mgmt                   | <a href="http://power.ti.com">power.ti.com</a>                                       |
| Microcontrollers             | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a>                   |
| RFID                         | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>                                 |
| OMAP Applications Processors | <a href="http://www.ti.com/omap">www.ti.com/omap</a>                                 |
| Wireless Connectivity        | <a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a> |

### Applications

|                               |                                                                                          |
|-------------------------------|------------------------------------------------------------------------------------------|
| Automotive and Transportation | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>                         |
| Communications and Telecom    | <a href="http://www.ti.com/communications">www.ti.com/communications</a>                 |
| Computers and Peripherals     | <a href="http://www.ti.com/computers">www.ti.com/computers</a>                           |
| Consumer Electronics          | <a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>                   |
| Energy and Lighting           | <a href="http://www.ti.com/energy">www.ti.com/energy</a>                                 |
| Industrial                    | <a href="http://www.ti.com/industrial">www.ti.com/industrial</a>                         |
| Medical                       | <a href="http://www.ti.com/medical">www.ti.com/medical</a>                               |
| Security                      | <a href="http://www.ti.com/security">www.ti.com/security</a>                             |
| Space, Avionics and Defense   | <a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a> |
| Video and Imaging             | <a href="http://www.ti.com/video">www.ti.com/video</a>                                   |

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)