

HC/49US (AT49) SMD LOW PROFILE CRYSTAL



11.5 x 4.7 x 4.2 mm

ABLS



RoHS
Compliant

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable

FEATURES:

- Suitable for RoHS reflow
- Available for tight stability & extended temperature range

APPLICATIONS:

- Computers, Modems, Microprocessors
- Wireless Applications

STANDARD SPECIFICATIONS:


PARAMETERS	
ABRACON P/N	ABLS Series
Frequency	3.579545 MHz to 75 MHz
Operation Mode	AT cut (Fundamental or 3rd OT) or BT cut (See options) 3.579545MHz - 24.0MHz (Fundamental: Standard) 24.01MHz - 75.00MHz (3rd- Overtone: Standard) 24.01MHz - 50.00MHz (Fund. AT or BT: See options)
Operating Temperature	0°C to + 70°C (see options)
Storage Temperature	- 55°C to + 125° C
Frequency Tolerance at +25°C	± 50 ppm max. (see options)
Frequency Stability over the Operating Temp. (Ref to +25°C)	± 50 ppm max. (see options)
Equivalent Series Resistance	See Table 1
Shunt Capacitance C ₀	7pF max.
Load Capacitance C _L	18pF (see options)
Drive Level	1 mW max., 100 μW typical
Aging at 25°C (first year)	± 5ppm max.
Insulation Resistance	500 MΩ min at 100Vdc ± 15V
Spurious Responses	-3dB max.
Drive level dependency (DLD)	from 1 μW to 500 μW (minimum 7 points tested)

TABLE 1: STANDARD ESR

FREQUENCY (MHz)	ESR (Ω) MAX
3.579 - 4.999 (Fund.)	180
5.000 - 5.999 (Fund.)	120
6.000 - 7.999 (Fund.)	100
8.000 - 8.999 (Fund.)	80
9.000 - 9.999 (Fund.)	60
10.000 - 15.999 (Fund.)	50
16.000 - 50.000 (Fund.)	40
24.01 - 31.999 (3rd O/T)	100
32.000 - 75.00 (3rd O/T)	80


OPTIONS & PART IDENTIFICATION:

(Left blank if standard)



* -10 to +60° C only.
** Option A, B, and 0 to +70° C only.
*** Frequency stability ±50ppm, ±100ppm, or ±150ppm only.
Contact ABRACON for tighter frequency stability.
**** For Fundamental BT, frequency stability ± 100ppm max. at -10° C to +60° C only.

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

Revised: 04.07.11

11.5 x 4.7 x 4.2 mm



Technical drawing of a rectangular plate with rounded ends. The dimensions are as follows:

- Overall width: 0.500 ± 0.024 inches (12.7 ± 0.6 mm)
- Inner width: 0.45 ± 0.006 inches (11.4 ± 0.15 mm)
- Thickness: 0.019 ± 0.006 inches (4.7 ± 0.15 mm)

Technical drawing of a mechanical part with dimensions:

- Top width: 0.406 max. (10.3)
- Right height: 0.16 max. (4.2)
- Left height: 0.004 max. (0.1 max.) / 0.000 min. (0.0 min.)
- Text: both sides

Figure 10 illustrates dimensioning a part with a hole. The drawing shows a rectangular part with a central hole and two horizontal slots. Dimension lines indicate the distance from the hole center to the slot edges and the slot width. Tolerances are given in both fractional and decimal forms.


Dimension 1 (Distance from hole center to slot edge):

$$\frac{0.192 \pm 0.008}{(4.88 \pm 0.2)}$$


Dimension 2 (Slot width):

$$\frac{0.024 + 0.008 / -0.004}{(0.6 + 0.2 / -0.1)}$$

FEEDING (PULL) DIRECTION



Dimensions: mm



ABRACON CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale

Revised: 04.07.11

30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | www.abracon.com