




10 9 8 7 6 5 4 3 2 1



基板取付穴推奨寸法
RECOMMENDED P.C.B.HOLE DIMENSION

注記
NOTE

- 1 ウエハーのそりは, 長さ 25.4 に対して 0.24 MAX..
CAMBER MUST BE 0.24 MAX. PER 25.4
- 2 全極数が偶数の場合のみ適用。
TO BE APPLIED ONLY WHEN ALL CKTS. ARE EVEN.

49.72	45.72	10-32-1101	5281-10A	10
44.64	40.64	↑ -109I	↑ -09A	9
39.56	35.56	↑ -108I	↑ -08A	8
34.48	30.48	↑ -107I	↑ -07A	7
29.4	25.4	↑ -106I	↑ -06A	6
24.32	20.32	↑ -105I	↑ -05A	5
19.24	15.24	↑ -104I	↑ -04A	4
14.16	10.16	↑ -103I	↑ -03A	3
9.08	5.08	↑ -102I	↑ -02A	2
B	A	EDP NO.	ENG. NO.	極数 NO. OF CKTS.

REVISED EC NO: J2014-1442 DRWN:TYAJIMA01 CHKD:KASAKAWA APPR:NUKITA 2014/03/25 2014/03/26 2014/03/26	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	± 0.15	TYAJIMA01	2014/03/13	TITLE KK 5.08 WAFER ASSY WITH LOCK			
		10 OVER 30 UNDER	± ---	CHECKED BY KASAKAWA	2014/03/13				
		30 OVER	± ---	APPROVED BY NUKITA	2014/03/13				
		ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.			SHEET NO.
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE DRAWING		SD-5281-001		1 OF 1		
	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							