




Agilent 33220A 20 MHz Function/Arbitrary Waveform Generator

Data Sheet

- Fully compliant to LXI Class C specification
- 20 MHz Sine and Square waveforms
- Pulse, Ramp, Triangle, Noise, and DC waveforms
- 14-bit, 50 MSa/s, 64 k-point arbitrary waveforms
- AM, FM, PM, FSK, and PWM modulation types
- Linear & logarithmic sweeps and burst operation
- 10 mV_{pp} to 10 V_{pp} amplitude range
- Graph mode for visual verification of signal settings
- Connect via USB, GPIB and LAN



Uncompromising performance for functions and waveforms

The Agilent Technologies 33220A function/arbitrary waveform generator uses direct digital synthesis (DDS) techniques to create a stable, accurate output signal for clean, low distortion sine waves. It also gives you square waves with fast rise and fall times up to 20 MHz and linear ramp waves up to 200 kHz.

Pulse generation

The 33220A can generate variable-edge-time pulses up to 5 MHz. With variable period, pulse width, and amplitude the 33220A is ideally suited to a wide variety of applications requiring a flexible pulse signal.

Custom waveform generation

Use the 33220A to generate complex custom waveforms. With 14-bit resolution, and a sampling rate of 50 MSa/s, the 33220A gives you the flexibility to create the waveforms you need. It also lets you store up to four waveforms in nonvolatile memory.

The Agilent IntuiLink arbitrary waveform software allows you to easily create, edit, and download complex waveforms using the waveform editor. Or you can capture a waveform using IntuiLink for Oscilloscope and send it to the 33220A for output. To find out more about IntuiLink, visit www.agilent.com/find/intuilink.



Agilent Technologies

Measurement Characteristics

Easy-to-use functionality

Front-panel operation of the 33220A is straight-forward and user friendly. You can access all major functions with a single key or two. The knob or numeric keypad can be used to adjust frequency, amplitude, offset, and other parameters. You can even enter voltage values directly in V_{pp} , V_{rms} , dBm, or as high and low levels. Timing parameters can be entered in Hertz (Hz) or seconds.

Internal AM, FM, PM, FSK, and PWM modulation make it easy to modulate waveforms without the need for a separate modulation source. Linear and logarithmic sweeps are also built in, with sweep rates selectable from 1 ms to 500 s. Burst mode operation allows for a user-selected number of cycles per period of time. GPIB, LAN, and USB interfaces are all standard, plus you get full programmability using SCPI commands.

External frequency reference (Option 001)

The 33220A external frequency reference lets you synchronize to an external 10 MHz clock, to another 33220A, or to an Agilent 33250A. Phase adjustments can be made from the front panel or via a computer interface, allowing precise phase calibration and adjustment.

Waveforms

Standard	Sine, Square, Ramp, Triangle, Pulse, Noise, DC
Built-in arbitrary	Exponential rise, Exponential fall, Negative ramp, Sin(x)/x, Cardiac

Waveforms Characteristics

Sine	
Frequency Range	1 μ Hz to 20 MHz
Amplitude Flatness ^{[1], [2]} (relative to 1 kHz)	
< 100 kHz	0.1 dB
100 kHz to 5 MHz	0.15 dB
5 MHz to 20 MHz	0.3 dB
Harmonic distortion ^{[2], [3]}	
DC to 20 kHz	< 1 V_{pp} $\geq$ 1 V_{pp} -70 dBc -70 dBc
20 kHz to 100 kHz	-65 dBc -60 dBc
100 kHz to 1 MHz	-50 dBc -45 dBc
1 MHz to 20 MHz	-40 dBc -35 dBc
Total harmonic distortion ^{[2], [3]}	
DC to 20 kHz	0.04%
Spurious (non-harmonic) ^{[2], [4]}	
DC to 1 MHz	-70 dBc
1 MHz to 20 MHz	-70 dBc + 6 dB/octave
Phase noise (10 kHz offset)	-115 dBc / Hz, typical
Square	
Frequency range	1 μ Hz to 20 MHz
Rise/Fall time	< 13 ns
Overshoot	< 2%
Variable duty cycle	20% to 80% (to 10 MHz) 40% to 60% (to 20 MHz)
Asymmetry (@ 50% duty)	1% of period + 5 ns
Jitter (RMS)	1 ns + 100 ppm of period
Ramp, Triangle	
Frequency range	1 μ Hz to 200 kHz
Linearity	< 0.1% of peak output
Variable Symmetry	0.0% to 100.0%
Pulse	
Frequency range	500 μ Hz to 5 MHz
Pulse width (period $\leq$ 10s)	20 ns minimum, 10 ns resolution
Variable edge time	< 13 ns to 100 ns
Overshoot	< 2%
Jitter (RMS)	300 ps + 0.1 ppm of period

Noise

Bandwidth	9 MHz typical
Arbitrary	
Frequency range	1 μ Hz to 6 MHz
Waveform length	2 to 64 k points
Amplitude resolution	14 bits (including sign)
Sample rate	50 MSa/s
Min. Rise/Fall Time	35 ns typical
Linearity	< 0.1% of peak output
Settling Time	< 250 ns to 0.5% of final value
Jitter (RMS)	6 ns + 30 ppm
Non-volatile memory	four waveforms

Common Characteristics

Frequency	
Accuracy ^[5]	$\pm$ (10 ppm + 3 pHz) in 90 days $\pm$ (20 ppm + 3 pHz) in 1 year
Resolution	1 μ Hz
Amplitude	
Range	10 mV _{pp} to 10 V _{pp} into 50 Ω 20 mV _{pp} to 20 V _{pp} into open circuit
Accuracy ^{[1], [2]} (at 1 kHz)	$\pm$ 1% of setting $\pm$ 1 mV _{pp}
Units	V _{pp} , V _{rms} , dBm
Resolution	4 digits
DC Offset	
Range (peak AC + DC)	$\pm$ 5 V into 50 Ω $\pm$ 10 V into open circuit
Accuracy ^{[1], [2]}	$\pm$ 2% of offset setting $\pm$ 0.5% of amplitude $\pm$ 2 mV
Resolution	4 digits
Main Output	
Impedance	50 Ω typical
Isolation	42 Vpk maximum to earth
Protection	Short-circuit protected, overload automatically disables main output

External Frequency Reference (Option 001)

Rear Panel Input	
Lock Range	10 MHz $\pm$ 500 Hz
Level	100 mV _{pp} to 5 V _{pp}
Impedance	1 k Ω typical, AC coupled
Lock Time	< 2 seconds
Rear Panel Output	
Frequency	10 MHz
Level	632 mV _{pp} (0 dBm), typical
Impedance	50 Ω typical, AC coupled

Measurement Characteristics (Continued)

Phase Offset

Range	+ 360° to - 360°
Resolution	0.001°
Accuracy	20 ns

Modulation

AM

Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Depth	0.0% to 120.0%

FM

Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Deviation	DC to 10 MHz

PM

Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Deviation	0.0 to 360.0 degrees

PWM

Carrier waveform	Pulse
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Deviation	0% to 100% of pulse width

FSK

Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	50% duty cycle square (2 mHz to 100 kHz)

External Modulation Input^[6] (for AM, FM, PM, PWM)

Voltage range	± 5 V full scale
Input impedance	5 kΩ typical
Bandwidth	DC to 20 kHz

Sweep

Waveforms	Sine, Square, Ramp, Arb
Type	Linear or Logarithmic
Direction	Up or Down
Sweep time	1 ms to 500 s
Trigger	Single, External, or Internal
Marker	falling edge of sync signal (programmable frequency)

Burst^[7]

Waveforms	Sine, Square, Ramp, Triangle, Pulse, Noise, Arb
Type	Counted (1 to 50,000 cycles), Infinite, Gated
Start/Stop Phase	-360° to +360°
Internal Period	1 μs to 500 s
Gate Source	External trigger
Trigger source	Single, External or Internal

Trigger Characteristics

Trigger input	
Input level	TTL compatible
Slope	Rising or Falling, selectable
Pulse width	> 100 ns
Input impedance	>10 kΩ, DC coupled
Latency	< 500 ns
Jitter (rms)	6 ns (3.5 ns for pulse)
Trigger output	
Level	TTL compatible into ≥ 1 kΩ
Pulse width	> 400 ns
Output Impedance	50 Ω, typical
Maximum rate	1 MHz
Fanout	≤ 4 Agilent 33220As

Programming Times (typical)

Configuration times			
	USB	LAN	PIB
Function Change	111 ms	111 ms	111 ms
Frequency Change	1.5 ms	2.7 ms	1.2 ms
Amplitude Change	30 ms	30 ms	30 ms
Select User Arb	124 ms	124 ms	123 ms
Arb Download Times (binary transfer)			
	USB	LAN	PIB
64 k points	96.9 ms	191.7 ms	336.5 ms
16 k points	24.5 ms	48.4 ms	80.7 ms
4 k points	7.3 ms	14.6 ms	19.8 ms

General

Power Supply	CAT II 100 - 240 V @ 50/60 Hz (-5%, +10%) 100 - 120 V @ 400 Hz (±10%)
Power Consumption	50 VA max
Operating Environment	IEC 61010 Pollution Degree 2 Indoor Location
Operating Temperature	0°C to 55°C
Operating Humidity	5% to 80% RH, non-condensing
Operating Altitude	Up to 3000 meters
Storage Temperature	-30°C to 70°C
State Storage Memory	Power off state automatically saved. Four user-configurable stored states
Interface	USB, GPIB, and LAN standard
Language	SCPI - 1993, IEEE-488.2
Dimensions (W x H x D)	
Bench top	261.1 mm x 103.8 mm x 303.2mm
Rack mount	212.8mm x 88.3mm x 272.3mm
Weight	3.4 kg (7.5 lbs)
Safety Designed to	UL-1244, CSA 1010, EN61010
EMC Tested to	MIL-461C, EN55011, EN50082-1
Vibration and Shock	MIL-T-28800, Type III, Class 5
Acoustic Noise	30 dBa
Warm-up Time	1 hour
Warranty	1 year standard

Footnotes

1. Add 1/10th of output amplitude and offset spec per °C for operation outside the range of 18°C to 28°C
2. Autorange enabled
3. DC offset set to 0 V
4. Spurious output at low amplitude is -75 dBm typical
5. Add 1 ppm/°C average for operation outside the range of 18°C to 28°C
6. FSK uses trigger input (1 MHz maximum)
7. Sine and square waveforms above 6 MHz are allowed only with an "infinite" burst count

Ordering Information

Agilent 33220A

20 MHz function/arbitrary waveform generator

Accessories included

Operating manual, service manual, quick reference guide, IntuiLink waveform editor software, test data, USB cable, and power cord (see language option).

Options

- Opt. 001** External timebase reference
- Opt. A6J** ANSI Z540 calibration
- Opt. AB0** Taiwan: Chinese manual
- Opt. AB1** Korea: Korean manual
- Opt. AB2** China: Chinese manual
- Opt. ABA** English: English manual
- Opt. ABD** Germany: German manual
- Opt. ABF** France: French manual
- Opt. ABJ** Japan: Japanese manual

Other Accessories

- 34131A** Carrying case
- 34161A** Accessory pouch
- 34190A** Rackmount kit
- 34191A** Dual flange kit, 2U
- 34194A** Dual lock link kit



Agilent Advantage Services is committed to your success throughout your equipment's lifetime. To keep you competitive, we continually invest in tools and processes that speed up calibration and repair and reduce your cost of ownership. You can also use Infoline Web Services to manage equipment and services more effectively. By sharing our measurement and service expertise, we help you create the products that change our world.

www.agilent.com/find/advantageservices



Agilent Email Updates

www.agilent.com/find/emailupdates
Get the latest information on the products and applications you select.

Agilent Channel Partners

www.agilent.com/find/channelpartners
Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.

www.agilent.com
www.agilent.com/find/33220A

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	(11) 4197 3500
Mexico	01800 5064 800
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 375 8100

Europe & Middle East

Belgium	32 (0) 2 404 93 40
Denmark	45 70 13 15 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
*0.125 €/minute	
Germany	49 (0) 7031 464 6333
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
United Kingdom	44 (0) 131 452 0200

For other unlisted countries:

www.agilent.com/find/contactus

Revised: June 8, 2011

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2011
Published in USA, December 4, 2011
5988-8544EN



Agilent Technologies