

Differential Pressure Manometer

✓ **Measures Gauge/Differential Pressure from 0 to 138 inH₂O (inches of water)**
With 0.1 inH₂O resolution

Features:

- 11 selectable units with Max/Min recording and Relative time stamp
- Compensated temperature range 32 to 122°F (0-50°C)
- Data Hold, Auto power off, and Min/Max functions
- Large LCD display with backlighting
- Zero function for offset correction or measurement
- Built-in RS-232 interface (optional software and cable)
- Includes 9V battery, connection tubing and hard carrying case

Applications:

- HVAC
- Fume Hoods
- Pneumatic controls
- Hydraulics
- Medical equipment
- Clean rooms



Includes:

Meter with double molded test leads, magnetic hanging strap, Type K bead wire temperature probe (EX520 and EX530), carrying case, and one 9V battery



Specifications	Range	Resolution	Basic Accuracy
inH ₂ O	±138.3 inH ₂ O	0.1 inH ₂ O	±0.3%FS
psi	±5.000 psi	0.001 psi	±0.3%FS
bar	±0.344 bar	0.001 bar	±0.3%FS
mbar	±344.7 mbar	0.1 mbar	±0.3%FS
kPa	±34.47 kPa	0.01 kPa	±0.3%FS
inHg	±10.18 inHg	0.01 inHg	±0.3%FS
mmHg	±258.5 mmHg	0.1 mmHg	±0.3%FS
oz/in ²	±80.00 oz/in ²	0.01 oz/in ²	±0.3%FS
ftH ₂ O	±11.53 ftH ₂ O	0.01 ftH ₂ O	±0.3%FS
cmH ₂ O	±350.1 cmH ₂ O	0.1 cmH ₂ O	±0.3%FS
kg/cm ²	±0.351 kg/cm ²	0.001 kg/cm ²	±0.3%FS
Dimensions	7.1 x 2.8 x 1.1" (182 x 72 x 30mm)		
Weight	5.3oz (150g)		

Ordering Information:

406800Digital Manometer with PC Interface (11 units)
406800-NIST406800 with NIST Certificate
407752PC Software and Cable



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[406800-NIST](#)