


- 1 TERMINAL WRAPAROUND: 0.007"(0.18mm) APPROX. ON BOTH ENDS
- 2 AVAILABLE IN 2 DIFFERENT SERIES
- 3 FOR FURTHER INFORMATION SEE DATA SHEET FOR 3650 SERIES-LOW INDUCTANCE,HIGH FREQUENCY CHIP INDUCTOR


Technical drawing of a rectangular plate. The overall height is labeled A and the overall width is labeled B . The plate features a central slot with rounded ends. The slot is defined by two parallel horizontal lines, with the top and bottom edges of the slot having a rounded profile. The slot is centered horizontally and vertically within the plate.



RoHS Compliant

36501E	1.27	0.76	0.61	0.15	0.23	0.56	0.66	0.50	0.46
36501J	1.80	1.12	1.02	0.38	0.33	0.86	1.02	0.64	0.64
SERIES	A MAX.	B MAX.	C MAX.	D REF.	F	G	H	K	J

DWN	SUBHASH.M	14-NOV-08
CHK	PRAKASH.S	14-NOV-08
APVD	STEPHEN.P	14-NOV-08

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
		0 PLC	± 0.2
		1 PLC	± 0.1
		2 PLC	$\pm -$
		3 PLC	$\pm -$
		4 PLC	$\pm -$
		ANGLES	$\pm 5^{\circ}$
MATERIAL		FINISH	
-		-	



TE Connectivity

NAME LOW INDUCTANCE,
HIGH FREQUENCY CHIP
INDUCTOR SERIES 3650

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A 3	00779	C- 1624112	-

CUSTOMER DRAWING	SCALE 20:1	SHEET 1 OF 1	REV BA1
------------------	------------	--------------	---------