



United States > All 3M Products > Market Segments > Electronics, Electrical, and Communications > 3M™ Tapes and Adhesives for Electronics > Cushioning Solutions > Cushioning Materials > Bumpon Products > 3M™ Bumpon™ Protective Products SJ5302 Clear, 3000 per case

3M™ Bumpon™ Protective Products SJ5302 Clear, 3000 per case

3M ID 70070753176 UPC# 00021200402302

Print Share



Network Access Message: The page

3M™ Bumpon™ Protective Product SJ5302 is a self-adhesive rubber bumper designed to be used as feet, stops and spacers. The hemispherical shape provides excellent sound damping and energy absorption. Clear, 0.312 in. wide x .085 in. high.

All 3M™ Bumpon™ Protective Products feature a plasticizer-free, urethane composition which exhibits:

- Easy application with 3M pressure sensitive adhesives.
- High skid-resistance.
- Won't scratch or stain surfaces.
- Reduces vibration and noise.
- Will not crack or harden.



Buy Online at Shop3M.com

Need Help?

Questions? We can help
[Contact Us](#)

OverviewSupport

Suggested Applications

Use almost anywhere slamming, scratching, nicking, scuffing, marring, sliding, vibration, or noise could be a problem for your product.

- Feet on the bottom of small appliances, desktop or handheld electronic devices, electronic cabinetry, telephones, keyboards, foot pedals, scales, clocks, speakers, dispensers, and computers.
- Stops for cabinet doors, lids, and drawers.
- Spacers for picture frames to provide alignment; for electronics and automotive applications and aid in assembly.
- Protectors to prevent damage in shipping, and keep parts from direct contact with each other.

Specifications

Adhesive Type	Acrylic (A20)
Application	Notebook Computer Non-Skid Feet, Small Electronic Device Cushioning Stops, Small Electronic Device Feet, Small Kitchen Appliance Feet - Recessed Application
Availability	Stocked
Backing Material	Polyurethane
Color	Clear
Diameter	0.312 Inch
Diameter (metric)	7.9 Millimetre
Hardness	75 Shore M
Height	0.085 Inch
Height (metric)	2.2 Millimetre
Height-Thickness Range	0.001 - 0.099 in
Height-Thickness Range (metric)	2.0 - 2.9 mm
Market Segment	Appliances, Electronics
Primary Liner	Translucent Polyester Film
Product Form	Molded
Product Series	SJ5302
Shape	Circular-Hemisphere
Substrate	ABS, Acrylic, Glass, Metals, Polycarbonate
Width-Diameter Range	0.300 - 0.399 in
Width-Diameter Range (metric)	1.0 - 9.9 mm

Product Disclaimer

- The technical information and data shown on this page should be considered representative or typical only and should not be used for specification purposes.
- 3M products shown on this website may not be available in all geographic regions or may not be available at this time. Please contact your local sales representative to determine product availability.

