


P.C. MOUNTING

O.P. (MM)	P.T. (MM)
8.8 ± 0.8	1.6 MAX.


O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



CIRCUIT: SPDT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
3. RATING: 3A @125VAC
1.5A @250VAC UL
4. OPERATING FORCE: 40± 15 GRAMS
5. OPERATING TEMP: -25°C TO 75°C
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
8. DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
9. ▲ DENOTES CRITICAL PARAMETER.
10. PACKAGED IN TRAYS, 120 PIECES PER TRAY.
11. 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC

SCALE: 3:1



C	18157	REMOVE CE APPROVED FROM NOTES	6/24/08	BLR
B	18089	NOTE 10 WAS 1000 PIECES PER BAG	5/9/08	RC
A	17809	RELEASE FOR PRODUCTION	10/26/07	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E-SWITCH™

TITLE SS0750301F040P1A

SCALE 4:1

DATE 6/24/2008

DR	BLR
----	-----

DWG
Q971003

REV
C