




- 1 POINT OF PLATING THICKNESS MEASUREMENT.
- 2 COPPER ALLOY PER ASTM-B-16
- 3 .000050 GOLD PER MIL-G-45204 OVER
.000030 NICKEL PER QQ-N-290.

-	1.359 [34.52]	.770 [19.56]	1-206210-0
OBSOLETE	1.379 [35.03]	.785 [19.94]	206210-8
-	.939 [23.85]	.345 [8.76]	206210-6
-	1.434 [36.42]	.840 [21.34]	206210-4
-	1.179 [29.95]	.585 [14.86]	206210-2
REMARKS	B DIM REF	A DIM±.010 [0.25]	PART #

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [MM] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ±.005 [0.13] ANGLES ± -	DR 8-11-93 J.A.BAKER CHK 08-15-93 A. SHARP APPD 08-15-93 A. SHARP APPD 08-15-93 A. SHARP PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	AMP AMP Incorporated Harrisburg, PA 17105-3508 NAME POSTED PIN CONTACT SIZE #20 SIZE D 00779 CAGE CODE C-206210 DRAWING NO SCALE 10:1 SHEET 1 OF 1
---	---	---

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.