

## Internet Office 500VA Low-profile Standby 120V UPS

MODEL NUMBER: **TM500**



### Description

Tripp Lite's space-saving TM500 Under-Monitor UPS System provides complete power protection for your entire computer set-up, even power hungry peripherals. 500 VA of battery backup maintains your Internet connection, allowing you to work online through short blackouts or safely shut down during longer ones. Unique design features 6 outlets (3 UPS & surge + 3 surge-only), individually switched outlets and diagnostic LEDs. Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment. A 6-ft. telephone cord is also included. \$150,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico, & Canada Only).

### Features

- 500 VA output power rating (300 watts)
- Up to 30 minutes typical backup time
- 6 protected outlets (3 UPS & surge + 3 surge-only); 6 ft. cord
- Unique space-saving, under-monitor console design
- Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment; 6 ft. telephone cord included
- Complete surge protection and EMI/RFI noise filtering
- \$150,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico, & Canada Only) —
- Master switch and 4 auxiliary switches give you control over multiple pieces of your equipment
- 4 diagnostic LEDs indicate AC Present, line fault, On Battery & Battery Low/Replace

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	500
Output Watt Capacity (Watts)	300
Nominal Output Voltage(s) Supported	120V
Frequency Compatibility	60 Hz

### Highlights

- 6 outlets (3 UPS/surge, 3 surge-only)
- Built-in RJ11 jacks provide complete modem/fax surge protection
- Under-monitor design supports virtually any monitor
- \$150,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

### Package Includes

- TM500 UPS System
- 6-ft. telephone cord
- Warranty information
- Instruction manual

Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles	6 5-15R outlet(s)
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
<b>INPUT</b>	
Rated input current (Maximum Load)	15A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
<b>BATTERY</b>	
Full Load Runtime (min.)	6 min. (300w)
Half Load Runtime (min.)	17 min. (150w)
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90%
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332031662
<b>LEDS ALARMS &amp; SWITCHES</b>	
LED Indicators	Front panel LEDs indicate line power status, battery power status and battery low/replace status
Audible Alarm	Audible alarm indicates power-failure
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation, plus 4 switches control individual output receptacles
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC Noise Suppression	Yes

<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Under-monitor console
Primary Form Factor	Under Monitor
UPS Power Module Dimensions (hwd, in.)	2 x 13.5 x 12.5
UPS Power Module Dimensions (hwd, cm)	5.1 x 34.3 x 31.8
UPS Power Module Weight (lbs.)	11.7
UPS Power Module Weight (kg)	5.3
UPS Shipping Dimensions (hwd / in.)	4 x 15 x 16
UPS Shipping Dimensions (hwd / cm)	10.2 x 38.1 x 40.6
Shipping Weight (lbs.)	12
Shipping Weight (kg)	5.4
UPS Housing Material	PVC
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	65.1
Battery Mode BTU / Hr. (Full Load)	88.7
AC Mode Efficiency Rating (100% Load)	94%
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	101
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico)
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.