







Recommended P.C. Board Layout



SIGN	DATE	DESCRIPTION	APPROVER
△	2016.11.13	Part change Rev. D	SHIN
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

Material

- Insulator: Glass filled Polyester
- Flammability: UL94V-0
- Contacts: Phosphor Bronze
- Contact Plating: See options
- Shell: Copper Alloy, 80u Ni over 50u Cu

Ratings

- Current: 1.5A
- Voltage: 30V AC(r.m.s.)
- Dielectric Withstanding Voltage: 500V AC at sea level
- Contact Resistance: <30mΩ
- Insulation Resistance: >1,000 MΩ
- Operating Temperature: -55° ~ +85°
- Mating Force: 3.5Kg Max
- Umating Force: 1Kg. Min

RoHS Compliant

PART NUMBER:

USB-A1VSXX

COLOR:
B: Black
W: White

PLATING:
6: Selective Au Flash/50u" Ni
8: Selective 30u" Au/50u" Ni (USB 2.0)

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

ON-SHORE TECHNOLOGY, INC.							
TITLE	USB - A type, Vertical, thru hole, single port						
PART NO.	USB-A1VSXX			DWG NO.	USB-A1VSXX.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN	4050		Tolerance	
	Sandy 2016.03.04	Sandy 2016.03.04	Sandy 2016.03.04			UNIT: mm	X° ±1°
				SHEET: 01/01		SCALE: NONE	X.X ±0.30
						REV.: D	X.XX ±0.25
							X.XXX ±0.15