

Distributed by:



[www.Jameco.com](http://www.Jameco.com) ♦ 1-800-831-4242

The content and copyrights of the attached  
material are the property of its owner.

# High Current/High Density Power Connector System

The power Connector series is designed for high current / high density applications which require the design flexibility of wire to wire and wire to board configurations in the interconnection system. The power connector system is appropriate for both power and signal applications as it can carry currents of up to 9 amperes per circuit.

## 4256T Series Crimp Terminal

### Specifications:

#### • Electrical:

- Voltage Rating: 600V (R.M.S.)
- Contact Resistance: 10mΩ max.
- Dielectric strength: 1500V AC
- UL File No. : E114003
- CSA File No. : LR86545

#### Mechanical:

- Temperature Rise: (Carrying rated current load) 30°C max.

### Ordering & Dimensional Information:

Part No.	Wire Size (AWG)	Max. Ins. Dia. (mm)	Material	Thickness (mm)	Finish	Chain Type			
4256T1	#22 ~ #28	1.8	Brass	0.2	Tin-plated	End Chain			
4256T2	#18 ~ #24	3.1							
4256T3	#16								
4256TP1	#22 ~ #28	1.8	Phosphor Bronze						
4256TP2	#18 ~ #24	3.1							
4256TP3	#16								

