


-	-	-	-	-	-	-	6
-	-	-	-	-	-	-	64
I	I	I	I	I	3-18031-0	SCR, SET, CUP POINT M6 X 6.0	63
-	-	-	-	-	-	-	62
2	2	2	2	2	2-18032-5	SCR, SET, FLT POINT M5 X 20.0	61
I	I	I	I	I	18024-7	SCR, BTN SKT HD CAP (M4 X 10.0)	60
I	I	I	I	I	5-18022-2	SCR, HEX HD CAP M4 X 8.0	59
-	-	-	-	-	-	-	58
I	I	I	I	I	985575-3	SCR, FLT SKT HD CAP M3 X 10.0	57
I	I	I	I	I	1338685-1	PAWL, FEED	56
-	-	-	-	-	-	-	55
4	4	4	4	4	18024-8	SCR, BTN SKT HD CAP (M4 X 12.0)	54
2	2	2	2	2	1-18023-3	SCR, SKT HD CAP M4 X 16.0	53
I	I	I	I	I	18030-1	NUT, HEX, REG M3	52
I	I	I	I	I	811242-5	BUMPER, HOLD DOWN	51
I	I	I	I	I	690753-2	SPACER, TONKER	50
I	I	I	I	I	18024-3	SCR, BTN SKT HD CAP (M3 X 10.0)	49
I	-	-	I	-	1338675-1	CAM, UNIVERSAL PRE FEED	48
-	I	I	-	I	1338676-1	CAM, UNIVERSAL POST-FEED	47
I	I	I	I	I	1320999-3	APPLICATOR SUBASSEMBLY, HDI	46
I	I	I	I	I	690191-1	PLUG, NYLON	45
I	I	I	I	I	1338660-1	RAM	44
-	-	-	-	-	-	-	43
-	-	-	-	-	-	-	42
I	I	I	I	I	2-18024-6	SCR, BTN SKT HD CAP (M8 X 25.0)	41
-	-	-	-	-	-	-	40
I	I	I	I	I	690125-1	SHIM SUB-ASSY	39
I	I	I	I	I	1-469367-2	SHIM	38
I	I	I	I	I	879103-3	DISC, ADJUSTABLE GEITNER	37
-	-	-	-	-	-	-	36
-	-	-	-	-	-	-	35
I	I	I	I	I	2-1320934-5	SUPPORT, TERMINAL	34
2	2	2	2	2	1-18024-0	SCR, BTN SKT HD CAP (M4 X 20.0)	33
I	I	I	I	I	18027-2	WASHER, FLAT, REG M4	32
I	I	I	I	I	1-18023-2	SCR, SKT HD CAP M4 X 12.0	31
I	I	I	I	I	1320908-1	SPACER, STRIP GUIDE	30
I	I	I	I	I	1633073-2	STRIP GUIDE ASSEMBLY	29
I	I	I	I	I	1-455888-7	SPACER, CRIMPER	28

- | | | | | | | | |
|---|---|---|---|---|-------------|---------------------------------|----|
| 2 | 2 | 2 | 2 | 2 | 1-22284-0 | SPRING, COMPRESSION | 27 |
| 1 | 1 | 1 | 1 | 1 | 356835-1 | LEVER, DRAG RELEASE | 26 |
| 1 | 1 | 1 | 1 | 1 | 240792-1 | DRAG, TERMINAL | 25 |
| 1 | 1 | 1 | 1 | 1 | 1320928-1 | PLATE, STRIP GUIDE | 24 |
| 1 | 1 | 1 | 1 | 1 | 980371-4 | SCR, SKT HD SHLDR 5.0 DIA X 6.0 | 23 |
| - | 1 | 1 | - | 1 | 690472-2 | STRIPPER | 22 |
| 1 | 1 | 1 | 1 | 1 | 1-18023-1 | SCR, SKT HD CAP M4 X 10.0 | 21 |
| 4 | 4 | 4 | 4 | 4 | 18025-2 | WASHER, SPRG LOCK, REG M4 | 20 |
| 1 | - | - | 1 | - | 690472-1 | STRIPPER | 19 |
| - | - | - | - | - | - | - | 18 |
| - | - | 1 | - | - | 1338684-2 | HOLDER, SHEAR, NO-CUT | 17 |
| - | - | - | - | - | - | - | 16 |
| - | - | - | - | - | - | - | 15 |
| - | - | - | - | - | - | - | 14 |
| - | - | - | - | - | - | - | 13 |
| 1 | 1 | 1 | 1 | 1 | 5-22280-0 | SPRING, COMPRESSION | 12 |
| 1 | 1 | 1 | 1 | 1 | 356885-5 | STOP, SHEAR | 11 |
| 1 | 1 | - | 1 | 1 | 1-1320921-0 | SHEAR HOLDER, FRONT, CUT | 10 |

1	1	1	1	1	356885-5	STOP, SHEAR	11
1	1	-	1	1	1-1320921-0	SHEAR HOLDER, FRONT, CUT	10
1	1	1	1	1	318707-1	FLOATING SHEAR, FRONT	9
2	2	1	1	1	1633129-2	ANVIL, COMBINATION .062	8
1	1	1	1	1	5-240641-0	SPACER	7
-	-	-	-	-	-	-	6
1	1	1	1	1	1338680-1	DEPRESSOR, SHEAR	5
1	1	1	1	1	238011-4	BLOCK, CRIMPER SPACER	4

2	2	1	1	1	1-456135-7	CRIMPER, INSULATION O PREMIUM	3		
1	1	1	1	1	1-455888-5	SPACER, CRIMPER	2		
2	2	1	1	1	3-456403-2	CRIMPER, WIRE PREMIUM	1		
5	-72	-71	-6	-2	-1	PART NO	DESCRIPTION	ITEM NO	
1. THIS DOCUMENT IS THE PROPERTY OF THE COMPANY THAT PREPARED IT. IT IS TO BE USED FOR THE PROJECT AND THE CONTRACTING OR ENGINEERING ORGANIZATION TO WHICH IT WAS SUBMITTED. IT IS NOT TO BE REPRODUCED OR COPIED FOR THE LATTERS USE.						DWN M. CLIFFORD 11JUL2005	tyco <i>Electronics</i> Tyco Electronics Harrisburg, PA 17105-3608	OBsolete NOT the LATEST REVISION	
TOLERANCES UNLESS OTHERWISE SPECIFIED:						APVD F. BACKHURST 11JUL2005 NAME	FINE ADJUST SIDE FEED HDI APPLICATOR		
 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH						APPLICATION SPEC See Table	SIZE CARD CODE DRAWING NO A 00779 © 1528600		RESTRICTED TO
WEIGHT -						CUSTOMER DRAWING	SCALE 3:5 SHEET 1 OF 1 REV A		