




- NOTES:
- MATERIALS AND FINISHES:  
BODY - BERYLLIUM COPPER, GOLD PLATING,  
CONTACT - BERYLLIUM COPPER, GOLD PLATING,  
INSULATOR - PTFE
  - ELECTRICAL:  
A. IMPEDANCE: 50 OHM  
B. FREQUENCY RANGE: DC - 6 GHz
  - PHYSICAL:  
A. DURABILITY: 500 CYCLES MIN.  
B. TEMPERATURE RANGE: -65° C TO 165° C
  - PACKAGING:  
A. QUANTITY: SINGLE PACK  
B. MARKING:  
AMPHENOL  
908-NM22109  
DATE CODE

| 908-NM22109                                                                                           |     | REVISIONS              |         |       |      |
|-------------------------------------------------------------------------------------------------------|-----|------------------------|---------|-------|------|
| DRAWING NO.                                                                                           | REV | DESCRIPTION            | DATE    | ECO   | APPR |
| FIRST ANGLE PROJ.  | A   | RELEASE TO MFG         | 5/8/09  | 47457 | CL   |
|                                                                                                       | B   | IMPROVED MATING FORCES | 8/27/12 | 49216 | DD   |



SCALE 6.000



RECOMMENDED PCB LAYOUT  
(TOP MOUNT)  
SCALE 6.000

NON-MAGNETIC

CUSTOMER OUTLINE DRAWING  
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                                              |                                           |                  |                                                          |       |  |                                                                                                                |                            |          |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------|-------------------------------------------|------------------|----------------------------------------------------------|-------|--|----------------------------------------------------------------------------------------------------------------|----------------------------|----------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:<br>2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES<br>±.015 (0,381 mm) ±.005 (0,127 mm) ± 1°                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | MATERIAL<br>SEE NOTES                                        | DRAWN<br>NISCHIT MV                       | DATE<br>8-May-08 | TITLE<br>MMCX JACK PCB<br>SMT REAR MOUNT<br>OR TOP MOUNT |       |  | Amphenol<br>Amphenol Corporation<br>Communication and Network<br>Products Division<br>Danbury, CT U.S.A. 06810 |                            |          |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                                              | ENGINEER<br>NISCHIT MV                    | DATE<br>8-May-08 |                                                          |       |  |                                                                                                                |                            |          |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | REFERENCE<br>GEN# ASSYF11_MMCX<br>EAR# 1293<br>615X-1740-100 | APPROVED<br>K. CAPOZZI                    | DATE<br>5/8/09   | CODE ID<br>74868                                         |       |  | DWG SIZE<br>B                                                                                                  | DRAWING NO.<br>908-NM22109 | REV<br>B |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                                              | CAD FILE<br>I:\SMP\908-NM22109908-NM22109 |                  |                                                          |       |  |                                                                                                                |                            |          |
| NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data. |                                                              |                                           |                  |                                                          |       |  |                                                                                                                |                            |          |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                                              |                                           | SCALE: 10.0:1    |                                                          | SHEET |  | 2 OF 2                                                                                                         |                            |          |