






2.54-4.32 [.100-.170]	ø0.36-ø0.66 [ø.014-ø.026]	TIN 	TIN 	 2-5645955-1
2.54-4.32 [.100-.170]	ø0.36-ø0.66 [ø.014-ø.026]	GOLD 	TIN 	 1-5645955-2
2.54-4.32 [.100-.170]	ø0.36-ø0.66 [ø.014-ø.026]	TIN 	TIN 	 1-5645955-1
2.54-4.32 [.100-.170]	ø0.36-ø0.66 [ø.014-ø.026]	GOLD 	TIN 	 5645955-2
LENGTH	DIA 	SPRING	EYELET	PART NO.
PIN		FINISH		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE 25JAN06		 TE Connectivity			
		CHK J. HAVENER 25JAN06					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. HAVENER 25JAN06		NAME	
		PRODUCT SPEC 108-14008		MINIATURE SPRING SOCKET ASSY SERIES 2 LONG WITH SEALANT			
		APPLICATION SPEC 114-26004					
		WEIGHT 0					
MATERIAL 		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C=5645955	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 1:1	SHEET 1 OF 1	REV A	