




HEAT SHRINK TUBING

TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved



✓ Active

TE CONNECTIVITY (TE) **CGPT-6/2-X-SP**

Raychem | CGPT

CGPT-6/2-X-SP
TE Internal Number: 0651914001
Alias ID: 1-1190492-3

EU RoHS Compliant

EU ELV Compliant

Wall Type Single

Resistant To Fluids, Mechanical Damage, Strain

Low Outgassing No

Product Source Czech Republic

Packaging Method Spool

DOCUMENTATION

Catalog Pages/Data Sheets

CGPT Pages From 9-1773447-9

PDF

English

At-Application-Tooling-For-Raychem-Heat-Shrink-Product-2-1773452-8

PDF

English

Product Specifications

Product Specification

CGPT Sleeving

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Wall Type Single

Product Family CGPT

Electrical Characteristics

Voltage (Max) (kV) .6

Body Features

Shrink Ratio 3:1

Color Clear

Flexibility Flexible

Material Irradiated Modified Polyolefin

Fluid Type Gasoline, Hydraulic Fluid, Lubricating Oil

Dimensions

Expanded Inside Diameter (Min) 6 mm [.236 in]

Recovered Wall Thickness (Nominal) .65 mm [.026 in]

Recovered Inside Diameter (Max) 2 mm [.079 in]

Recovered Wall Thickness (Tolerance) .12 mm [.005 in]

Usage Conditions

Shrink Temperature (Min) (°C) 80

Resistant To Fluids, Mechanical Damage, Strain

Recovery Temperature (°C) 120

Operating Temperature Range (°C) -40 – 135

Flammability Non-Flame-Retardant

Fluid Resistance Splash Protection

Product Availability

Applicable Region Asia, EMEA

Packaging Features

Packaging Method Spool

Other

Low Outgassing No

Product Source Czech Republic

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF

