

# MIL-C-11015 & 39014 Multilayer Ceramic Capacitors

## CK and CKR Military Grade Capacitors



MIL-C-11015 & 39014 - CK and CKR - military grade capacitors are available as radial and axial leaded capacitors with the option of hot solder dipped leads on the CKRs.




### Highlights

- Available on tape and reel
- Molded case construction
- CKR available with stand-off
- Hot solder dip leads on Type CKR

### Specifications

**Capacitance Range:** 10 pF to 3.3  $\mu$ F  
**Voltage Range:** 50, 100, 200 Vdc  
**Temperature Coefficient:** X7R (Mil BX or BR)

### Outline Drawings



#### Radial

| Type  | Inches |      |      |      |      | mm  |     |     |     |     |
|-------|--------|------|------|------|------|-----|-----|-----|-----|-----|
|       | L      | H    | T    | S    | d    | L   | H   | T   | S   | d   |
| CK05  | .190   | .190 | .090 | .200 | .025 | 4.8 | 4.8 | 2.3 | 5.1 | .64 |
| CKR05 | .190   | .190 | .090 | .200 | .025 | 4.8 | 4.8 | 2.3 | 5.1 | .64 |
| CK06  | .290   | .290 | .090 | .200 | .025 | 7.4 | 7.4 | 2.3 | 5.1 | .64 |
| CKR06 | .290   | .290 | .090 | .200 | .025 | 7.4 | 7.4 | 2.3 | 5.1 | .64 |

#### Axial

| Type  | Inches |      |      | mm  |      |     |
|-------|--------|------|------|-----|------|-----|
|       | D      | L    | d    | D   | L    | d   |
| CK12  | .090   | .160 | .020 | 2.3 | 4.0  | .51 |
| CKR11 | .090   | .160 | .020 | 2.3 | 4.0  | .51 |
| CK13  | .090   | .250 | .020 | 2.3 | 6.4  | .51 |
| CKR12 | .090   | .250 | .020 | 2.3 | 6.4  | .51 |
| CK14  | .140   | .390 | .025 | 3.6 | 9.9  | .64 |
| CKR14 | .140   | .390 | .025 | 3.6 | 9.9  | .64 |
| CK15  | .250   | .500 | .025 | 6.4 | 12.7 | .64 |
| CKR15 | .250   | .500 | .025 | 6.4 | 12.7 | .64 |
| CK16  | .350   | .690 | .025 | 8.9 | 17.5 | .64 |
| CKR16 | .350   | .690 | .025 | 8.9 | 17.5 | .64 |

#### TO ORDER MIL-C-11015 PARTS:

Order by CK part number shown in Ratings Table  
 Example: CK05BX104M

#### TO ORDER MIL-C-39014 PARTS:

Indicate the prefix M39014/-- followed by the applicable MIL dash number. Example: For M39014/01-1594 (CKR05BX104MS); order M39014/011594

# MIL-C-11015 & 39014 Multilayer Ceramic Capacitors

## Ratings

| Cap                                      | Tol.<br>% | MIL-C-11015/18 | MIL-C-39014/01 | 39014/01 Failure Rate Levels |      |      |      |
|------------------------------------------|-----------|----------------|----------------|------------------------------|------|------|------|
|                                          |           |                | References     | M                            | P    | R    | S    |
| 50 Vdc - Radial Leaded - CK05/M39014/01  |           |                |                |                              |      |      |      |
|                                          |           |                | CKR05BX123K*   | 1457                         | 1497 | 1537 | 1577 |
|                                          |           |                | CKR05BX153K*   | 1458                         | 1498 | 1538 | 1578 |
|                                          |           |                | CKR05BX153M*   | 1459                         | 1499 | 1539 | 1579 |
|                                          |           |                | CKR05BX183K*   | 1460                         | 1500 | 1540 | 1580 |
|                                          |           |                | CKR05BX223K*   | 1461                         | 1501 | 1541 | 1581 |
|                                          |           |                | CKR05BX223M*   | 1462                         | 1502 | 1542 | 1582 |
|                                          |           |                | CKR05BX273K*   | 1463                         | 1503 | 1543 | 1583 |
|                                          |           |                | CKR05BX333K*   | 1464                         | 1504 | 1544 | 1584 |
|                                          |           |                | CKR05BX333M*   | 1465                         | 1505 | 1545 | 1585 |
|                                          |           |                | CKR05BX393K*   | 1466                         | 1506 | 1546 | 1586 |
|                                          |           |                | CKR05BX473K*   | 1467                         | 1507 | 1547 | 1587 |
|                                          |           |                | CKR05BX473M*   | 1468                         | 1508 | 1548 | 1588 |
|                                          |           |                | CKR05BX563K*   | 1469                         | 1509 | 1549 | 1589 |
|                                          |           |                | CKR05BX683K*   | 1470                         | 1510 | 1550 | 1590 |
|                                          |           |                | CKR05BX683M*   | 1471                         | 1511 | 1551 | 1591 |
|                                          |           |                | CKR05BX823K*   | 1472                         | 1512 | 1552 | 1592 |
|                                          |           |                | CKR05BX104K*   | 1473                         | 1513 | 1553 | 1593 |
|                                          |           |                | CKR05BX104M*   | 1474                         | 1514 | 1554 | 1594 |
| 100 Vdc - Radial Leaded - CK05/M39014/01 |           |                |                |                              |      |      |      |
|                                          |           |                | CKR05BX122K*   | 1239                         | 1279 | 1319 | 1359 |
|                                          |           |                | CKR05BX152K*   | 1240                         | 1280 | 1320 | 1360 |
|                                          |           |                | CKR05BX152M*   | 1441                         | 1481 | 1521 | 1561 |
|                                          |           |                | CKR05BX182K*   | 1442                         | 1482 | 1522 | 1562 |
|                                          |           |                | CKR05BX222K*   | 1443                         | 1483 | 1523 | 1563 |
|                                          |           |                | CKR05BX222M*   | 1444                         | 1484 | 1524 | 1564 |
|                                          |           |                | CKR05BX272K*   | 1445                         | 1485 | 1525 | 1565 |
|                                          |           |                | CKR05BX332K*   | 1446                         | 1486 | 1526 | 1566 |
|                                          |           |                | CKR05BX332M*   | 1447                         | 1487 | 1527 | 1567 |
|                                          |           |                | CKR05BX392K*   | 1448                         | 1488 | 1528 | 1568 |
|                                          |           |                | CKR05BX472K*   | 1449                         | 1489 | 1529 | 1569 |
|                                          |           |                | CKR05BX472M*   | 1450                         | 1490 | 1530 | 1570 |
|                                          |           |                | CKR05BX562K*   | 1451                         | 1491 | 1531 | 1571 |
|                                          |           |                | CKR05BX682K*   | 1452                         | 1492 | 1532 | 1572 |
|                                          |           |                | CKR05BX682M*   | 1453                         | 1493 | 1533 | 1573 |
|                                          |           |                | CKR05BX822K*   | 1454                         | 1494 | 1534 | 1574 |
|                                          |           |                | CKR05BX103K*   | 1455                         | 1495 | 1535 | 1575 |
|                                          |           |                | CKR05BX103M*   | 1456                         | 1496 | 1536 | 1576 |

| Cap                                      | Tol. | MIL-C-11015/18 | MIL-C-39014/01 | 39014/01 Failure Rate Levels |      |      |      |
|------------------------------------------|------|----------------|----------------|------------------------------|------|------|------|
|                                          | %    |                | References     | M                            | P    | R    | S    |
| 200 Vdc - Radial Leaded - CK05/M39014/01 |      |                |                |                              |      |      |      |
| FOR EQUIVALENT REPLACEMENT               |      |                | CKR05BX100K*   | 1201                         | 1241 | 1281 | 1321 |
|                                          |      |                | CKR05BX100M*   | 1202                         | 1242 | 1282 | 1322 |
|                                          |      |                | CKR05BX120K*   | 1203                         | 1243 | 1283 | 1323 |
|                                          |      |                | CKR05BX150K*   | 1204                         | 1244 | 1284 | 1324 |
|                                          |      |                | CKR05BX150M*   | 1205                         | 1245 | 1285 | 1325 |
|                                          |      |                | CKR05BX180K*   | 1206                         | 1246 | 1286 | 1326 |
|                                          |      |                | CKR05BX220K*   | 1207                         | 1247 | 1287 | 1327 |
|                                          |      |                | CKR05BX220M*   | 1208                         | 1248 | 1288 | 1328 |
|                                          |      |                | CKR05BX270K*   | 1209                         | 1249 | 1289 | 1329 |
|                                          |      |                | CKR05BX330K*   | 1210                         | 1250 | 1290 | 1330 |
|                                          |      |                | CKR05BX330M*   | 1211                         | 1251 | 1291 | 1331 |
|                                          |      |                | CKR05BX390K*   | 1212                         | 1252 | 1292 | 1332 |
|                                          |      |                | CKR05BX470K*   | 1213                         | 1253 | 1293 | 1333 |
|                                          |      |                | CKR05BX470M*   | 1214                         | 1254 | 1294 | 1334 |
|                                          |      |                | CKR05BX560K*   | 1215                         | 1255 | 1295 | 1335 |
|                                          |      |                | CKR05BX680K*   | 1216                         | 1256 | 1296 | 1336 |
|                                          |      |                | CKR05BX680M*   | 1217                         | 1257 | 1297 | 1337 |
|                                          |      |                | CKR05BX820K*   | 1218                         | 1258 | 1298 | 1338 |
|                                          |      |                | CKR05BX101K*   | 1219                         | 1259 | 1299 | 1339 |
|                                          |      |                | CKR05BX101M*   | 1220                         | 1260 | 1300 | 1340 |
|                                          |      |                | CKR05BX121K*   | 1221                         | 1261 | 1301 | 1341 |
|                                          |      |                | CKR05BX151K*   | 1222                         | 1262 | 1302 | 1342 |
|                                          |      |                | CKR05BX151M*   | 1223                         | 1263 | 1303 | 1343 |
|                                          |      |                | CKR05BX181K*   | 1224                         | 1264 | 1304 | 1344 |
|                                          |      |                | CKR05BX221K*   | 1225                         | 1265 | 1305 | 1345 |
|                                          |      |                | CKR05BX221M*   | 1226                         | 1266 | 1306 | 1346 |
|                                          |      |                | CKR05BX271K*   | 1227                         | 1267 | 1307 | 1347 |
|                                          |      |                | CKR05BX331K*   | 1228                         | 1268 | 1308 | 1348 |
|                                          |      |                | CKR05BX331M*   | 1229                         | 1269 | 1309 | 1349 |
|                                          |      |                | CKR05BX391K*   | 1230                         | 1270 | 1310 | 1350 |
|                                          |      |                | CKR05BX471K*   | 1231                         | 1271 | 1311 | 1351 |
|                                          |      |                | CKR05BX471M*   | 1232                         | 1272 | 1312 | 1352 |
|                                          |      |                | CKR05BX561K*   | 1233                         | 1273 | 1313 | 1353 |
|                                          |      |                | CKR05BX681K*   | 1234                         | 1274 | 1314 | 1354 |
|                                          |      |                | CKR05BX681M*   | 1235                         | 1275 | 1315 | 1355 |
|                                          |      |                | CKR05BX821K*   | 1236                         | 1276 | 1316 | 1356 |
|                                          |      |                | CKR05BX102K*   | 1237                         | 1277 | 1317 | 1357 |
|                                          |      |                | CKR05BX102M*   | 1238                         | 1278 | 1318 | 1358 |

\*Insert proper letter symbol for Failure Rate Designator

M = 1% / 1000 Hours, P = 0.1% / 1000 Hours

R = 0.01% / 1000 Hours, S = 0.001% / 1000 Hours

Add 'V' at end of failure rate designator if stand-off design is required, (CKR only)

Add 'TR' to end of part number for Tape & Reel

Leads will be trimmed to .625" length

CK05 - 2,000 per reel

CKR05 - 1,700 per reel

(Available in full reels only)

# MIL-C-11015 & 39014 Multilayer Ceramic Capacitors

## Ratings

| Cap                                     | Tol.<br>% | MIL-C-11015/19 | MIL-C-39014/02                           | 39014/02 Failure Rate Levels |      |              |      |      |      |      |
|-----------------------------------------|-----------|----------------|------------------------------------------|------------------------------|------|--------------|------|------|------|------|
|                                         |           |                | References                               | M                            | P    | R            | S    |      |      |      |
| 50 Vdc - Radial Leaded - CK06/M39014/02 |           |                |                                          |                              |      |              |      |      |      |      |
|                                         |           |                | CKR06BX124K*                             | 1233                         | 1273 | 1313         | 1353 |      |      |      |
|                                         |           |                | CKR06BX154K*                             | 1234                         | 1274 | 1314         | 1354 |      |      |      |
|                                         |           |                | CKR06BX184K*                             | 1235                         | 1275 | 1315         | 1355 |      |      |      |
|                                         |           |                | CKR06BX224K*                             | 1236                         | 1276 | 1316         | 1356 |      |      |      |
|                                         |           |                | CKR06BX274K*                             | 1237                         | 1277 | 1317         | 1357 |      |      |      |
|                                         |           |                | CKR06BX334K*                             | 1238                         | 1278 | 1318         | 1358 |      |      |      |
|                                         |           |                | CKR06BX394K*                             | 1239                         | 1279 | 1319         | 1359 |      |      |      |
|                                         |           |                | CKR06BX474K*                             | 1240                         | 1280 | 1320         | 1360 |      |      |      |
|                                         |           |                | CKR06BX564K*                             | 1404                         | 1408 | 1412         | 1416 |      |      |      |
|                                         |           |                | CKR06BX684K*                             | 1405                         | 1409 | 1413         | 1417 |      |      |      |
|                                         |           |                | CKR06BX824K*                             | 1406                         | 1410 | 1414         | 1418 |      |      |      |
|                                         |           |                | CKR06BX105K*                             | 1407                         | 1411 | 1415         | 1419 |      |      |      |
|                                         |           |                | 100 Vdc - Radial Leaded - CK06/M39014/02 |                              |      |              |      |      |      |      |
|                                         |           |                |                                          |                              |      | CKR06BX123K* | 1231 | 1271 | 1311 | 1351 |
|                                         |           |                |                                          |                              |      | CKR06BX153K* | 1220 | 1260 | 1300 | 1340 |
|                                         |           |                |                                          |                              |      | CKR06BX183K* | 1221 | 1261 | 1301 | 1341 |
| CKR06BX223K*                            | 1222      | 1262           |                                          |                              |      | 1302         | 1342 |      |      |      |
| CKR06BX273K*                            | 1232      | 1272           |                                          |                              |      | 1312         | 1352 |      |      |      |
| CKR06BX333K*                            | 1223      | 1263           |                                          |                              |      | 1303         | 1343 |      |      |      |
| CKR06BX393K*                            | 1224      | 1264           |                                          |                              |      | 1304         | 1344 |      |      |      |
|                                         |           |                |                                          |                              |      |              |      |      |      |      |

| Cap                                      | Tol.<br>% | MIL-C-11015/19 | MIL-C-39014/02 | 39014/02 Failure Rate Levels |      |      |      |
|------------------------------------------|-----------|----------------|----------------|------------------------------|------|------|------|
|                                          |           |                | References     | M                            | P    | R    | S    |
| 100 Vdc - Radial Leaded - CK05/M39014/02 |           |                |                |                              |      |      |      |
|                                          |           |                | CKR06BX473K*   | 1225                         | 1265 | 1305 | 1345 |
|                                          |           |                | CKR06BX563K*   | 1226                         | 1266 | 1306 | 1346 |
|                                          |           |                | CKR06BX683K*   | 1227                         | 1267 | 1307 | 1347 |
|                                          |           |                | CKR06BX823K*   | 1228                         | 1268 | 1308 | 1348 |
|                                          |           |                | CKR06BX104K*   | 1229                         | 1269 | 1309 | 1349 |
| 200 Vdc - Radial Leaded - CK06/M39014/02 |           |                |                |                              |      |      |      |
|                                          |           |                | CKR06BX122K*   | 1201                         | 1241 | 1281 | 1321 |
|                                          |           |                | CKR06BX152K*   | 1202                         | 1242 | 1282 | 1322 |
|                                          |           |                | CKR06BX152M*   | 1203                         | 1243 | 1283 | 1323 |
|                                          |           |                | CKR06BX182K*   | 1204                         | 1244 | 1284 | 1324 |
|                                          |           |                | CKR06BX222K*   | 1206                         | 1246 | 1286 | 1326 |
|                                          |           |                | CKR06BX222M*   | 1207                         | 1247 | 1287 | 1327 |
|                                          |           |                | CKR06BX272K*   | 1208                         | 1248 | 1288 | 1328 |
|                                          |           |                | CKR06BX332K*   | 1209                         | 1249 | 1289 | 1329 |
|                                          |           |                | CKR06BX332M*   | 1210                         | 1250 | 1290 | 1330 |
|                                          |           |                | CKR06BX392K*   | 1211                         | 1251 | 1291 | 1331 |
|                                          |           |                | CKR06BX472K*   | 1212                         | 1252 | 1292 | 1332 |
|                                          |           |                | CKR06BX472M*   | 1213                         | 1253 | 1293 | 1333 |
|                                          |           |                | CKR06BX562K*   | 1214                         | 1254 | 1294 | 1334 |
|                                          |           |                | CKR06BX682K*   | 1215                         | 1255 | 1295 | 1335 |
|                                          |           |                | CKR06BX682M*   | 1216                         | 1256 | 1296 | 1336 |
|                                          |           |                | CKR06BX822K*   | 1217                         | 1257 | 1297 | 1337 |
|                                          |           |                | CKR06BX103K*   | 1218                         | 1258 | 1298 | 1338 |
|                                          |           |                | CKR06BX103M*   | 1219                         | 1259 | 1299 | 1339 |

Add 'TR' to end of part number for Tape & Reel  
Leads will be trimmed to .625" length  
CK06 & CKR06 1,500 per reel  
(Available in full reels only)

\*Insert proper letter symbol for Failure Rate Designator

M = 1% / 1000 Hours, P = 0.1% / 1000 Hours

R = 0.01% / 1000 Hours, S = 0.001% / 1000 Hours

Add 'V' at end of failure rate designator if stand-off design is required, (CKR only)

| Cap                                    | Tol<br>% | MIL-C-11015/20 | MIL-C-39014/05<br>References | 39014/05 Failure Rate Levels |      |      |      |
|----------------------------------------|----------|----------------|------------------------------|------------------------------|------|------|------|
|                                        |          |                |                              | M                            | P    | R    | S    |
| 50 Vdc - Axial Leaded - CK12/M39014/05 |          |                |                              |                              |      |      |      |
| 6600 pF                                | 10       | CK12BX562K     | CKR11BX562K*                 | 2651                         | 2851 | 2051 | 2251 |
| 6800 pF                                | 10       | CK12BX682K     | CKR11BX682K*                 | 2652                         | 2852 | 2052 | 2252 |
| 6800 pF                                | 20       | CK12BX682M     | CKR11BX682M*                 | 2653                         | 2853 | 2053 | 2253 |
| 8200 pF                                | 10       | CK12BX822K     | CKR11BX822K*                 | 2654                         | 2854 | 2054 | 2254 |
| 0.01 uF                                | 10       | CK12BX103K     | CKR11BX103K*                 | 2655                         | 2855 | 2055 | 2255 |
| 0.01 uF                                | 20       | CK12BX103M     | CKR11BX103M*                 | 2656                         | 2856 | 2056 | 2256 |

| Cap                                     | Tol. | MIL-C-11015/20 | MIL-C-39014/05 | 39014/05 Failure Rate Levels |      |      |      |
|-----------------------------------------|------|----------------|----------------|------------------------------|------|------|------|
|                                         | %    |                | References     | M                            | P    | R    | S    |
| 100 Vdc - Axial Leaded - CK12/M39014/05 |      |                |                |                              |      |      |      |
| 10 pF                                   | 10   | CK12BX100K     | CKR11BX100K*   | 2601                         | 2801 | 2001 | 2201 |
| 10 pF                                   | 20   | CK12BX100M     | CKR11BX100M*   | 2602                         | 2802 | 2002 | 2202 |
| 12 pF                                   | 10   | CK12BX120K     | CKR11BX120K*   | 2603                         | 2803 | 2003 | 2203 |
| 15 pF                                   | 10   | CK12BX150K     | CKR11BX150K*   | 2604                         | 2804 | 2004 | 2204 |
| 15 pF                                   | 20   | CK12BX150M     | CKR11BX150M*   | 2605                         | 2805 | 2005 | 2205 |
| 18 pF                                   | 10   | CK12BX180K     | CKR11BX180K*   | 2606                         | 2806 | 2006 | 2206 |

# MIL-C-11015 & 39014 Multilayer Ceramic Capacitors

## Ratings

| Cap                                     | Tol. | MIL-C-11015/20 | MIL-C-39014/05 | 39014/05 Failure Rate Levels |      |      |      |
|-----------------------------------------|------|----------------|----------------|------------------------------|------|------|------|
|                                         | %    |                | References     | M                            | P    | R    | S    |
| 100 Vdc - Axial Leaded - CK12/M39014/05 |      |                |                |                              |      |      |      |
| 22 pF                                   | 10   | CK12BX220K     | CKR11BX220K*   | 2607                         | 2807 | 2007 | 2207 |
| 22 pF                                   | 20   | CK12BX220M     | CKR11BX220M*   | 2608                         | 2808 | 2008 | 2208 |
| 27 pF                                   | 10   | CK12BX270K     | CKR11BX270K*   | 2609                         | 2809 | 2009 | 2209 |
| 33 pF                                   | 10   | CK12BX330K     | CKR11BX330K*   | 2610                         | 2810 | 2010 | 2210 |
| 33 pF                                   | 20   | CK12BX330M     | CKR11BX330M*   | 2611                         | 2811 | 2011 | 2211 |
| 39 pF                                   | 10   | CK12BX390K     | CKR11BX390K*   | 2612                         | 2812 | 2012 | 2212 |
| 47 pF                                   | 10   | CK12BX470K     | CKR11BX470K*   | 2613                         | 2813 | 2013 | 2213 |
| 47 pF                                   | 20   | CK12BX470M     | CKR11BX470M*   | 2614                         | 2814 | 2014 | 2214 |
| 56 pF                                   | 10   | CK12BX560K     | CKR11BX560K*   | 2615                         | 2815 | 2015 | 2215 |
| 68 pF                                   | 10   | CK12BX680K     | CKR11BX680K*   | 2616                         | 2816 | 2016 | 2216 |
| 68 pF                                   | 20   | CK12BX680M     | CKR11BX680M*   | 2617                         | 2817 | 2017 | 2217 |
| 82 pF                                   | 10   | CK12BX820K     | CKR11BX820K*   | 2618                         | 2818 | 2018 | 2218 |
| 100 pF                                  | 10   | CK12BX101K     | CKR11BX101K*   | 2619                         | 2819 | 2019 | 2219 |
| 100 pF                                  | 20   | CK12BX101M     | CKR11BX101M*   | 2620                         | 2820 | 2020 | 2220 |
| 120 pF                                  | 10   | CK12BX121K     | CKR11BX121K*   | 2621                         | 2821 | 2021 | 2221 |
| 150 pF                                  | 10   | CK12BX151K     | CKR11BX151K*   | 2622                         | 2822 | 2022 | 2222 |
| 150 pF                                  | 20   | CK12BX151M     | CKR11BX151M*   | 2623                         | 2823 | 2023 | 2223 |
| 180 pF                                  | 10   | CK12BX181K     | CKR11BX181K*   | 2624                         | 2824 | 2024 | 2224 |
| 220 pF                                  | 10   | CK12BX221K     | CKR11BX221K*   | 2625                         | 2825 | 2025 | 2225 |
| 220 pF                                  | 20   | CK12BX221M     | CKR11BX221M*   | 2626                         | 2826 | 2026 | 2226 |
| 270 pF                                  | 10   | CK12BX271K     | CKR11BX271K*   | 2627                         | 2827 | 2027 | 2227 |
| 330 pF                                  | 10   | CK12BX331K     | CKR11BX331K*   | 2628                         | 2828 | 2028 | 2228 |

\*Insert proper letter symbol for Failure Rate Designator  
M = 1% / 1000 Hours, P = 0.1% / 1000 Hours  
R = 0.01% / 1000 Hours, S = 0.001% / 1000 Hours

| Cap                                     | Tol.<br>% | MIL-C-11015/20 | MIL-C-39014/05<br>References | 39014/05 Failure Rate Levels |      |      |      |
|-----------------------------------------|-----------|----------------|------------------------------|------------------------------|------|------|------|
|                                         |           |                |                              | M                            | P    | R    | S    |
| 100 Vdc - Axial Leaded - CK12/M39014/05 |           |                |                              |                              |      |      |      |
| 330 pF                                  | 20        | CK12BX331M     | CKR11BX331M*                 | 2629                         | 2829 | 2029 | 2229 |
| 390 pF                                  | 10        | CK12BX391K     | CKR11BX391K*                 | 2630                         | 2830 | 2030 | 2230 |
| 470 pF                                  | 10        | CK12BX471K     | CKR11BX471K*                 | 2631                         | 2831 | 2031 | 2231 |
| 470 pF                                  | 20        | CK12BX471M     | CKR11BX471M*                 | 2632                         | 2832 | 2032 | 2232 |
| 560 pF                                  | 10        | CK12BX561K     | CKR11BX561K*                 | 2633                         | 2833 | 2033 | 2233 |
| 680 pF                                  | 10        | CK12BX681K     | CKR11BX681K*                 | 2634                         | 2834 | 2034 | 2234 |
| 680 pF                                  | 20        | CK12BX681M     | CKR11BX681M*                 | 2635                         | 2835 | 2035 | 2235 |
| 820 pF                                  | 10        | CK12BX821K     | CKR11BX821K*                 | 2636                         | 2836 | 2036 | 2236 |
| 1000 pF                                 | 10        | CK12BX102K     | CKR11BX102K*                 | 2637                         | 2837 | 2037 | 2237 |
| 1000 pF                                 | 20        | CK12BX102M     | CKR11BX102M*                 | 2638                         | 2838 | 2038 | 2238 |
| 1200 pF                                 | 10        | CK12BX122K     | CKR11BX122K*                 | 2639                         | 2839 | 2039 | 2239 |
| 1500 pF                                 | 10        | CK12BX152K     | CKR11BX152K*                 | 2640                         | 2840 | 2040 | 2240 |
| 1500 pF                                 | 20        | CK12BX152M     | CKR11BX152M*                 | 2641                         | 2841 | 2041 | 2241 |
| 1800 pF                                 | 10        | CK12BX182K     | CKR11BX182K*                 | 2642                         | 2842 | 2042 | 2242 |
| 2200 pF                                 | 10        | CK12BX222K     | CKR11BX222K*                 | 2643                         | 2843 | 2043 | 2243 |
| 2200 pF                                 | 20        | CK12BX222M     | CKR11BX222M*                 | 2644                         | 2844 | 2044 | 2244 |
| 2700 pF                                 | 10        | CK12BX272K     | CKR11BX272K*                 | 2645                         | 2845 | 2045 | 2245 |
| 3300 pF                                 | 10        | CK12BX332K     | CKR11BX332K*                 | 2646                         | 2846 | 2046 | 2246 |
| 3300 pF                                 | 20        | CK12BX332M     | CKR11BX332M*                 | 2647                         | 2847 | 2047 | 2247 |
| 3900 pF                                 | 10        | CK12BX392K     | CKR11BX392K*                 | 2648                         | 2848 | 2048 | 2248 |
| 4700 pF                                 | 10        | CK12BX472K     | CKR11BX472K*                 | 2649                         | 2849 | 2049 | 2249 |
| 4700 pF                                 | 20        | CK12BX472M     | CKR11BX472M*                 | 2650                         | 1850 | 2050 | 2250 |

Add 'TR' to end of part number for Tape & Reel  
CK12 & CKR11 5,000 per reel  
(Available in full reels only)

| Cap                                    | Tol. | MIL-C-11015/19 | MIL-C-39014/05<br>References | 39014/05 Failure Rate Levels |      |      |      |
|----------------------------------------|------|----------------|------------------------------|------------------------------|------|------|------|
|                                        | %    |                |                              | M                            | P    | R    | S    |
| 50 Vdc - Axial Leaded - CK13/M39014/05 |      |                |                              |                              |      |      |      |
| .012 uF                                | 10   | CK13BX123K     | CKR12BX123K*                 | 2663                         | 2863 | 2063 | 2263 |
| .015 uF                                | 10   | CK13BX153K     | CKR12BX153K*                 | 2664                         | 2864 | 2064 | 2264 |
| .015 uF                                | 20   | CK13BX153M     | CKR12BX153M*                 | 2665                         | 2865 | 2065 | 2265 |
| .018 uF                                | 10   | CK13BX183K     | CKR12BX183K*                 | 2666                         | 2866 | 2066 | 2266 |
| .022 uF                                | 10   | CK13BX223K     | CKR12BX223K*                 | 2667                         | 2867 | 2067 | 2267 |
| .022 uF                                | 20   | CK13BX223M     | CKR12BX223M*                 | 2668                         | 2868 | 2068 | 2268 |
| .027 uF                                | 10   | CK13BR273K     | CKR12BX273K*                 | 2669                         | 2869 | 2069 | 2269 |
| .033 uF                                | 10   | CK13BR333K     | CKR12BX333K*                 | 2670                         | 2870 | 2070 | 2270 |
| .033 uF                                | 20   | CK13BR333M     | CKR12BX333M*                 | 2671                         | 2871 | 2071 | 2271 |

| Cap                                     | Tol. | MIL-C-11015/19 | MIL-C-39014/05 | 39014/05 Failure Rate Levels |      |      |      |
|-----------------------------------------|------|----------------|----------------|------------------------------|------|------|------|
|                                         | %    |                | References     | M                            | P    | R    | S    |
| 50 Vdc - Axial Leaded - CK13/M39014/05  |      |                |                |                              |      |      |      |
| .039 uF                                 | 10   | CK13BR393K     | CKR12BX393K*   | 2672                         | 2872 | 2072 | 2272 |
| .047 uF                                 | 10   | CK13BR473K     | CKR12BX473K*   | 2673                         | 2873 | 2073 | 2273 |
| .047 uF                                 | 20   | CK13BR473M     | CKR12BX473M*   | 2674                         | 2874 | 2074 | 2274 |
| 100 Vdc - Axial Leaded - CK13/M39014/05 |      |                |                |                              |      |      |      |
| 5600 pF                                 | 10   | CK13BX562K     | CKR12BX562K*   | 2657                         | 2857 | 2057 | 2257 |
| 6800 pF                                 | 10   | CK13BX682K     | CKR12BX682K*   | 2658                         | 2858 | 2058 | 2258 |
| 6800 pF                                 | 20   | CK13BX682M     | CKR12BX682M*   | 2659                         | 2859 | 2059 | 2259 |
| 8200 pF                                 | 10   | CK13BX822K     | CKR12BX822K*   | 2660                         | 2860 | 2060 | 2260 |
| .01 uF                                  | 10   | CK13BX103K     | CKR12BX103K*   | 2661                         | 2861 | 2061 | 2261 |
| .01 uF                                  | 20   | CK13BX103M     | CKR12BX103M*   | 2662                         | 2862 | 2062 | 2262 |

# MIL-C-11015 & 39014 Multilayer Ceramic Capacitors

## Ratings

| Cap                                            | Tol. | MIL-C-11015/19 | MIL-C-39014/05 | 39014/05 Failure Rate Levels |      |      |      | Cap                                            | Tol. | MIL-C-11015/19 | MIL-C-39014/05 | 39014/05 Failure Rate Levels |      |      |      |
|------------------------------------------------|------|----------------|----------------|------------------------------|------|------|------|------------------------------------------------|------|----------------|----------------|------------------------------|------|------|------|
| Cap                                            | %    | MIL-C-11015/19 | References     | M                            | P    | R    | S    | Cap                                            | %    | MIL-C-11015/19 | References     | M                            | P    | R    | S    |
| <b>50 Vdc - Axial Leaded - CK14/M39014/05</b>  |      |                |                |                              |      |      |      | <b>100 Vdc - Axial Leaded - CK14/M39014/05</b> |      |                |                |                              |      |      |      |
| .056 uF                                        | 10   |                | CKR14BX563K*   | 2687                         | 2887 | 2087 | 2287 | .015 uF                                        | 20   | CK14BX153M     | CKR14BX153M*   | 2677                         | 2877 | 2077 | 2277 |
| .068 uF                                        | 10   |                | CKR14BX683K*   | 2688                         | 2888 | 2088 | 2288 | .018 uF                                        | 10   | CK14BX183K     | CKR14BX183K*   | 2678                         | 2878 | 2078 | 2278 |
| .068 uF                                        | 20   |                | CKR14BX683M*   | 2689                         | 2889 | 2089 | 2289 | .022 uF                                        | 10   | CK14BX223K     | CKR14BX223K*   | 2679                         | 2879 | 2079 | 2279 |
| .082 uF                                        | 10   |                | CKR14BX823K*   | 2690                         | 2890 | 2090 | 2290 | .022 uF                                        | 20   | CK14BX223M     | CKR14BX223M*   | 2680                         | 2880 | 2080 | 2280 |
| .10 uF                                         | 10   |                | CKR14BX104K*   | 2691                         | 2891 | 2091 | 2291 | .027 uF                                        | 10   | CK14BX273K     | CKR14BX273K*   | 2681                         | 2881 | 2081 | 2281 |
| .10 uF                                         | 20   |                | CKR14BX104M*   | 2692                         | 2892 | 2092 | 2292 | .033 uF                                        | 10   | CK14BX333K     | CKR14BX333K*   | 2682                         | 2882 | 2082 | 2282 |
| .12 uF                                         | 10   | CK14BR124K     | CKR14BR124K*   | 2699                         | 2899 | 2099 | 2299 | .033 uF                                        | 20   | CK14BX333M     | CKR14BX333M*   | 2683                         | 2883 | 2083 | 2283 |
| .15 uF                                         | 10   | CK14BR154K     | CKR14BR154K*   | 2700                         | 2900 | 2100 | 2300 | .039 uF                                        | 10   | CK14BX393K     | CKR14BX393K*   | 2684                         | 2884 | 2084 | 2284 |
| .15 uF                                         | 20   | CK14BR154M     | CKR14BR154M*   | 2701                         | 2901 | 2101 | 2301 | .047 uF                                        | 10   | CK14BX473K     | CKR14BX473K*   | 2685                         | 2885 | 2085 | 2285 |
| .18 uF                                         | 10   | CK14BR184K     | CKR14BR184K*   | 2702                         | 2902 | 2102 | 2302 | .047 uF                                        | 20   | CK14BX473M     | CKR14BX473M*   | 2686                         | 2886 | 2086 | 2286 |
| .22 uF                                         | 10   | CK14BR224K     | CKR14BR224K*   | 2703                         | 2903 | 2103 | 2303 | .056 uF                                        | 10   | CK14BR563K     | CKR14BR563K*   | 2693                         | 2893 | 2093 | 2293 |
| .22 uF                                         | 20   | CK14BR224M     | CKR14BR224M*   | 2704                         | 2904 | 2104 | 2304 | .068 uF                                        | 10   | CK14BR683K     | CKR14BR683K*   | 2694                         | 2894 | 2094 | 2294 |
| .27 uF                                         | 10   | CK14BR274K     | CKR14BR274K*   | 2705                         | 2905 | 2105 | 2305 | .068 uF                                        | 20   | CK14BR683M     | CKR14BR683M*   | 2695                         | 2895 | 2095 | 2295 |
| <b>100 Vdc - Axial Leaded - CK14/M39014/05</b> |      |                |                |                              |      |      |      | .082 uF                                        | 10   | CK14BR823K     | CKR14BR823K*   | 2696                         | 2896 | 2096 | 2296 |
| .012 uF                                        | 10   | CK14BX123K     | CKR14BX123K*   | 2675                         | 2875 | 2075 | 2275 | .1 uF                                          | 10   | CK14BR104K     | CKR14BR104K*   | 2697                         | 2897 | 2097 | 2297 |
| .015 uF                                        | 10   | CK14BX153K     | CKR14BX153K*   | 2676                         | 2876 | 2076 | 2276 | .1 uF                                          | 20   | CK14BR104M     | CKR14BR104M*   | 2698                         | 2898 | 2098 | 2298 |

| Cap                                            | Tol. | MIL-C-11015/19 | MIL-C-39014/05 | 39014/05 Failure Rate Levels |      |      |      | Cap                                            | Tol. | MIL-C-11015/19 | MIL-C-39014/05 | 39014/05 Failure Rate Levels |      |      |      |
|------------------------------------------------|------|----------------|----------------|------------------------------|------|------|------|------------------------------------------------|------|----------------|----------------|------------------------------|------|------|------|
| Cap                                            | %    | MIL-C-11015/19 | References     | M                            | P    | R    | S    | Cap                                            | %    | MIL-C-11015/19 | References     | M                            | P    | R    | S    |
| <b>50 Vdc - Axial Leaded - CK15/M39014/05</b>  |      |                |                |                              |      |      |      | <b>100 Vdc - Axial Leaded - CK15/M39014/05</b> |      |                |                |                              |      |      |      |
| .33 uF                                         | 10   | CK15BR334K     | CKR15BR334K*   | 2719                         | 2919 | 2119 | 2319 | .068 uF                                        | 20   |                | CKR15BX683M*   | 2708                         | 2908 | 2108 | 2308 |
| .33 uF                                         | 20   | CK15BR334M     | CKR15BR334M*   | 2720                         | 2920 | 2120 | 2320 | .082 uF                                        | 10   |                | CKR15BX823K*   | 2709                         | 2909 | 2109 | 2309 |
| .47 uF                                         | 10   | CK15BR474K     | CKR15BR474K*   | 2721                         | 2921 | 2121 | 2321 | .10 uF                                         | 10   | CK15BX104K     | CKR15BX104K*   | 2710                         | 2910 | 2110 | 2310 |
| .47 uF                                         | 20   | CK15BR474M     | CKR15BR474M*   | 2722                         | 2922 | 2122 | 2322 | .10 uF                                         | 20   | CK15BX104M     | CKR15BX104M*   | 2711                         | 2911 | 2111 | 2311 |
| .68 uF                                         | 10   |                | CKR15BR684K*   | 2723                         | 2923 | 2123 | 2323 | .12 uF                                         | 10   | CK15BR124K     | CKR15BR124K*   | 2712                         | 2912 | 2112 | 2312 |
| .68 uF                                         | 20   |                | CKR15BR684M*   | 2724                         | 2924 | 2124 | 2324 | .15 uF                                         | 10   | CK15BR154K     | CKR15BR154K*   | 2713                         | 2913 | 2113 | 2313 |
| 1.0 uF                                         | 10   | CK15BR105K     | CKR15BR105K*   | 2725                         | 2925 | 2125 | 2325 | .15 uF                                         | 20   | CK15BR154M     | CKR15BR154M*   | 2714                         | 2914 | 2114 | 2314 |
| 1.0 uF                                         | 20   | CK15BR105M     | CKR15BR105M*   | 2726                         | 2926 | 2126 | 2326 | .18 uF                                         | 10   | CK15BR184K     | CKR15BR184K*   | 2715                         | 2915 | 2115 | 2315 |
| <b>100 Vdc - Axial Leaded - CK15/M39014/05</b> |      |                |                |                              |      |      |      | .22 uF                                         | 10   | CK15BR224K     | CKR15BR224K*   | 2716                         | 2916 | 2116 | 2316 |
| .056 uF                                        | 10   |                | CKR15BX563K*   | 2706                         | 2906 | 2106 | 2306 | .22 uF                                         | 20   | CK15BR224M     | CKR15BR224M*   | 2717                         | 2917 | 2117 | 2317 |
| .068 uF                                        | 10   |                | CKR15BX683K*   | 2707                         | 2907 | 2107 | 2307 | .27 uF                                         | 10   | CK15BR274K     | CKR15BR274K*   | 2718                         | 2918 | 2118 | 2318 |

| Cap                                           | Tol. | MIL-C-11015/19 | MIL-C-39014/05 | 39014/05 Failure Rate Levels |      |      |      | Cap                                            | Tol. | MIL-C-11015/19 | MIL-C-39014/05 | 39014/05 Failure Rate Levels |      |      |      |
|-----------------------------------------------|------|----------------|----------------|------------------------------|------|------|------|------------------------------------------------|------|----------------|----------------|------------------------------|------|------|------|
| Cap                                           | %    | MIL-C-11015/19 | References     | M                            | P    | R    | S    | Cap                                            | %    | MIL-C-11015/19 | References     | M                            | P    | R    | S    |
| <b>50 Vdc - Axial Leaded - CK16/M39014/05</b> |      |                |                |                              |      |      |      | <b>100 Vdc - Axial Leaded - CK16/M39014/05</b> |      |                |                |                              |      |      |      |
| 10 uF                                         | 10   | CK16BR105K     | CKR16BR105K*   | 2731                         | 2931 | 2131 | 2331 | .47 uF                                         | 10   | CK16BR474K     | CKR16BR474K*   | 2727                         | 2927 | 2127 | 2327 |
| 10 uF                                         | 20   | CK16BR105M     | CKR16BR105M*   | 2732                         | 2932 | 2132 | 2332 | .47 uF                                         | 20   | CK16BR474M     | CKR16BR474M*   | 2728                         | 2928 | 2128 | 2328 |
| 2.2 uF                                        | 10   | CK16BR225K     | CKR16BR225K*   | 2733                         | 2933 | 2133 | 2333 | .68 uF                                         | 10   |                | CKR16BR684K*   | 2729                         | 2929 | 2129 | 2329 |
| 2.2 uF                                        | 20   | CK16BR225M     | CKR16BR225M*   | 2734                         | 2934 | 2134 | 2334 | .68 uF                                         | 20   |                | CKR16BR684M*   | 2730                         | 2930 | 2130 | 2330 |
| .3 uF                                         | 10   | CK16BR335K     | CKR16BR335K*   | 2735                         | 2935 | 2135 | 2335 |                                                |      |                |                |                              |      |      |      |
| 3.3 uF                                        | 20   | CK16BR335M     | CKR16BR335M*   | 2736                         | 2936 | 2136 | 2336 |                                                |      |                |                |                              |      |      |      |

\*Insert proper letter symbol for Failure Rate Designator  
M = 1% / 1000 Hours, P = 0.1% / 1000 Hours  
R = 0.01% / 1000 Hours, S = 0.001% / 1000 Hours  
Add 'V' at end of failure rate designator if stand-off design is required, (CKR only)

Add 'TR' to end of part number for Tape & Reel  
Leads will be trimmed to .625" length  
CK13 - 5,000 per reel  
CK14 - 3,000 per reel  
CK15 - 500 per reel  
CK16 - 300 per reel  
(Available in full reels only)

**Notice and Disclaimer:** All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.

DISCONTINUED CONTACT KEMET FOR EQUIVALENT REPLACEMENT