




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M	REVISED PER ECO-16-004940	06AUG2016	NK	MZ



RECOMMENDED LAYOUT

- ① NYLON, UL 94-VO RATED, RED.
- ② PHOSPHOR BRONZE.
- ③ 3.81µm [.000150] MIN TIN-LEAD OVER 1.27µm [.000050] MIN NICKEL.
- ④ 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- ⑤ .000150 MIN TIN OVER .000050 MIN NICKEL.
- ⑥ 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.

OBSOLETE	6	NO	1-207528-0
	6	YES	207528-9
	5	NO	207528-8
	5	YES	207528-7
	4	NO	207528-4
	4	YES	207528-3
	3	NO	-207528-2-
	3	YES	207528-1
CONTACT FINISH		MOUNTING TABS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	03/19/92	 TE Connectivity						
DIMENSIONS: INCHES			L.SIPE	3-25-92							
			CHK	R.STONE	NAME SOCKET HEADER ASSEMBLY, 12 POSITION, METRIMATE						
			APVD	A.TRAVIS							
			PRODUCT SPEC 108-10033								
			APPLICATION SPEC —								
			WEIGHT								
MATERIAL			FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
HOUSING: 1			CONTACT: SEE TABLE		A2	00779	G-207528	—			
CUSTOMER DRAWING						SCALE	4:1	SHEET	1 of 1	REV	M