


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		E1	REVISED PER ECO-11-004917	11MAR11	RK	HMR

D


C

B


A



1. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.3 – 0.9MM² (22–18 AWG).
3. INSULATION RANGE: 1.50–2.79[.059–.110] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
5. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SECTION A—A
SCALE 20:1



SECTION B—B
SCALE 20:1

GOLD 5	0.25[.010] BRASS	1–794228–0
GOLD 1	0.25[.010] BRASS	794228–3
PRE–TIN	0.25[.010] BRASS	794228–1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 11AUG2003	TE Connectivity			
DIMENSIONS: INCHES		CHK C. JONES 11AUG2003				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 0.15 [.006] 4 PLC ± ANGLES ±		PIN, LOOSE PIECE, MINI UNIVERSAL MATE–N–LOK 2			
MATERIAL SEE TABLE		APVD C. JONES 11AUG2003	APPLICATION SPEC		SIZE A2	CAGE CODE 00779
FINISH SEE TABLE		WEIGHT	DRAWING NO C=794228		RESTRICTED TO —	
CUSTOMER DRAWING		SCALE 10:1		SHEET 1 of 1	REV E1	