





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
GP	0	A		RELEASED PER EC 0S12-0488-04	10JAN05	MY SB
		B		REVISED PER EC 0S11-0007-05	14FEB05	MY SB


- NOTES:
- MATERIAL:
HOUSING AND EJECTOR:
HIGH TEMPERATURE NYLON
CONTACT:
PHOSPHOR BRONZE
 - FINISH:
CONTACT AREA:
0.00076[.000030] MIN THICK GOLD
0.00381[.000150] MIN THICK NICKEL
SOLDERTAIL:
0.00381[.000150] MIN THICK MATTE TIN OVER
0.00064[.000025] MIN THICK NICKEL
 - MODULE BOARD PADS:
FOR OPTIMUM PERFORMANCE PADS SHOULD BE SMOOTH AND FLAT
PADS TO BE PLATED WITH:
0.00102[.000040] MIN THICK GOLD OVER
0.00127[.000050] MIN THICK NICKEL





SECTION Y - Y
SCALE 5:1

DETAIL C	DETAIL A	NON-BUFFERED DRAM, 3.3 VOLT	5390170-6
FUNCTION KEY #1	VOLTAGE KEY #2	PART DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN M. YEOMANS 10JAN05	tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm[INCHES]		CHK M. YEOMANS 10JAN05		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. BURKHOLDER 10JAN05	NAME SOCKET ASSEMBLY, 168 POSITION, CENTER PLASTIC POST 2.60[.103] SOLDERTAIL, LOW PROFILE DIMM 2 P	
0 PLC ± 1 PLC ± 2 PLC ±0.13[.005] 3 PLC ± 4 PLC ±		PRODUCT SPEC -	SIZE A2	
MATERIAL -		APPLICATION SPEC -	CAGE CODE 00779	
FINISH -		WEIGHT -	DRAWING NO 5390170	
		CUSTOMER DRAWING	RESTRICTED TO -	
		SCALE 2:1	SHEET 1 OF 3	
			REV B	




THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				20							
© COPYRIGHT 20				BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.											
LOC		DIST		REVISIONS											
GP		0		P	LTR	DESCRIPTION				DATE	DWN	APVD			
				-		SEE SHEET 1				-	-	-			




MINIMUM REPAIRABLE
SOCKET TO SOCKET SPACING

WITH THE MODULES REMOVED, SOCKETS ON 15.88 [0.625]
OR GREATER SPACING CAN BE INDIVIDUALLY UNSOLDERED
FROM THE BOARD AND REMOVED IF NECESSARY.



MINIMUM SOCKET TO SOCKET SPACING

WITH A 4.00 [0.158] WIDE MODULE BOARD, A SOCKET TO SOCKET SPACING OF 13.34 [0.525] WILL
LEAVE APPROXIMATELY 0.65 [0.026] OF CLEARANCE BETWEEN THE MODULE AND THE NEXT SOCKET BODY.
THIS SPACING MAY OR MAY NOT BE SUITABLE DEPENDING ON YOUR MINIMUM GAP REQUIREMENTS.



POSSIBLE SOCKET TO SOCKET SPACING FOR 9MM MODULE

WITH A 9.00 [0.355] WIDE MODULE BOARD, A SOCKET TO SOCKET SPACING OF 22.86 [0.900] WILL
LEAVE APPROXIMATELY 0.66 [0.026] CLEARANCE BETWEEN THE ADJACENT MODULES.
THIS SPACING MAY OR MAY NOT BE SUITABLE DEPENDING ON YOUR MINIMUM GAP REQUIREMENTS.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm[INCHES]

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±0.13[0.005]
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	-

DWN
M. YEOMANS 10JAN05

CHK
M. YEOMANS 10JAN05

APVD
S. BURKHOLDER 10JAN05

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

Tyco Electronics
Harrisburg, PA 17105-3608

NAME
SOCKET ASSEMBLY, 168 POSITION,
CENTER PLASTIC POST 2.60[0.103]
SOLDERTAIL, LOW PROFILE DIMM 2 P

SIZE
A2

CAGE CODE
00779

DRAWING NO
5390170

RESTRICTED TO
-

SCALE
2:1

SHEET
3

OF
3

REV
B