





LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
AF		50								A		REL -1 PER 0710-0367-95		28AUG95		MF/NN	



- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.08±0.08 [.200±.003] CENTERS.
- 2 SLOT ACCEPTS 0.25-0.32mm [#30-#28] AWG COPPER MAGNET WIRE 2 WIRES MAX OF THE SAME SIZE PER SLOT.
- 3 IDENTIFICATION NUMBER 6 FOR WIRE SLOT SIZE.
- 4 0.00203 [.000080] - 0.00381 [.000150] TIN PER MIL-T-10727 OVER 0.00254 [.000100] -0.00508 [.000200] COPPER UNDERPLATE PER MIL-C-14550.



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

63818-1											
PART NO											
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± 1° MATERIAL H04 BRASS FINISH 4						DR 29/OCT/94 MICHAEL S. FEHER CHK 31/OCT/94 JEFF R. RUTH APPD 31/OCT/94 NELSON E. NEFF APPD 31/OCT/94 TERRY L. SHUTTER PRODUCT SPEC 108-2012 APPLICATION SPEC 114-2069 WEIGHT -					
						AMP AMP Incorporated Harrisburg, PA 17105-3608					
						NAME TERMINAL, POSTED, MAG-MATE™					
						SIZE C	CAGE CODE 00779	DRAWING NO C=63818	SHEET 1 OF 1		