

Preliminary


TOSHIBA CMOS Digital Integrated Circuit Silicon Monolithic

TC7SZ14F, TC7SZ14FU

Schmitt Inverter

Features

- High output drive: ± 24 mA (min) @ $V_{CC} = 3$ V
- High speed: $t_{pd} = 3.7$ ns (typ.) @ $V_{CC} = 5$ V, 50 pF
- Wide operating voltage range: $V_{CC} (opr) = 1.65$ to 5.5 V
- High latch-up immunity: Higher than or equal to ± 500 mA
- High ESD : Higher than or equal to ± 200 V (JEITA)
: Higher than or equal to ± 2000 V (MIL)
- Power-down protection is provided on all inputs and outputs.
- Matches the performance of TC74LCX Series when operated at 3.3 V



Weight:


SSOP5-P-0.95 : 0.016 g (typ.)

SSOP5-P-0.65A : 0.006 g (typ.)


Maximum Ratings ($T_a = 25^\circ\text{C}$)

Characteristics	Symbol	Rating	Unit
Supply voltage range	V_{CC}	-0.5 to 6	V
DC input voltage	V_{IN}	-0.5 to 6	V
DC output voltage	V_{OUT}	-0.5 to 6	V
Input diode current	I_{IK}	-20	mA
Output diode current	I_{OK}	-20	mA
DC output current	I_{OUT}	± 50	mA
DC V_{CC} /ground current	I_{CC}	± 50	mA
Power dissipation	P_D	200	mW
Storage temperature	T_{stg}	-65 to 150	$^\circ\text{C}$
Lead temperature (10 s)	T_L	260	$^\circ\text{C}$


Marking



Pin Assignment (top view)



Logic Diagram



Truth Table

A	Y
L	H
H	L

Recommended Operating Conditions

Characteristics	Symbol	Rating	Unit
Supply voltage	V _{CC}	1.65 to 5.5	V
		1.5 to 5.5 (Note 1)	
Input voltage	V _{IN}	0 to 5.5	V
Output voltage	V _{OUT}	0 to 5.5 (Note 2)	V
		0 to V _{CC} (Note 3)	
Operating temperature	T _{opr}	−40 to 85	°C

Note 1: Data retention only

Note 2: V_{CC} = 0 V

Note 3: High or Low State

Electrical Characteristics

DC Electrical Characteristics

Characteristics	Symbol	Test Condition	V _{CC} (V)	Ta = 25°C			Ta = −40–85°C		Unit
				Min	Typ.	Max	Min	Max	
Positive threshold voltage	V _P	—	1.65	0.6	1.0	1.4	0.65	1.4	V
			1.8	0.7	1.1	1.5	0.7	1.5	
			2.3	1.0	1.4	1.8	1.0	1.8	
			3.0	1.3	1.75	2.2	1.3	2.2	
			4.5	1.9	2.45	3.1	1.9	3.1	
			5.5	2.2	2.9	3.6	2.2	3.6	
Negative threshold voltage	V _N	—	1.65	0.2	0.5	0.8	0.2	0.8	V
			1.8	0.25	0.55	0.9	0.25	0.9	
			2.3	0.40	0.75	1.15	0.40	1.15	
			3.0	0.6	1.0	1.5	0.6	1.5	
			4.5	1.0	1.43	2.0	1.0	2.0	
			5.5	1.2	1.70	2.4	1.2	2.4	
Hysteresis voltage	V _H	—	1.65	0.1	0.48	0.9	0.1	1.0	V
			1.8	0.15	0.54	1.0	0.15	1.0	
			2.3	0.25	0.65	1.1	0.25	1.1	
			3.0	0.4	0.77	1.2	0.4	1.2	
			4.5	0.6	1.01	1.5	0.6	1.5	
			5.5	0.7	1.18	1.7	0.7	1.7	

Characteristics	Symbol	Test Condition	V _{CC} (V)	Ta = 25°C			Ta = -40~85°C		Unit
				Min	Typ.	Max	Min	Max	
High-level output voltage	V _{OH}	V _{IN} = V _{IL}	I _{OH} = -100 µA	1.65	1.55	1.65	—	1.55	V
				1.8	1.7	1.8	—	1.7	
				2.3	2.2	2.3	—	2.2	
				3.0	2.9	3.0	—	2.9	
				4.5	4.4	4.5	—	4.4	
			I _{OH} = -4 mA	1.65	1.29	1.52	—	1.29	
			I _{OH} = -8 mA	2.3	1.9	2.15	—	1.9	
			I _{OH} = -16 mA	3.0	2.4	2.8	—	2.4	
			I _{OH} = -24 mA	3.0	2.3	2.68	—	2.3	
			I _{OH} = -32 mA	4.5	3.8	4.2	—	3.8	
Low-level output voltage	V _{OL}	V _{IN} = V _{IH}	I _{OL} = 100 µA	1.65	—	0	0.1	—	
				1.8	—	0	0.1	—	
				2.3	—	0	0.1	—	
				3.0	—	0	0.1	—	
				4.5	—	0	0.1	—	
			I _{OL} = 4 mA	1.65	—	0.08	0.24	—	
			I _{OL} = 8 mA	2.3	—	0.1	0.3	—	
			I _{OL} = 16 mA	3.0	—	0.15	0.4	—	
			I _{OL} = 24 mA	3.0	—	0.22	0.55	—	
			I _{OL} = 32 mA	4.5	—	0.22	0.55	—	
Input leakage current	I _{IN}	V _{IN} = 5.5 V or GND	0~5.5	—	—	±1	—	±10	µA
Power OFF leakage current	I _{OFF}	V _{IN} or V _{OUT} = 5.5 V	0.0	—	—	1	—	10	µA
Quiescent supply current	I _{CC}	V _{IN} = 5.5 V or GND	1.65~5.5	—	—	1	—	10	µA

AC Electrical Characteristics (Unless otherwise specified Input: t_r = t_f = 3 ns)

Characteristics	Symbol	Test Condition	V _{CC} (V)	Ta = 25°C			Ta = -40~85°C		Unit
				Min	Typ.	Max	Min	Max	
Propagation delay time	t _{pLH} t _{pHL}	C _L = 15 pF, R _L = 1 MΩ	1.65	2.0	9.1	15.0	2.0	15.6	ns
			1.8	2.0	7.6	12.5	2.0	13	
			2.5 ± 0.2	1.0	5.0	9.0	1.0	9.5	
			3.3 ± 0.3	1.0	3.7	6.3	1.0	6.5	
			5.0 ± 0.5	0.5	3.1	5.2	0.5	5.5	
		C _L = 50 pF, R _L = 500 Ω	3.3 ± 0.3	1.5	4.4	7.2	1.5	7.5	
			5.0 ± 0.5	0.5	3.7	5.9	0.8	6.2	
Input capacitance	C _{IN}	—	—	—	—	—	—	—	pF
Power dissipation capacitance	C _{PD}	(Note 4)	—	—	—	—	—	—	pF

Note 4: CPD is defined as the value of the internal equivalent capacitance which is Calculated from the operating current consumption without load.


Average operating current can be obtained by the equation.

$$I_{CC (opr)} = C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC}$$

Package Dimensions

SSOP5-P-0.95

Unit : mm




Weight: 0.016 g (typ.)

Package Dimensions

SSOP5-P-0.65A

Unit : mm



Weight: 0.006 g (typ.)

RESTRICTIONS ON PRODUCT USE

000707EBA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.