

Digital Multimeter, Bench

2,000 Display Counts



Specification Table

Basic Functions	Range	Best Accuracy
DC Voltage	200 mV / 2 V / 20 V / 200 V / 1,000 V	$\pm(0.5\% + 2)$
AC Voltage	2 V / 20 V / 200 V / 1,000 V	$\pm(0.8\% + 3)$
DC Current	200 μ A / 2 mA / 20 mA / 200 mA / 10 A	$\pm(0.8\% + 2)$
AC Current	2 mA / 20 mA / 200 mA / 10 A	$\pm(1\% + 3)$
Resistance	200 Ω / 2 k Ω / 20 k Ω / 200 k Ω / 2 M Ω / 20 M Ω	$\pm(0.8\% + 3)$
Capacitance	20 nF / 2 μ F / 200 μ F	$\pm(4\% + 3)$
Frequency	2 kHz / 200 kHz	$\pm(1.5\% + 5)$
Temperature ($^{\circ}$ C)	-40 $^{\circ}$ C to 1,000 $^{\circ}$ C	$\pm(1.2\% + 3)$
Special Functions		
Transistor	-	✓
Sleep Mode	-	✓
Diode	-	✓
Continuity Buzzer	-	✓
Display Backlight	-	✓
REL	-	✓
Maximum / Minimum Mode	-	✓
Low Battery Display	-	✓
Input Impedance for DC Voltage Measurement	>10 M Ω	✓
Data Hold	-	✓
Maximum Display	1,999	



Digital Multimeter, Bench

2,000 Display Counts



General Characteristics

Power	220 V ac / 50 Hz or 1.5 V Battery × 6 (R14)
LCD Size	108 × 35 mm
Product Colour	Orange and Grey
Product Net Weight	1,500 g
Product Size	300 × 245 × 105 mm
Standard Accessories	Test Lead, 220 V ac Power Cord, English Manual, Point Contact Temperature Probe, Multi-Purpose Socket
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	4 pieces
Standard Carton Measurement	685 × 370 × 325 mm (0.082CBM Per Export Carton)
Standard Carton Gross Weight	14 kg

Part Number Table

Description	Part Number
DMM, Bench, 2,000 Counts	72-8715

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA™ is the registered trademark of the Group. © Premier Farnell plc 2012.

