

Ordering number FA11905_TINA3-S

Family	Tina3	FWHM	(simulated) 6
Type	Assembly	Efficiency	(simulated) 0 %
LED	Z5	cd/Im	-
Color	White	Gerber File	Available
Diameter	16.1 mm		
Height	11.4 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	Ready		

Ordering number FA11824_TINA3-W

Family	Tina3	FWHM	38 degrees
Type	Assembly	Efficiency	92 %
LED	Z5	cd/Im	1.600
Color	White	Gerber File	Available
Diameter	16.1 mm		
Height	6.9 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	Ready		

Ordering number FA11825_TINA3-WW

Family	Tina3	FWHM	43 degrees
Type	Assembly	Efficiency	90 %
LED	Z5	cd/Im	1.100
Color	White	Gerber File	Available
Diameter	16.1 mm		
Height	6.9 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	Ready		

Ordering number FA11826_TINA3-WWW

Family	Tina3	FWHM	62 degrees
Type	Assembly	Efficiency	89 %
LED	Z5	cd/Im	0.700
Color	White	Gerber File	Available
Diameter	16.1 mm		
Height	6.9 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Pin, tape		
Status	Ready		



PRODUCT DATASHEET
Tina3 series
last update 9/4/2013



NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Tina3 series

last update 9/4/2013



GENERAL INFORMATION

- Product series especially designed & optimized for Z5 series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.


Please find more information about used material from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

- Optic holder molded by high quality PC material (120 degrees of Celcius / 248 degrees of Fahrenheit).

Relative intensity of FA11826_Tina3-WWW-XP-G



4

3

2

1

4

3

2


1

D


C

B

A




Oval beam direction




8.6

c / c




11.4

Spot version height



6.9

0.8



Ø 16.1

Top view

Tolerances if not otherwise shown
According to DIN ISO 2768-1
Linear measures:
Up to 30mm class F, otherwise class M.
According to DIN ISO 2768-2
Form and position: class K

LEDiL

Ledil Oy
Salorankatu 10
FIN 24240 SALO
Finland

THIRD ANGLE PROJECTION:



DRAWING TITLE

TINA3 Datasheet

This drawing is the property
of LEDiL Oy. It may not be
reproduced, copied or
communicated without a written
agreement with LEDiL Oy."

SIZE

A4

PART NUMBER

-

SCALE

4:3

WEIGHT

-


SHEET

1 / 1


D

A


Luminaire: Ledil Oy FA11824_TINA3-W (Seuol Z5 68lm @ 250mA) Efficiency=92%
Lamps: 1 x Seuol Z5 68lm @ 250mA




Luminaire: Ledil Oy FA11825_TINA3-WW (Seoul Z5 68lm @ 250mA) Efficiency=90%
Lamps: 1 x Seoul Z5 68lm @ 250mA



Luminaire: Ledil Oy FA11826_TINA3-WWW (Seoul Z5 68lm @ 250mA) Efficiency=89%
Lamps: 1 x Seoul Z5 68lm @ 250mA



Luminaire: Ledil Oy FA11824_TINA3-W (Seuol Z5 68lm @ 250mA) Efficiency=92%
Lamps: 1 x Seuol Z5 68lm @ 250mA




cd/klm

C0 - C180

C90 - C270

Luminaire: Ledil Oy FA11825_TINA3-WW (Seoul Z5 68lm @ 250mA) Efficiency=90%
Lamps: 1 x Seoul Z5 68lm @ 250mA



cd/klm

— C0 - C180

— C90 - C270

Luminaire: Ledil Oy FA11826_TINA3-WWW (Seoul Z5 68lm @ 250mA) Efficiency=89%
Lamps: 1 x Seoul Z5 68lm @ 250mA

